

# WS17S WATER/STEAM HOSE 17 BAR

## HIGH PRESSURE OILFIELD HOSE



### APPLICATION

Saturated Steam

**TEMPERATURE** (-40°C to +208°C) (-40°F to +406°F)

**CONSTRUCTION** Tube Black EPDM Rubber

Reinforcement High Tensile Steel Cords

Cover Red EPDM Rubber  
Abrasion, Ozone & Heat Resistant

**STANDARDS** Additional standards/certifications available upon customer request

**COUPLINGS** Crimped



ID		OD		WORKING PRESSURE		BURST PRESSURE		MBR		WEIGHT		MAX HOSE LENGTH		REFERENCE CODE	REFERENCE NUMBER
inch	mm	inch	mm	bar	psi	bar	psi	inch	mm	kg/m	lb/ft	m	ft		
1/2	13	0.98	25	17	255	170	2550	5	0.1	0.6	0.4	60	196	H2WS17S08	-
3/4	19	1.30	33	17	255	170	2550	7	0.2	0.8	0.6	60	196	H2WS17S12	-
1	25	1.57	40	17	255	170	2550	10	0.3	1.0	0.7	60	196	H2WS17S16	-
1 1/2	38	2.13	54	17	255	170	2550	15	0.4	1.7	1.1	60	196	H2WS17S24	-
2	51	2.72	69	17	255	170	2550	16	0.4	2.6	1.7	60	196	H2WS17S32	-
2 1/2	63.5	3.15	80	17	255	170	2550	18	0.5	3.0	2.0	60	196	H2WS17S40	-

Gates Corporation is a leading manufacturer of application-specific fluid power and power transmission solutions. At Gates, we are driven to push the boundaries of materials science to engineer products that continually exceed expectations.