

WT20S POTABLE WATER DELIVERY HOSE 20 BAR



HIGH PRESSURE OILFIELD HOSE

APPLICATION

Potable Water Transfer

TEMPERATURE	(-30°C to +100°C) (-22°F to +212°F)	
CONSTRUCTION	Tube	White Color Non-Toxic, Taste & Odour Free, Natural Rubber
	Reinforcement	High Tensile Synthetic Textile
	Cover	Orange CR/BR Blend Rubber Abrasion, Ozone & Hydrocarbon Resistant
STANDARDS	Additional standards/certifications available upon customer request	
COUPLINGS	Crimped	



ID		OD		WORKING PRESSURE		BURST PRESSURE		MBR		WEIGHT		MAX HOSE LENGTH		REFERENCE CODE	REFERENCE NUMBER
inch	mm	inch	mm	bar	psi	bar	psi	inch	mm	kg/m	lb/ft	m	ft		
1/2	13	0.91	23	20	300	80	1200	3	0.1	0.4	0.3	60	196	H2WT20S08	-
3/4	19	1.22	31	20	300	80	1200	5	0.1	0.6	0.4	60	196	H2WT20S12	-
1	25	1.46	37	20	300	80	1200	6	0.2	0.8	0.5	60	196	H2WT20S16	-
1 1/2	38	1.97	50	20	300	80	1200	9	0.2	1.1	0.7	60	196	H2WT20S24	-
2	51	2.68	68	20	300	80	1200	12	0.3	1.9	1.3	60	196	H2WT20S32	-
3	76	3.90	99	20	300	80	1200	18	0.5	2.7	1.8	60	196	H2WT20S48	-
4	102	4.72	120	20	300	80	1200	24	0.6	3.8	2.6	60	196	H2WT20S64	-

Gates Corporation is a leading manufacturer of application-specific fluid power and power transmission solutions. At Gates, we are driven to push the boundaries of materials science to engineer products that continually exceed expectations.