

Belts and Coolant Hose for Farm Tractors and Farm Equipment Alphabetical Listing (1969 And Older)

If you cannot locate the application, refer to the
Manufacturers' Part Number or Competitive Changeover
Listing in the 31-2040 Catalog.

Order Belts and Hose by Gates Number. Manufacturers'
Part Number is shown for reference only.

AG-GATOR

Tractors Belts

Application	Mfr. Part No.	Belt No.
2004		
CUMMINS V-378 ENG.		
Fan & W.P.....	178686	②TR22344 ^{GS}
Pump.....	17580	②9580 ^{GS}
CUMMINS V-504C ENG.		
Fan & W.P.....		②TR22525 ^{GS}
Fan To Alt.....		②7370
A.C.....		7410
Hyd. Pump.....		②9580 ^{GS}

Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
2004		
CUMMINS V-378 ENG.		
Lower.....		26519
CUMMINS V-504C ENG.		
Upper.....		26512

Farm Equipment Belts

Application	Mfr. Part No.	Belt No.
804 SPRAYER		
FORD V-8 ENG.		
Fan.....		②9570 ^{GS}

ALLIS-CHALMERS; See Deutz-Allis Also

Tractors Belts

Application	Mfr. Part No.	Belt No.
B; C		
Fan.....	207003	TR22322 ^{GS}
Fan & Gen.; W/34 1/8" Belt O.C.	215885	TR22336 ^{GS}
Fan & Gen.; W/37 1/8" Belt O.C.	209656	TR22373 ^{GS}
CA		
Fan & Gen.....	209656	TR22373 ^{GS}
D10; D12		
10 ENG.; 138 ENG.; 149 ENG.		
Fan & Gen.; Ser. No. D10-3501 & Before; Ser. No. D12-3001...	209656	TR22373 ^{GS}
Fan & Gen.; Ser. No. D10-3502; Ser. No. D12-3002 & After.....	233432	7380
D14		
Fan & Gen.; W/Elec. Starter.....	209656	TR22373 ^{GS}
Fan & Gen.; W/O Elec. Starter ...	207003	TR22322 ^{GS}

ALLIS-CHALMERS; See Deutz-Allis Also - Continued

Belts - Continued

Application	Mfr. Part No.	Belt No.
D15D; D15G		
D175 DIESEL ENG.		
Fan & Gen.....	233489	②9420 ^{GS}
160 GAS ENG.; G149 GAS ENG.		
Fan & Gen.....	233432	7380
D17D; D17G; D17 SERIES IV		
DA262 DIESEL ENG.		
Fan & Gen.; Ser. No. 119938 & Before.....	229559	②9455 ^{GS}
Fan & Gen.; Ser. No. 119939 & After.....	237048	9455 ^{GS}
P.S.....	235394	9375 ^{GS}
226 GAS ENG.		
Fan & Gen.....	229211	9463 ^{GS}
P.S.; Ser. No. 42001 & After.....	237386	9425 ^{GS}
D19; D19D		
DA262 ENG.; G262 ENG.		
Fan & Gen.; W/46 1/4" Belt O.C.	235353	9463 ^{GS}
Fan & Gen.; W/48 1/4" Belt O.C.	227470	9480 ^{GS}
P.S.....	235394	9375 ^{GS}
D21; D21D		
3400 DIESEL ENG.; 3500 DIESEL ENG.		
Fan & Alt.; Ser. No. 4445 & Be- fore.....	240595	②9580 ^{GS}
Fan & Alt.; Ser. No. 4446 & Af- ter.....	254350	9560 ^{GS}
G		
CONTINENTAL N62 ENG.		
Fan & Gen.....	800116	TR22416 ^{GS}
H3; HD3		
D175 DIESEL ENG.		
Fan & Gen.....	233490	②9420 ^{GS}
G149 GAS ENG.		
Fan & Gen.....	233432	7380
H4; HD4		
Fan & Alt.; W/45 3/4" Belt O.C....	237048	9455 ^{GS}
Fan & Alt.; W/67 1/4" Belt O.C....	245120	9670 ^{GS}
HD5; HD5A; HD5B; HD5D; HD5E; HD5F; HD5G		
Fan & Gen.; Std.....	033138	②TR22625 ^{GS}
Fan & Gen.; Slow Speed.....	074293	②9625 ^{GS}
HD6; HD6A; HD6B; HD6E; HD6G		
HD344 ENG.; 6000 ENG.		
Fan; Ser. No. 6-10368 & Before; Ser. No. 13321.....	4348910	②TR28596 ^{GS}
Fan; Ser. No. 6-10369; Ser. No. 13322 & After.....	4349777	②TR28483 ^{GS}
W.P. & Gen.; Ser. No. 6-10368 & Before.....	4348851	TR28514 ^{GS}
W.P. & Gen.; Ser. No. 6-10369 & After.....	4349729	TR22485 ^{GS}

- | | | | |
|-------------------|------------------|--------------------------------------|--|
| ② Two Required. | ⑤ Five Required. | ▲ Durion® Silicone Hose Recommended. | ✦ Green Stripe® 4-Ply Coolant Hose Recommended. |
| ③ Three Required. | ⑥ Six Required. | ✦ Use Notched Belt Only. | ✦ Use Wire Inserted Green Stripe® Coolant Hose. |
| ④ Four Required. | ✂ Cut To Fit. | GS Green Stripe® Construction. | ✦ Green Stripe II Straight Coolant Hose Recommended. |

For a maintenance free coolant connection, see PowerGrip® SB clamp application section.

Belts and Coolant Hose for Farm Tractors and Farm Equipment (1969 And Older)

ALLIS-CHALMERS; See Deutz-Allis Also - Continued

Belts - Continued

Application	Mfr. Part No.	Belt No.
HD6; HD6A; HD6B; HD6E; HD6G - Continued		
HD344 ENG.; 6000 ENG. - Continued		
W.P. & Gen.; Ser. No. 13322 & After.....	4349728	TR22514 GS
HD6EP; HD7G		
6000 DIESEL ENG.; 7000 DIESEL ENG.		
Fan.....	4337756	②TR28514 GS
W.P. & Gen.....	4337725	TR22525 GS
HD7; HD7W; HD8		
DETROIT DIESEL 3-71 ENG.; DETROIT DIESEL 4-71 ENG.; DETROIT DIESEL 6-71 ENG.		
Fan.....	602944	②TR22578 GS
Gen.....	040549	TR20451 GS
HD9		
DETROIT DIESEL 4-71 ENG.		
Fan.....	033138	②TR22625 GS
Gen.; Ser. No. 3270 & Before.....	079582	TR22405 GS
Gen.; Ser. No. 3271 & After.....	040549	TR20451 GS
HD10; HD10W; HD14		
DETROIT DIESEL 4-71 ENG.; DETROIT DIESEL 6-71 ENG.		
Fan.....	602944	②TR22578 GS
Gen.....	040549	TR20451 GS
HD11; HD11B; HD11E; HD11ES; HD11EP; HD11F; HD11S		
HD516 ENG.; 6000 ENG.; 10000 ENG.; 11000 ENG.		
Fan; Ser. No. 11-4854 & Before.....	4335452	②TR28649 GS
Fan; Ser. No. 11-4855 & After.....	4349778	②TR28522 GS
Fan; Ser. No. 13322 & After.....	4337757	②TR28545 GS
W.P. & Gen.; Ser. No. 11-4855 & After.....	4349728	TR22514 GS
W.P. & Gen.; Ser. No. 13322 & After.....	4338212	TR22534 GS
HD11G		
HD516 ENG.; 6000 ENG.; 10000 ENG.; 11000 ENG.		
Fan; Ser. No. 11-4854 & Before.....	4335452	②TR28649 GS
Fan; Ser. No. 11-4855 & After.....	4349778	②TR28522 GS
Fan; Ser. No. 13322 & After.....	4337757	②TR28545 GS
W.P. & Gen.; Ser. No. 89498 & Before.....	4335446	TR28550 GS
W.P. & Gen.; Ser. No. 89499 Thru 11-4854.....	4347817	TR28550 GS
W.P. & Gen.; Ser. No. 11-4855 & After.....	4349728	TR22514 GS
W.P. & Gen.; Ser. No. 13322 & After.....	4338212	TR22534 GS
HD11EC; HD11FC; HD11GS		
10000 ENG.		
Fan; Ser. No. 11-4854 & Before.....	4335412	②TR28545 GS
W.P. & Gen.; Ser. No. 11-4854 & Before.....	4335446	TR28550 GS
HD14C		
Gen.....	602944	TR22578 GS
HD15; HD15A; HD15AC; HD15C; HD15F; HD15FC; HD15G; HD15GC		
DETROIT DIESEL 6-71 ENG.		
Fan; W/O Torque Converter.....	069704	②B81
Gen.; W/Torque Converter.....	076750	TR22588 GS
Gen.; W/O Torque Converter.....	602944	TR22578 GS
HD16; HD16A; HD16AC; HD16B; HD16D; HD16DC; HD16DP; HD16FC		
HD844 ENG.; 16000 ENG.		
Fan & Gen.....	086979	②CX81
W.P.....	4386813	TR22495 GS
1700 MK II ENG.		
W.P.....		9500 GS
HD16GC		
HD844 ENG.; 16000 ENG.		
W.P.....	4386813	TR22495 GS
1700 MK II ENG.		
W.P.....		9500 GS

ALLIS-CHALMERS; See Deutz-Allis Also - Continued

Belts - Continued

Application	Mfr. Part No.	Belt No.
HD19; HD19F; HD19G; HD19H		
DETROIT DIESEL ENG.		
Fan; Ser. No. 1802 & After.....	067529	②CX81
Gen.....	602944	TR22578 GS
HD20G		
DETROIT DIESEL 6-110 ENG.		
Fan & Gen.....	067529	②CX81
HD21; HD21A; HD21AC; HD21F; HD21P		
6DA844 ENG.; 21000 ENG.		
Fan; Ser. No. 9001 & Before.....	067529	②CX81
W.P.....	4386813	TR22495 GS
Gen.....	082879	9530 GS
HD21G		
6DA844 ENG.; 21000 ENG.		
W.P.....	694929	TR22485 GS
Gen.....	082879	9530 GS
HD41 CRAWLER		
CUMMINS VT1710C ENG.		
Fan.....	673606	③CX81
W.P.....	178665	②TR28390 GS
Alt.; W/36 3/8" Belt O.C.....	663945	TR22358 GS
Alt.; W/39 1/8" Belt O.C.....		TR22386 GS
IB		
Fan.....	207003	TR22322 GS
Fan & Gen.....	209656	TR22373 GS
I 40; I 400		
G149 GAS ENG.		
Fan & Gen.....	233432	7380
I 60; I 600		
G160 GAS ENG.		
Fan & Gen.....	233432	7380
D175 DIESEL ENG.		
Fan & Gen.....	233489	②9420 GS
U; UC; UM		
Fan.....	U2754	TR28514 GS
Gen.; W/2 1/2" Dia. Pulley.....	212336	2240
Gen.; W/3 5/8" Dia. Pulley.....	U424	9260 GS
W; WC; WD; WF; WK		
Fan.....	203073	TR22416 GS
Fan & Gen.....	209824	TR22461 GS
WD45		
DIESEL ENG.		
Fan & Gen.; Ser. No. 77855 & Before.....	226935	9476 GS
Fan & Gen.; Ser. No. 77856 & After.....	227470	9480 GS
P.S.....	227398	9590 GS
GAS ENG.		
Fan & Gen.....	209824	TR22461 GS
P.S.....	227398	9590 GS
170D		
G226 GAS ENG.		
Fan & Alt.....	248316	9470 GS
PERKINS 4.236 DIESEL ENG.		
Fan & Alt.....	227470	9480 GS
650 CRAWLER; 652 CRAWLER; 653 CRAWLER; 655 CRAWLER		
2200 DIESEL ENG.		
W.P.....	237048	9455 GS
Alt.....	245120	9670 GS
708C		
ALLIS-CHALMERS 4.236 DIESEL ENG.		
Fan & Alt.; W/55A. Alt.....		9520 GS
8580		
6120T ENG.		
Fan.....	259566	②TR28616 GS
W.P.....	4395701	7465
Alt.....	259401	TR22517 GS
A.C.; Ser. No. 1635 & Before.....	259363	9451 GS
A.C.; Ser. No. 1636 & After.....	256935	9480 GS

② Two Required.
③ Three Required.
④ Four Required.

⑤ Five Required.
⑥ Six Required.
✂ Cut To Fit.

▲ Durion® Silicone Hose Recommended.
✦ Use Notched Belt Only.
GS Green Stripe® Construction.

✦ Green Stripe® 4-Ply Coolant Hose Recommended.
✧ Use Wire Inserted Green Stripe® Coolant Hose.
* Green Stripe II Straight Coolant Hose Recommended.

For a maintenance free coolant connection, see PowerGrip® SB clamp application section.

Belts and Coolant Hose for Farm Tractors and Farm Equipment (1969 And Older)

ALLIS-CHALMERS; See Deutz-Allis Also - Continued

Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
B; C		
Upper	1 1/4" I.D.	
Lower	1 1/4" I.D.	
CA		
Upper	1 1/4" I.D.	
Lower	② 1 1/4" I.D.	
D10; D12		
10 ENG.; 138 ENG.; 149 ENG.		
Upper	×20563	
Lower	② 1 1/4" I.D.	
By Pass	④ 5/8" I.D.	
D14		
Upper	×21942	25249
Lower	② 1 1/4" I.D.	
By Pass	④ 5/8" I.D.	
D15D		
D175 DIESEL ENG.		
Upper	1 1/2" I.D.	
Lower	×20267	
D15G		
149 GAS ENG.		
Upper	×20661	25251
160 GAS ENG.		
Upper	×20661	25251
Lower	25252	
By Pass	④ 5/8" I.D.	
D17D		
DA262 DIESEL ENG.		
Upper; Ser. No. 38964 & Before	② 1 3/4" I.D.	
Upper; Ser. No. 38965 & After	26502	
Lower; Ser. No. 38964 & Before	1 1/2" I.D.	
Lower; Ser. No. 38965 & After	×20559	25528(A)
By Pass	1" I.D.	
D17G		
Upper	×20088	25474
Lower	×21794	25476(A,B)
By Pass	④ 3/4" I.D.	
D17 SERIES IV		
DIESEL ENG.		
Upper	26502	
Lower	×20559	25528(A)
GAS ENG.		
Upper	×20088	25474
Lower	×21794	25476(A,B)
By Pass	④ 3/4" I.D.	
D19		
262 DIESEL ENG.		
Upper	26502	
262 GAS ENG.		
Upper	26502	
Lower	×20559	25528(A)
D21		
426 ENG.; 3400 ENG.; 3500 ENG.		
Upper	26511	
Lower	26508	
By Pass	25257	
G		
N62 ENG.		
Upper	1 1/2" I.D.	
Lower	1 1/2" I.D.	
H3		
G149 GAS ENG.		
Upper	×20661	
HD3		
D175 DIESEL ENG.		
Upper	② 1 1/2" I.D.	
Lower	② 1 1/2" I.D.	
HD5; HD5A; HD5B; HD5E; HD5F; HD5G		
Upper	1 1/2" I.D.	

ALLIS-CHALMERS; See Deutz-Allis Also - Continued

Coolant Hose - Continued

Application	Molded or Strt.	Vulco-Flex®
HD5; HD5A; HD5B; HD5E; HD5F; HD5G - Continued		
Lower	② 1 3/4" I.D.	
HD6		
Upper	2" I.D.	
Lower	23550	
HD6; HD6A; HD6B; HD6E; HD6G		
Upper	23547	
Lower	23550	
By Pass	1 7/8" I.D.	
HD6EP; HD7G		
6000 DIESEL ENG.; 7000 DIESEL ENG.		
Upper	23547	
Lower	④ 2 1/2" I.D.	
HD9		
DETROIT DIESEL 4-71 ENG.		
Upper	2" I.D.	
Lower	2" I.D.	
By Pass	1" I.D.	
HD10; HD10W		
Upper	2" I.D.	
Upper	2 1/4" I.D.	
Lower	2 1/4" I.D.	
HD11		
HD516 ENG.		
Upper	2 1/4" I.D.	
Lower	2 1/2" I.D.	
HD11; HD11B; HD11E; HD11EC; HD11EP; HD11ES; HD11F; HD11FC; HD11G; HD11GE; HD11S		
HD516 ENG.; 10000 ENG.; 11000 ENG.		
Upper; Ser. No. 6426 & Before	④ 2 1/8" I.D.	
Upper; Ser. No. 6427 & After	23547	
Lower	2 1/2" I.D.	
HD15; HD15A; HD15AC; HD15C; HD15F; HD15FC; HD15G; HD15GC		
BUDA HD844 ENG.		
Upper	3" I.D.	
Lower	2 1/2" I.D.	
DETROIT DIESEL ENG.		
Upper	② 2 1/4" I.D.	
Lower	2 1/4" I.D.	
HD16; HD16A; HD16AC; HD16B; HD16D; HD16DC; HD16DP; HD16FC; HD16GC		
HD844 ENG.; 16000 ENG.; M1700 MK II ENG.		
Upper; Ser. No. 5901 & After	② 2 3/4" I.D.	
Lower; Ser. No. 5901 & After	② 2 1/2" I.D.	
By Pass	1 5/8" I.D.	
HD19; HD19F; HD19G; HD19G; HD19H		
Upper; Ser. No. 1801 & Before	② 2 1/4" I.D.	
Upper; Ser. No. 1802 & After	2 1/4" I.D.	
Lower	2 1/4" I.D.	
HD20F; HD20G; HD20H		
DETROIT DIESEL 6-110 ENG.		
Upper	2 3/4" I.D.	
Lower; Std. Models	② 2 3/4" I.D.	
Lower; W/Torque Converter	2 3/4" I.D.	
By Pass	1 1/4" I.D.	
HD21		
BUDA 6DA844 ENG.		
Upper	② 3" I.D.	
Lower	2 1/2" I.D.	
HD21; HD21A; HD21AC; HD21B; HD21F; HD21G; HD21P		
Upper	2 3/4" I.D.	
Lower	② 2 1/2" I.D.	
HD41 CRAWLER		
CUMMINS VT1710C ENG.		
Upper - Eng. To Pipe	② ④ 3" I.D.	
Upper - Pipe To Rad	② ④ 3" I.D.	
Lower - Eng. To Pipe	② ④ 3 1/2" I.D.	
Lower - Pipe To Rad	② ④ 3 1/2" I.D.	

- | | | | |
|-------------------|------------------|--------------------------------------|--|
| ② Two Required. | ⑤ Five Required. | ▲ Durion® Silicone Hose Recommended. | ✦ Green Stripe® 4-Ply Coolant Hose Recommended. |
| ③ Three Required. | ⑥ Six Required. | ✦ Use Notched Belt Only. | ④ Use Wire Inserted Green Stripe® Coolant Hose. |
| ④ Four Required. | × Cut To Fit. | GS Green Stripe® Construction. | * Green Stripe II Straight Coolant Hose Recommended. |

For a maintenance free coolant connection, see PowerGrip® SB clamp application section.

Belts and Coolant Hose for Farm Tractors and Farm Equipment (1969 And Older)

ALLIS-CHALMERS; See Deutz-Allis Also - Continued

Coolant Hose - Continued

Application	Molded or Strt.	Vulco-Flex®
IB		
Upper	1 1/4" I.D.	
Lower	②1 1/4" I.D.	
I 40; I 400		
149 GAS ENG.		
Upper	>20563	
Lower	②1 1/2" I.D.	
I 60; I 600		
D175 DIESEL ENG.		
Upper	1 1/2" I.D.	
Lower	>20267	
Lower	1 1/2" I.D.	
G160 GAS ENG.		
Upper	>20661	25251(A,B)
U; UC; UM		
Upper	2" I.D.	
Lower	2" I.D.	
W; WC; WD; WF; WK		
Upper	1 1/2" I.D.	
Lower	1 1/2" I.D.	
WD45		
DIESEL ENG.		
Upper	②1 3/4" I.D.	
Lower	1 1/2" I.D.	
GAS ENG.		
Upper	1 1/2" I.D.	
Lower	1 1/2" I.D.	
180D		
DIESEL ENG.; GAS ENG.		
Upper	21256	26504
Lower		26504
650 CRAWLER; 652 CRAWLER; 653 CRAWLER; 655 CRAWLER		
2200 DIESEL ENG.		
Upper	>20520	
708C		
ALLIS-CHALMERS 4.236 DIESEL ENG.		
Upper		26519
840B		
2800 ENG.		
Upper	>20611	26511
918		
Upper	21256	26504
Lower		26504

Farm Equipment Belts

Application	Mfr. Part No.	Belt No.
A2 COMBINE; B COMBINE; R COMBINE		
D262 DIESEL ENG.		
Fan & Gen.; Eng. Ser. No. 122475 & Before.....	4510744	9470 GS
Hyd. Pump; Ser. No. 14053 Thru 26500.....	1117027	TR28483 GS
Hyd. Pump; Ser. No. 26501 Thru 30000.....	1128092	TR28463 GS
HERCULES ENG.		
Fan; Ser. No. 14052 & Before	1117027	TR28483 GS
Hyd. Pump; Ser. No. 13500 & Before.....	1117040	TR28545 GS
Hyd. Pump; Ser. No. 13501 Thru 14052.....	1117027	TR28483 GS
G230 GAS ENG.		
Fan & Gen.; Eng. Ser. No. 397016 & Before.....	4510744	9470 GS
Fan & Gen.; Eng. Ser. No. 397017 Thru 408560.....	4512419	9480 GS

ALLIS-CHALMERS; See Deutz-Allis Also - Continued

Belts - Continued

Application	Mfr. Part No.	Belt No.
A2 COMBINE; B COMBINE; R COMBINE - Continued		
G230 GAS ENG. - Continued		
Hyd. Pump; Ser. No. 14053 Thru 26500.....	1117027	TR28483 GS
Hyd. Pump; Ser. No. 26501 Thru 30000.....	1128092	TR28463 GS
GLEANER C COMBINE; GLEANER CR COMBINE		
D262 ENG.; G262 ENG.		
Fan & Gen.; Ser. No. 7001 & After.....	4512419	9480 GS
Hyd. Pump.....	1125973	TR28454 GS
GLEANER CH COMBINE		
D262 ENG.; G262 ENG.		
Fan & Gen.; Ser. No. 7001 & After.....	4512419	9480 GS
Hyd. Pump.....	1134651	TR28429 GS
GLEANER C2 COMBINE		
D262 ENG.; G262 ENG.		
Fan & Gen.; Ser. No. 7001 & After.....	4512419	9480 GS
GLEANER E COMBINE		
G226 ENG.		
Fan.....	229211	9463 GS
Hyd. Pump; W/O P.S.....	1130921	9447 GS
Hyd. Pump; W/P.S.....	1131774	9425 GS
GLEANER E3 COMBINE		
A.C.; W/Comfort Cab; Ser. No. 5000 & Before.....	1142239	9451 GS
A.C.; W/Comfort Cab; Ser. No. 5001 Thru 8200.....	1152788	9480 GS
A.C.; W/LaPort Cab.....	1166813	9490 GS
Hyd. Pump; W/O P.S.....	1130921	9447 GS
Hyd. Pump; W/P.S.....	1131774	9425 GS
GLEANER F COMBINE		
DIESEL ENG.		
Alt./Gen.; Ser. No. 5000 & Before.....		9540 GS
Alt./Gen.; Ser. No. 5001 Thru 12200.....	1140911	9490 GS
Alt./Gen.; Ser. No. 12201 & After.....	1154358	9540 GS
A.C.; Ser. No. 12200 & Before....	1142239	9451 GS
A.C.; Ser. No. 12201 & After.....	1139187	9490 GS
Gov.; Ser. No. 12201 & After.....	1148120	9510 GS
Hyd. Pump; Ser. No. 5000 & Before.....	1133220	TR28483 GS
Hyd. Pump; Ser. No. 25800 & Before.....	1152608	TR28445 GS
Hyd. Pump; Ser. No. 25801 & After.....	1193749	TR28429 GS
GAS ENG.		
Alt./Gen.; Ser. No. 5000 & Before.....		9540 GS
Alt./Gen.; Ser. No. 5001 Thru 12200.....	1140911	9490 GS
Alt./Gen.; Ser. No. 12201 & After.....	1148119	9395 GS
A.C.; Ser. No. 12200 & Before....	1142239	9451 GS
A.C.; Ser. No. 12201 & After.....	1139187	9490 GS
Gov.; Ser. No. 12201 & After.....	1148120	9510 GS
Hyd. Pump; Ser. No. 5000 & Before.....	1133220	TR28483 GS
Hyd. Pump; Ser. No. 12201 Thru 25800.....	1167408	9590 GS
Hyd. Pump; Ser. No. 25801 & After.....	1167410	9395 GS
GLEANER G COMBINE; GLEANER GH COMBINE		
DIESEL ENG.		
Fan & Alt.; Ser. No. 17000 & Before.....	1154797	9570 GS
Fan & Alt.; Ser. No. 17001 Thru 21000.....	1167004	9580 GS
Fan & Alt.; Ser. No. 21001 & After.....	1172696	②9570 GS
A.C.; Ser. No. 12200 & Before....	1142239	9451 GS

- ② Two Required.
- ③ Three Required.
- ④ Four Required.

- ⑤ Five Required.
- ⑥ Six Required.
- > Cut To Fit.

- ▲ Durion® Silicone Hose Recommended.
- ✦ Use Notched Belt Only.
- GS Green Stripe® Construction.

- ✦ Green Stripe® 4-Ply Coolant Hose Recommended.
- ② Use Wire Inserted Green Stripe® Coolant Hose.
- * Green Stripe II Straight Coolant Hose Recommended.

For a maintenance free coolant connection, see PowerGrip® SB clamp application section.

Belts and Coolant Hose for Farm Tractors and Farm Equipment (1969 And Older)

ALLIS-CHALMERS; See Deutz-Allis Also - Continued

Belts - Continued

Application	Mfr. Part No.	Belt No.
GLEANER G COMBINE; GLEANER GH COMBINE - Continued		
DIESEL ENG. - Continued		
A.C.; Ser. No. 12201 Thru 17000.....	1152788	9480 ^{GS}
A.C.; Ser. No. 17001 & After.....	166813	9490 ^{GS}
Gov.	1164565	7520
Hyd. Pump; W/43 3/8" Belt O.C. .	1172514	TR28429 ^{GS}
Hyd. Pump; W/54 1/4" Belt O.C. .	1154358	9540 ^{GS}
GAS ENG.		
Fan & Alt.; Ser. No. 17000 & Before.....	1139187	9530 ^{GS}
Fan & Alt.; Ser. No. 17001 & After.....	1165501	②7535
A.C.; Ser. No. 12200 & Before....	1142239	9451 ^{GS}
A.C.; Ser. No. 12201 Thru 17000.....	1152788	9480 ^{GS}
A.C.; Ser. No. 17001 & After.....	1166813	9490 ^{GS}
Gov.	1164565	7520
Hyd. Pump; Ser. No. 21000 & Before.....	1146714	9540 ^{GS}
Hyd. Pump; Ser. No. 21001 & After.....		9405 ^{GS}
GLEANER K COMBINE		
DIESEL ENG.		
Fan & Alt.	1139187	9530 ^{GS}
A.C.; W/52 1/4" Belt O.C.		9520 ^{GS}
Hyd. Pump; Ser. No. 25200 & Before.....	1146714	9405 ^{GS}
Hyd. Pump; Ser. No. 25201 & After.....	1300400	9415 ^{GS}
GAS ENG.		
Fan & Alt.	1146660	7400
A.C.; Ser. No. 5000 & Before.....	1142239	9451 ^{GS}
A.C.; Ser. No. 5001 Thru 12200.	1152788	9480 ^{GS}
A.C.; Ser. No. 12001 & After.....	1166813	9490 ^{GS}
Hyd. Pump; W/O P.S.; Ser. No. 1200 & Before.....	1152615	9660 ^{GS}
Hyd. Pump; W/O P.S.; Ser. No. 12001 & After.....	1142239	9451 ^{GS}
Hyd. Pump; W/P.S.; Ser. No. 12200 & Before.....	1146713	9620 ^{GS}
Hyd. Pump; W/P.S.; Ser. No. 12201 & After.....	1166813	9490 ^{GS}
GLEANER L COMBINE		
D2900 ENG.		
Fan & Alt.; Ser. No. 4200 & Before.....	1172696	9570 ^{GS}
Fan & Alt.; Ser. No. 4201 & After.....	1159298	9580 ^{GS}
Fan & Alt.; Dual Alt.; Upper.....	1167004	9580 ^{GS}
Fan & Alt.; Dual Alt.; Lower.....	1184327	9625 ^{GS}
Hyd. Pump.....	1173232	9640 ^{GS}
D3500 ENG.		
Fan & Alt.; Dual Alt.; Lower.....	1184961	②TR22692 ^{GS}
A.C.	1166813	9490 ^{GS}
Hyd. Pump.....		9620 ^{GS}
GAS ENG.		
Fan & Alt.; Ser. No. 2600 & Before.....	1175751	②7550
Fan & Alt.; Ser. No. 2601 & After.....	1165501	7535
Hyd. Pump; W/62 1/4" Belt O.C. .		9620 ^{GS}
Hyd. Pump; W/68 1/4" Belt O.C. .	1172977	9680 ^{GS}
GLEANER M COMBINE		
D2900 MKI ENG.; D2900 MKII ENG.		
Fan & Alt.; Dual Alt.; Upper.....	1167004	9580 ^{GS}
Fan & Alt.; Dual Alt.; Lower.....	1184327	9625 ^{GS}
Fan & Alt.; W/Single Alt.; Ser. No. 4201 & After.....	1159298	②9580 ^{GS}
A.C.	1166813	9490 ^{GS}
GAS ENG.		
Fan & Alt.	1165501	7535

ALLIS-CHALMERS; See Deutz-Allis Also - Continued

Belts - Continued

Application	Mfr. Part No.	Belt No.
TWO ROW COTTON PICKER; MODEL 500 COTTON PICKER		
GAS ENG.		
Fan.....	229211	9463 ^{GS}
DIESEL ENG.		
Fan.....	229559	9455 ^{GS}
60 COMBINE		
B125 ENG.		
Fan.....	207003	TR22322 ^{GS}
Fan & Gen.....	209656	TR22363 ^{GS}

Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
A2 COMBINE; B COMBINE; R COMBINE		
D262 ENG.; G262 ENG.		
Upper.....		26611
Lower; Ser. No. 26000 & Before.....		26611
Lower; Ser. No. 26001 & After.....		26612
HERCULES ENG.		
Upper.....		25528
Lower.....		25477
C COMBINE; CH COMBINE; CR COMBINE		
D262 ENG.; G262 ENG.		
Upper; W/26 3/8" Rad.....		26611
Upper; W/31 3/8" Rad.....		26612
Lower.....		26612
GLEANER E COMBINE; GLEANER E3 COMBINE		
G226 ENG.		
Upper.....		25476
Lower.....		25477
By Pass.....	×21942	
GLEANER F COMBINE		
6-CYL. 301 DIESEL ENG.		
Upper.....	21256	
Lower.....		26504
6-CYL. 292 GAS ENG.; 6-CYL. 292 LPG ENG.		
Upper; Ser. No. 12201 & After.....	20433	25526
Lower; Ser. No. 12200 & Before.....		26612
Lower; Ser. No. 12201 & After.....	20584	26612
By Pass.....	20563	
GLEANER G COMBINE		
6-CYL. 301 DIESEL ENG.		
Upper; Ser. No. 12200 & Before.....	21256	25527
Upper; Ser. No. 12201 & After.....	20595	26505
Lower.....		26504
6-CYL. GAS ENG.		
Upper; Early.....		26504
Upper; Late.....		25532
Lower; Early.....		26501
Lower; Late.....		26612
V-8 350 GAS ENG.		
Upper.....		25530
GLEANER L COMBINE		
D3500 ENG.		
Lower.....	21194	26521
GAS ENG.		
By Pass.....	20566	
GLEANER M COMBINE		
D2900 MKI GAS ENG.		
Lower; W/Hydro-Drive; Ser. No. 7401 & After.....		26506
By Pass.....	20566	
D2900 MKII GAS ENG.		
By Pass.....	20566	
TWO ROW COTTON PICKER		
GAS ENG.		
Upper.....	1 1/2" I.D.	
Lower.....	1 1/2" I.D.	

- ② Two Required.
- ③ Three Required.
- ④ Four Required.
- ⑤ Five Required.
- ⑥ Six Required.
- × Cut To Fit.
- ▲ Durion® Silicone Hose Recommended.
- ✦ Use Notched Belt Only.
- GS Green Stripe® Construction.
- ✦ Green Stripe® 4-Ply Coolant Hose Recommended.
- ✦ Use Wire Inserted Green Stripe® Coolant Hose.
- * Green Stripe II Straight Coolant Hose Recommended.

For a maintenance free coolant connection, see PowerGrip® SB clamp application section.

Belts and Coolant Hose for Farm Tractors and Farm Equipment (1969 And Older)

ALLIS-CHALMERS; See Deutz-Allis

Also - Continued

Coolant Hose - Continued

Application	Molded or Strt.	Vulco-Flex®
450 HAY LIFT		
INTERNATIONAL/NAVISTAR 6-CYL. ENG.		
Upper		26511
Lower		26515
500 COTTON PICKER		
GAS ENG.		
Upper; Early.....	>20088	25474
Lower; Early.....	>21794	25476(A,B)
500SP HAY LIFT		
DETROIT DIESEL 3-53 ENG.		
Upper		26611
Lower	②>20367	
FORD 6-CYL. 300 ENG.		
Upper		25530
Lower		26505

AMERICAN HAYMASTER

Farm Equipment Belts

Application	Mfr. Part No.	Belt No.
450 HAYSTACKER		
INTERNATIONAL/NAVISTAR 6-CYL. GAS ENG.		
Fan.....		9451 ^{GS}
Gen. & W.P.....		9440 ^{GS}
500SP HAYSTACKER		
DETROIT DIESEL 3-71 ENG.		
Fan.....	5172384	②9470 ^{GS}
Alt. & W.P.....	5133172	②6596
540SP HAYSTACKER		
FORD 6-CYL. 300 ENG.		
Fan.....	JC460	9455 ^{GS}
W.P. & Alt.....	JB420	7417

ANTONIO CARRARO

Tractors Belts

Application	Mfr. Part No.	Belt No.
BITRAC HS		
MAK2-CYL. DIESEL ENG.		
Fan & Alt.		7375
5500; 7500; 7700		
49 H.P. ENG.; 64 H.P. ENG.		
Fan & Alt.		7385
7700; 8008		
4-CYL. DIESEL ENG.		
Fan & Alt.	46510578A	7380

Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
BITRAC HS		
MAK2-CYL. DIESEL ENG.		
Upper - Eng. To Thermostat.....	>20065	
Lower		25252

BIG BUD

Tractors Belts

Application	Mfr. Part No.	Belt No.
450/50; 525/50		
CUMMINS KT450 ENG.; CUMMINS KTA1150 ENG.		
Alt.....	206996	K050370 ^{GS}
A.C.....		9600 ^{GS}

Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
450/50; 525/50		
CUMMINS KT450 ENG.; CUMMINS KTA1150 ENG.		
Lower - Eng. To Pipe.....	✦3 1/2" I.D.	

BLUE

Tractors Belts

Application	Mfr. Part No.	Belt No.
G1000		
4-CYL. GAS ENG.		
Fan & Alt.		7425
W.P. & Idler.....		②7425

Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
G1000		
Upper	2" I.D.	
Lower	1 1/2" I.D.	

BOLENS

Tractors Belts

Application	Mfr. Part No.	Belt No.
G152; G154; G174		
MITSUBISHI KE70 ENG.		
Fan & Alt.	1873737	7350
G192; G194		
MITSUBISHI KE75 ENG.		
Fan & Alt.	1876225	9385 ^{GS}
G242; G244		
ISUZU 2AB1 ENG.		
Fan & Alt.	1876226	9385 ^{GS}

BOURGOIN

Farm Equipment Belts

Application	Mfr. Part No.	Belt No.
GX406 CORN PICKER		
PERKINS 4-CYL. DIESEL ENG.		
Fan & Alt.	2614B570	②9660 ^{GS}

Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
GX406 CORN PICKER		
PERKINS 4-CYL. DIESEL ENG.		
Upper - Eng. To Pipe.....	>20206	
Upper - Pipe To Rad.	✦2" I.D.	

- ② Two Required.
- ③ Three Required.
- ④ Four Required.
- ⑤ Five Required.
- ⑥ Six Required.
- > Cut To Fit.
- ▲ Durion® Silicone Hose Recommended.
- ✦ Use Notched Belt Only.
- ^{GS} Green Stripe® Construction.
- ✦ Green Stripe® 4-Ply Coolant Hose Recommended.
- ② Use Wire Inserted Green Stripe® Coolant Hose.
- * Green Stripe II Straight Coolant Hose Recommended.

For a maintenance free coolant connection, see PowerGrip® SB clamp application section.