

Belts and Coolant Hose for Farm Tractors and Farm Equipment Alphabetical Listing (1970 And Newer)

If you cannot locate the application, refer to the
Manufacturers' Part Number or Competitive Changeover
Listing in the 31-2040 Catalog.

Order Belts and Hose by Gates Number. Manufacturers'
Part Number is shown for reference only.

ALLIS-CHALMERS

Tractors Belts

Application	Mfr. Part No.	Belt No.
160		
PERKINS 4.152 DIESEL ENG.		
Fan & Gen.; W/48 1/4" Belt O.C.	2080291	9480 GS
Fan & Gen.; W/50 1/4" Belt O.C.	2074320	9500 GS
P.S.	2073746	9290 GS
170; 175		
G226 GAS ENG.		
Fan & Alt.	248316	9470 GS
PERKINS 4.236 DIESEL ENG.		
Fan & Alt.	227470	9480 GS
180		
AC 265 GAS ENG.; AC 301 DIESEL ENG.		
Fan & Alt.	243021	9530 GS
185		
AC 301 DIESEL ENG.		
Fan & Alt.	243021	9530 GS
190		
2500 GAS ENG.		
Fan & Alt.; Ser. No. 2G05728 & Before	243021	9530 GS
Fan & Alt.; Ser. No. 2G05729 & After	252145	9525 GS
A.C.	246618	9360 GS
2800 GAS ENG.		
Fan & Alt.	252145	9525 GS
A.C.	246618	9360 GS
2900 DIESEL ENG.		
Fan & Alt.; Ser. No. 2D25950 & Before	252145	9525 GS
Fan & Alt.; Ser. No. 2D25951 & After	255200	9510 GS
A.C.	246618	9360 GS
190XT		
2500 GAS ENG.		
Fan & Alt.; Ser. No. 2G05728 & Before	243021	9530 GS
Fan & Alt.; Ser. No. 2G05729 & After	252145	9525 GS
A.C.	246618	9360 GS
2800 GAS ENG.		
Fan & Alt.	252145	9525 GS
A.C.	246618	9360 GS
2900 DIESEL ENG.		
Fan & Alt.; Ser. No. 2D25950 & Before	252145	9525 GS
Fan & Alt.; Ser. No. 2D25951 & After	255200	9510 GS
A.C.	246618	9360 GS
200		
2900 DIESEL ENG.		
Fan & Alt.; W/52 3/4" Belt O.C....	256230	9525 GS
Fan & Alt.; W/53 1/4" Belt O.C....	256655	9530 GS

ALLIS-CHALMERS - Continued

Belts - Continued

Application	Mfr. Part No.	Belt No.
200 - Continued		
2900 DIESEL ENG. - Continued		
A.C.	256417	9720 GS
210		
3500 DIESEL ENG.		
Fan & Alt.	254351	9560 GS
A.C.; W/81 1/4" Belt O.C.		9810 GS
220		
3500 DIESEL ENG.		
Fan & Alt.	254351	9560 GS
A.C.; W/81 1/4" Belt O.C.		9810 GS
6040		
PERKINS 3.152 3-CYL. DIESEL ENG.		
Fan, Alt. & W.P.	229211	9463 GS
6060		
AC 200T 4-CYL. DIESEL ENG.		
Fan & Alt.	263408	9540 GS
A.C.; Ser. No. 4373 & Before	272411	9447 GS
A.C.; Ser. No. 3770 & After	562203	9440 GS
6070		
AC 200T 4-CYL. DIESEL ENG.		
Fan & Alt.	263408	9540 GS
A.C.	562203	9440 GS
6080		
AC 200T 4-CYL. DIESEL ENG.		
Fan & Alt.	263408	9540 GS
A.C.; Ser. No. 3769 & Before	272411	9447 GS
A.C.; Ser. No. 4374 & After	562203	9440 GS
7000		
AC 301T DIESEL ENG.		
Fan & Alt.	260328	9550 GS
A.C.; Ser. No. 8000 & Before	260149	9765 GS
A.C.; Ser. No. 8001 & After	268485	9530 GS
7010; 7020		
AC 301T 6-CYL. DIESEL ENG.		
Fan & Alt.		9570 GS
A.C.	260149	9765 GS
7030; 7040; 7045; 7050; 7060		
AC 426 6-CYL. DIESEL ENG.		
Fan & Alt.	267631	TR20619 GS
A.C.	268485	9530 GS
7080		
AC 670HI 6-CYL. DIESEL ENG.		
Fan & Alt.	269183	TR22607 GS
A.C.; Ser. No. 3828 & Before	268485	9530 GS
A.C.; Ser. No. 3829 & After	261802	9545 GS
8010		
AC 649T 6-CYL. DIESEL ENG.		
Fan & Alt.	254350	9560 GS
A.C.	260149	9765 GS

- ② Two Required.
- ③ Three Required.
- ④ Four Required.
- ⑤ Five Required.
- ⑥ Six Required.
- ✂ Cut To Fit.
- ▲ Durion® Silicone Hose Recommended.
- ✦ Use Notched Belt Only.
- GS Green Stripe® Construction.
- ✦ Green Stripe® 4-Ply Coolant Hose Recommended.
- ✦ Use Wire Inserted Green Stripe® Coolant Hose.
- ✦ Green Stripe II Straight Coolant Hose Recommended.

For a maintenance free coolant connection, see PowerGrip® SB clamp application section.

Belts and Coolant Hose for Farm Tractors and Farm Equipment (1970 And Newer)

ALLIS-CHALMERS - Continued

Belts - Continued

Application	Mfr. Part No.	Belt No.
8030		
AC 670T 6-CYL. DIESEL ENG.		
Fan & Alt.	273193	②TR22664 ^{GS}
A.C.; Ser. No. 1906 & Before.....	268485	9530 ^{GS}
A.C.; Ser. No. 1907 & After.....	273705	9505 ^{GS}
8050		
AC 670I 6-CYL. DIESEL ENG.		
Fan & Alt.	273193	②TR22664 ^{GS}
A.C.; Ser. No. 1836 & Before.....	268485	9530 ^{GS}
A.C.; Ser. No. 1837 & After.....	273705	9505 ^{GS}
8070		
AC 670I 6-CYL. DIESEL ENG.		
Fan & Alt.	273193	②TR22664 ^{GS}
A.C.; Ser. No. 1350 & Before.....	268485	9530 ^{GS}
A.C.; Ser. No. 1351 & After.....	273705	9505 ^{GS}

Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
170		
DIESEL ENG.		
Upper.....	1 3/4" I.D.	
Lower.....	>20993	25480
GAS ENG.		
Upper; Early.....		25477
Upper; Late.....		25482
Lower.....	20065	25473
By Pass.....	*3/4" I.D.	
175		
DIESEL ENG.		
Upper.....	1 3/4" I.D.	
Lower.....	>20993	25480
GAS ENG.		
Upper; Early.....		25477
Upper; Late.....		25482
Lower.....	20065	25473
By Pass.....	*3/4" I.D.	
180; 185		
DIESEL ENG.; GAS ENG.		
Upper.....	21256	26504
Lower.....		26504
190		
D2900 DIESEL ENG.; G2800 GAS ENG.		
Upper; Ser. No. 14450 & Before.....		26503
Upper; Ser. No. 14451 & After.....	21256	26504
Lower; Ser. No. 14450 & Before.....		26503
Lower; Ser. No. 14451 & After.....		26504
190XT		
D2900 DIESEL ENG.; G2800 GAS ENG.		
Upper; Ser. No. 14450 & Before.....		26503
Upper; Ser. No. 14451 & After.....	21256	26504
Lower; Ser. No. 14450 & Before.....		26503
Lower; Ser. No. 14451 & After.....		26504
200		
2900 DIESEL ENG.		
Upper.....	>21944	26505
210; 220		
3500 ENG.		
Upper; Early.....		26505
Upper; Late.....		26511
Lower; Early.....		26504
Lower; Late.....		26508
By Pass.....		25257
6040		
PERKINS 3.152 3-CYL. DIESEL ENG.		
Upper.....	>21174	25473
Lower.....	>20808	
By Pass.....	>20573	
6060		
Upper.....	>21379	26524

ALLIS-CHALMERS - Continued

Coolant Hose - Continued

Application	Molded or Strt.	Vulco-Flex®
7000		
AC 301T DIESEL ENG.		
Upper.....	20401	26525
By Pass.....	>21942	
7010		
AC 301T 6-CYL. DIESEL ENG.		
Upper.....	>20401	26524
Lower.....		26531
7030; 7040; 7045; 7050; 7060		
AC 426 6-CYL. DIESEL ENG.		
Upper.....	>20731	26523
Lower.....	2 1/4" I.D.	
By Pass.....	>20573	
7080		
AC 670HI 6-CYL. DIESEL ENG.		
Upper.....		26523
Lower.....	>20756	
By Pass.....	>20065	
8010		
AC 649T 6-CYL. DIESEL ENG.		
Upper.....		26528
By Pass.....	>20661	25251
8030		
AC 670T 6-CYL. DIESEL ENG.		
Upper.....		26527
Lower.....	♣2 1/2" I.D.	
By Pass.....	>20065	
8070		
AC 670I 6-CYL. DIESEL ENG.		
Upper.....	>21115	26527
8550		
AC 731T DIESEL ENG.		
Upper.....		26531
Lower.....		26532
By Pass.....	20351	

Tractors, Articulated

Belts

Application	Mfr. Part No.	Belt No.
4W220		
AC 6-CYL. DIESEL ENG.		
Fan & Alt.	273193	②TR22664 ^{GS}
A.C.	273705	9505 ^{GS}
4W305		
AC 6-CYL. DIESEL ENG.		
Fan.....	273419	②TR28628 ^{GS}
W.P.	4396941	7475
Alt.....	259401	TR22517 ^{GS}
A.C.	226935	9476 ^{GS}
440		
CUMMINS V-555 DIESEL ENG.		
Fan & W.P.....	204481	③9625 ^{GS}
Alt.....	178398	②7340
A.C.; W/40 3/4" Belt O.C.		9405 ^{GS}
A.C.; W/41 1/4" Belt O.C.		9412 ^{GS}
7580		
AC 670HI 6-CYL. DIESEL ENG.		
Fan & Alt.	269183	②TR22607 ^{GS}
A.C.; Ser. No. 2611 & Before.....	268485	9530 ^{GS}
A.C.; Ser. No. 2612 & After.....	261802	9545 ^{GS}
8550		
AC 731T DIESEL ENG.		
Fan.....	259566	②TR28616 ^{GS}
W.P.	4395701	7465
Alt.....	259401	TR22517 ^{GS}
A.C.; Ser. No. 1635 & Before.....	259363	9451 ^{GS}
A.C.; Ser. No. 1636 & After.....	256935	9480 ^{GS}

② Two Required. ⑤ Five Required. ▲ Durion® Silicone Hose Recommended. ♣ Green Stripe® 4-Ply Coolant Hose Recommended.
 ③ Three Required. ⑥ Six Required. ✦ Use Notched Belt Only. Ⓞ Use Wire Inserted Green Stripe® Coolant Hose.
 ④ Four Required. ✧ Cut To Fit. ^{GS} Green Stripe® Construction. * Green Stripe II Straight Coolant Hose Recommended.

For a maintenance free coolant connection, see PowerGrip® SB clamp application section.

Belts and Coolant Hose for Farm Tractors and Farm Equipment (1970 And Newer)

ALLIS-CHALMERS - Continued

Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
4W305		
6120T DIESEL ENG.		
Upper		26531
Lower		26532
440		
CUMMINS V-555 ENG.		
Upper	✱2" I.D.	
7580		
AC 670HI 6-CYL. DIESEL ENG.		
Upper	>21133	

Tractors, Compact Utility Belts

Application	Mfr. Part No.	Belt No.
5015		
HINO CS100 DIESEL ENG.		
Fan & Alt.	2100737	7380
5020		
TOYOSHA 2-CYL. DIESEL ENG.		
Fan & Alt.	2097654	9400 GS
5030		
TOYOSHA 2-CYL. DIESEL ENG.		
Fan & Alt.	2097654	9400 GS
5040		
UZINA D115 3-CYL. DIESEL ENG.		
Fan & Alt.	2091561	7450
5045		
FIAT 8035M 3-CYL. DIESEL ENG.		
Fan & Alt.; Ser. No. 700,000 & After	2091561	7450
5050		
FIAT 8035M 3-CYL. DIESEL ENG.		
Fan & Alt.; Ser. No. 700,000 & Before	2091544	7445
Fan & Alt.; Ser. No. 700,000 & After	2091561	7450
6140		
TOYOSHA 3-CYL. DIESEL ENG.		
Fan & Alt.		9440 GS

Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
5015		
HINO CS100 DIESEL ENG.		
Upper	20782	
5020		
TOYOSHA 2-CYL. DIESEL ENG.		
Upper - Eng. To Pipe.....	20065	25472
Lower - Eng. To Pipe.....		25252
5030		
TOYOSHA 2-CYL. DIESEL ENG.		
Upper		25473
Lower		25252
5045		
FIAT 8035 3-CYL. ENG.		
Upper	>21794	25477
Lower - Eng. To Pipe.....	1 1/2" I.D.	
Lower - Pipe To Rad.	1 1/2" I.D.	
5050		
FIAT 8035 3-CYL. ENG.		
Lower - Eng. To Pipe.....	1 1/2" I.D.	
Lower - Pipe To Rad.	1 1/2" I.D.	
6140		
TOYOSHA 3-CYL. DIESEL ENG.		
Upper	>21794	25474

ALLIS-CHALMERS - Continued

Farm Equipment, Cotton Picker

Belts

Application	Mfr. Part No.	Belt No.
616		
DIESEL ENG.		
Fan; Ser. No. 250 & Before.....	229559	②9455 GS
Fan; Ser. No. 251 & After	227470	9480 GS
P.S.	826215	9425 GS
GAS ENG.		
Fan; Ser. No. 68068 & Before	229211	9463 GS
Fan; Ser. No. 68069 & After	237048	9455 GS
P.S.	826215	9425 GS
622		
GAS ENG.		
Fan; Ser. No. 68068 & Before	229211	9463 GS
Fan; Ser. No. 68069 & After	237048	9455 GS
P.S.	826215	9425 GS
DIESEL ENG.		
Fan; Ser. No. 351 & Before.....	229559	②9455 GS
Fan; Ser. No. 352 & After	227470	9480 GS
P.S.	826215	9425 GS
801; 802		
GAS ENG.		
Fan; Ser. No. 68068 & Before	229211	9463 GS
Fan; Ser. No. 68069 & After	237048	9455 GS
P.S.	826215	9425 GS
DIESEL ENG.		
Fan.....	227470	9480 GS
P.S.	826215	9425 GS

Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
616; 622		
GAS ENG.		
Upper; Early.....	>20088	25474
Lower; Early.....	>21794	25476
DIESEL ENG.		
Upper; Early.....		25473
Lower; Early.....	*1 1/2" I.D.	
801; 802		
GAS ENG.		
Upper	*1 3/4" I.D.	
Lower	>20957	
860		
2800 DIESEL ENG.		
Upper		26505
By Pass	>20563	

Farm Equipment, Cotton Stripper

Belts

Application	Mfr. Part No.	Belt No.
707; 707XTB		
Hyd. Pump.....	548872	9455 GS
760XTB		
Alt./Gen.	1146660	7400
Gov.	1146702	7480
Hyd. Pump.....	562203	9440 GS
860; 860XTB		
GAS ENG.		
Alt./Gen.	1146660	7400
Gov.; Ser. No. 4000 & Before	1146702	7480
Hyd. Pump.....	562203	9440 GS
DIESEL ENG.		
Alt./Gen.	582884	9550 GS
Gov.; Ser. No. 4000 & Before	1146702	7480
Hyd. Pump.....	582377	TR28463 GS

- ② Two Required.
- ③ Three Required.
- ④ Four Required.
- ⑤ Five Required.
- ⑥ Six Required.
- > Cut To Fit.
- ▲ Durion® Silicone Hose Recommended.
- ✱ Use Notched Belt Only.
- GS Green Stripe® Construction.
- ✱ Green Stripe® 4-Ply Coolant Hose Recommended.
- ② Use Wire Inserted Green Stripe® Coolant Hose.
- * Green Stripe II Straight Coolant Hose Recommended.

For a maintenance free coolant connection, see PowerGrip® SB clamp application section.

Belts and Coolant Hose for Farm Tractors and Farm Equipment (1970 And Newer)

ALLIS-CHALMERS - Continued Farm Equipment, Forage Harvester

Belts

Application	Mfr. Part No.	Belt No.
880		
Alt.; W/53 1/4" Belt O.C.		9530 GS
Alt.; W/54 1/4" Belt O.C.		9540 GS
A.C.	1148120	9510 GS
Hyd. Pump.....	1173232	9640 GS

BELARUS

Tractors Belts

Application	Mfr. Part No.	Belt No.
250		
VLADIMIR 2-CYL. DIESEL ENG. Gen. & Blower.....		7520
250AS		
VLADIMIR 2-CYL. DIESEL ENG. Gen. & Blower.....		7500
310		
BELARUS 4-CYL. DIESEL ENG. Gen. & Blower.....		7500
420A; 420AN		
BELARUS 4-CYL. DIESEL ENG. Alt. & Blower.....	②7525	
500		
BELARUS 4-CYL. DIESEL ENG. Fan & Alt.		TR24489 GS
520		
BELARUS 4-CYL. DIESEL ENG. Fan & Alt.		TR24489 GS
560		
BELARUS 4-CYL. DIESEL ENG. Fan & Alt.		TR24515 GS
Fan & A.C.....		TR22508 GS
Alt.; W/A.C.....		9279 GS
562		
BELARUS 4-CYL. DIESEL ENG. Fan & Alt.		TR24515 GS
Fan & A.C.....		TR22508 GS
Alt.; W/A.C.....		9279 GS
611		
BELARUS 4-CYL. DIESEL ENG. Fan & Alt.		TR24578 GS
800		
BELARUS 4-CYL. DIESEL ENG. Fan & Alt.		7516
Fan & A.C.....		9510 GS
Alt.; W/A.C.....		9270 GS
802		
BELARUS 4-CYL. DIESEL ENG. Fan & Alt.		7516
Fan & A.C.....		9510 GS
Alt.; W/A.C.....		9270 GS
822		
BELARUS 4-CYL. DIESEL ENG. Fan & Alt.		7516
Fan & A.C.....		9510 GS
Alt.; W/A.C.....		9270 GS
925		
BELARUS 4-CYL. DIESEL ENG. Fan & Alt.	17510	9510 GS
A.C., Alt. & Idler.....	17280	9279 GS

BELARUS - Continued Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
560		
BELARUS 4-CYL. DIESEL ENG. Upper	>21794	25474
Lower	>21145	
By Pass	*1" I.D.	
562		
BELARUS 4-CYL. DIESEL ENG. Upper	>21794	25474
Lower	>21145	
By Pass	*1" I.D.	
800		
BELARUS 4-CYL. DIESEL ENG. Upper	>21794	25474
Lower	>21145	
By Pass	*1" I.D.	
802		
BELARUS 4-CYL. DIESEL ENG. Upper	>21794	25474
Lower	>21145	
By Pass	*1" I.D.	
822		
BELARUS 4-CYL. DIESEL ENG. Upper	>21794	25474
Lower	>21145	
By Pass	*1" I.D.	
925		
BELARUS 4-CYL. DIESEL ENG. Upper	20065	25473
M-500; M-520		
BELARUS 4-CYL. DIESEL ENG. Upper	>20065	
Lower	>20945	
By Pass	*3/4" I.D.	
XT3		
BELARUS V-6 DIESEL ENG. Upper - Eng. To Pipe.....	*1 1/2" I.D.	
Upper - Pipe To Rad.....	*1 1/2" I.D.	
Lower - Eng. To Pipe.....	*2 3/8" I.D.	
Lower - Pipe To Rad.....	*2 3/8" I.D.	
611		
BELARUS V-6 DIESEL ENG. Upper	*1 3/4" I.D.	
Lower - Eng. To Pipe.....	*1 7/8" I.D.	
Lower - Pipe To Rad.....	*1 1/2" I.D.	
820		
BELARUS 4-CYL. DIESEL ENG. Upper		25474

Tractors, Articulated Belts

Application	Mfr. Part No.	Belt No.
1500 (XT3)		
BELARUS V-6 DIESEL ENG. Fan.....		②TR24597 GS
Fan To Alt.....		9463 GS
1770		
BELARUS V-6 DIESEL ENG. Fan To Alt.....		9451 GS
Fan, Alt. & A.C.....	22490	TR22485 GS
Air Brake Compr.....		TR24449 GS
Fan.....		②TR24597 GS

Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
1770		
BELARUS V-6 DIESEL ENG. Upper	*1 5/8" I.D.	
Lower	*2 3/8" I.D.	

- ② Two Required.
- ③ Three Required.
- ④ Four Required.
- ⑤ Five Required.
- ⑥ Six Required.
- ∞ Cut To Fit.
- ▲ Durion® Silicone Hose Recommended.
- ✦ Use Notched Belt Only.
- GS Green Stripe® Construction.
- ✦ Green Stripe® 4-Ply Coolant Hose Recommended.
- ✦ Use Wire Inserted Green Stripe® Coolant Hose.
- * Green Stripe II Straight Coolant Hose Recommended.

For a maintenance free coolant connection, see PowerGrip® SB clamp application section.