

# Belts and Coolant Hose for Farm Tractors and Farm Equipment (1969 And Older)

## KOMATSU - Continued Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
<b>D31A</b>		
4D105-3 ENG.		
Upper .....	×20957	26501
Lower .....		26510
<b>D55S DOZER</b>		
S4D120 ENG.		
Upper .....	×20611	26509
Lower - Eng. To Pipe.....	2" I.D.	
Lower - Pipe To Rad.....	2" I.D.	
<b>D60P DOZER</b>		
CUMMINS NH220CI ENG.		
Upper .....		26523
Lower .....		26520
<b>D65E DOZER</b>		
CUMMINS NH220CI ENG.		
Upper .....	×20731	26523
<b>D65EX DOZER</b>		
6-CYL. DIESEL ENG.		
Upper .....		26533
<b>D65P DOZER</b>		
CUMMINS NH220CI ENG.		
Upper .....		26521
Lower .....		26520
<b>D65S DOZER</b>		
CUMMINS NH220CI ENG.		
Upper .....		26522
Lower .....	2 1/4" I.D.	
<b>D66S-1 DOZER</b>		
KOMATSU SA6D110-1 ENG.		
Upper .....		26524
By Pass .....	×21942	
<b>D75S DOZER</b>		
CUMMINS NH220CI ENG.		
Upper .....		26524
<b>D85E DOZER</b>		
KOMATSU/CUMMINS NT855 ENG.		
Upper .....	✦2 3/8" I.D.	
<b>D375A DOZER</b>		
KOMATSU SA6D470 ENG.		
Upper .....	✦3" I.D.	

## KUBOTA

### Tractors Belts

Application	Mfr. Part No.	Belt No.
<b>G3200; G4200; G5200</b>		
Fan & Alt. ....	REMF1320	7320
<b>G6200</b>		
Fan & Alt. ....	REMF1345	7345
<b>1750</b>		
Fan & Alt. ....	FM36.2	7365
<b>3450</b>		
Fan & Alt. ....	REMF1415	7420

### Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
<b>G3200; G5200; G6200</b>		
Upper .....	×20802	
Lower .....	×20802	
<b>1750</b>		
Upper .....	×21391	
Lower .....	1" I.D.	
<b>3450</b>		
Upper .....	×21794	
Lower .....		25255

## LEYLAND

### Tractors Belts

Application	Mfr. Part No.	Belt No.
<b>154</b>		
<b>15T DIESEL ENG.</b>		
Fan & Alt.; W/40 1/4" Belt O.C....	13H3348	9400 <sup>GS</sup>
Fan & Alt.; W/41 3/4" Belt O.C....		9415 <sup>GS</sup>
Hyd. Pump.....	BTJ6280	TR22525 <sup>GS</sup>
<b>16T GAS ENG.</b>		
Fan & Alt. ....	13H4646	9380 <sup>GS</sup>
Hyd. Pump.....	BTJ6280	TR22525 <sup>GS</sup>
<b>235</b>		
<b>PERKINS 108TD ENG.</b>		
Hyd. Pump.....		9510 <sup>GS</sup>
<b>245; 253</b>		
<b>PERKINS D3-152 ENG.</b>		
Fan & Alt. ....	12B633	TR22461 <sup>GS</sup>
<b>272; 384</b>		
<b>DIESEL ENG.</b>		
Fan & Alt. ....	12B1421	9505 <sup>GS</sup>
<b>344</b>		
<b>DIESEL ENG.</b>		
Fan & Alt. ....	BMK977	9510 <sup>GS</sup>

## LITTLE GIANT

### Tractors Belts

Application	Mfr. Part No.	Belt No.
<b>C48</b>		
<b>DETROIT DIESEL 3-71 ENG.</b>		
Fan.....		®9420 <sup>GS</sup>
Alt.....		9370 <sup>GS</sup>

## LONG

### Tractors Belts

Application	Mfr. Part No.	Belt No.
<b>154</b>		
<b>LEYLAND DIESEL ENG.</b>		
Fan & Gen.....		9395 <sup>GS</sup>
Hyd. Pump.....		TR22517 <sup>GS</sup>
<b>344; 384</b>		
<b>LEYLAND 59 H.P. DIESEL ENG.; LEYLAND 75 H.P. DIESEL ENG.</b>		
Fan & Gen.....		9505 <sup>GS</sup>
<b>4/25</b>		
<b>4-CYL. GAS ENG.</b>		
Fan & Gen.....	3H4646	7369
Gov. ....	8T13470	7215
Hyd. Pump.....		3520
<b>5-N-1</b>		
<b>4-CYL. DIESEL ENG.</b>		
Fan & Alt. ....		K060525 <sup>GS</sup>
<b>1100 WHEEL LOADER</b>		
Fan & Alt. ....		7512
A.C. ....		9505 <sup>GS</sup>

### Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
<b>154</b>		
<b>LEYLAND DIESEL ENG.</b>		
Upper .....	1 1/4" I.D.	
Lower .....		25250
<b>344; 384</b>		
<b>LEYLAND 59 H.P. DIESEL ENG.; LEYLAND 75 H.P. DIESEL ENG.</b>		
Upper .....	×20450	25474
Lower .....	1 1/2" I.D.	

- ② Two Required.
- ③ Three Required.
- ④ Four Required.

- ⑤ Five Required.
- ⑥ Six Required.
- × Cut To Fit.

- ▲ Durion® Silicone Hose Recommended.
- ✦ Use Notched Belt Only.
- <sup>GS</sup> Green Stripe® Construction.

- ✦ Green Stripe® 4-Ply Coolant Hose Recommended.
- ✦ Use Wire Inserted Green Stripe® Coolant Hose.
- \* Green Stripe II Straight Coolant Hose Recommended.

For a maintenance free coolant connection, see PowerGrip® SB clamp application section.

# Belts and Coolant Hose for Farm Tractors and Farm Equipment (1969 And Older)

## LONG - Continued

### Coolant Hose - Continued

Application	Molded or Strt.	Vulco-Flex®
<b>4/25</b>		
<b>4-CYL. GAS ENG.</b>		
Upper .....		25250
Lower .....		25251
<b>5-N-1</b>		
<b>4-CYL. DIESEL ENG.</b>		
Upper .....		25473
Lower .....		25480
<b>512S</b>		
<b>D116 ENG.; D121 ENG.</b>		
Upper .....	>20958	26502
Lower - Eng. To Pipe.....	1 1/2" I.D.	
Lower - Pipe To Rad.....	1 1/2" I.D.	
<b>1100 WHEEL LOADER</b>		
<b>X7501T DIESEL ENG.</b>		
Upper .....		25527
Lower - Pipe To Rad.....	1 1/2" I.D.	

## MACDON

### Farm Equipment Belts

Application	Mfr. Part No.	Belt No.
<b>920 WINDROWER</b>		
<b>3.9 L DIESEL ENG.</b>		
Fan & Alt. ....		K080560 GS
<b>7000 WINDROWER; 9000 WINDROWER</b>		
<b>CHRYSLER 6-CYL. 225 GAS ENG.</b>		
Fan & Alt. ....	K240071	7590
A.C. ....	K240341	7483
Gov. ....	K243341	7460
<b>CUMMINS B SERIES 3.9 L DIESEL ENG.</b>		
Fan & Alt. ....	K080560 GS	9480 GS
A.C.; W/48 5/8" Belt O.C. ....		9412 GS
A.C.; W/41 1/2" Belt O.C. ....		

### Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
<b>9000 WINDROWER</b>		
<b>CUMMINS B SERIES 3.9 L DIESEL ENG.</b>		
Lower .....		26611

## MASSEY-FERGUSON

### Tractors Belts

Application	Mfr. Part No.	Belt No.
<b>F40</b>		
Fan & Gen.....	509572M1	9425 GS
<b>FE35</b>		
<b>23C DIESEL ENG.</b>		
Fan & Gen.....	826960M1	TR28423 GS
<b>TE20; TO20; TO30</b>		
Fan & Gen.....	181636M1	TR28406 GS
<b>TE-A20</b>		
Fan & Gen.; Ser. No. 132206 & Before .....	825660M1	TR24407 GS
<b>TO35</b>		
<b>DIESEL ENG.</b>		
Fan & Gen.....	184930M1	TR28423 GS
<b>GAS ENG.</b>		
Fan & Gen.....	509572M1	9425 GS
<b>MF11 LOADER</b>		
Fan & Alt.; Ser. No. J1399 & Before .....	1446201M1	9505 GS

## MASSEY-FERGUSON - Continued

### Belts - Continued

Application	Mfr. Part No.	Belt No.
<b>MF11 LOADER - Continued</b>		
Fan & Alt.; Ser. No. J1400 & Af- ter .....	2614087RF	②7512
<b>MF25</b>		
Fan & Alt. ....	966427M1	9390 GS
<b>MF30D</b>		
Fan & Alt. ....	531371M1	9525 GS
<b>MF35</b>		
<b>DIESEL ENG.</b>		
Fan & Alt./Gen.....	186976M1	9490 GS
<b>GAS ENG.</b>		
Fan & Alt./Gen.....	509572M1	9425 GS
<b>MF50</b>		
<b>DIESEL ENG.</b>		
Fan & Alt./Gen.; Agricultural .....	189789M1	9485 GS
Fan & Alt.; Ind. ....	843198M1	9525 GS
Fan & Gen.; Ind. ....	186750M2	9476 GS
<b>GAS ENG.</b>		
Fan & Alt. ....	513890M1	9451 GS
Fan & Gen.....	509572M1	9425 GS
<b>MF50A</b>		
Fan & Alt. ....	843198M1	9525 GS
<b>MF50D</b>		
Fan & Alt. ....	517344M2	9540 GS
<b>MF65</b>		
<b>DIESEL ENG.</b>		
Fan & Alt./Gen.....	186750M2	9476 GS
<b>GAS ENG.</b>		
Fan & Alt./Gen.....	184526M1	9440 GS
<b>MF85; MF88; MF SUPER 90</b>		
<b>DIESEL ENG.</b>		
Fan & Gen.....	190083M1	9510 GS
<b>GAS ENG.</b>		
Fan & Gen.....	185223M1	9530 GS
<b>MF135</b>		
<b>DIESEL ENG.</b>		
Fan & Gen.; Ser. No. 9A38904 & Before .....	186976M1	9490 GS
Fan & Alt.; Orchard; Ser. No. 9A38905 & After .....	517456M1	9500 GS
Fan & Alt.; Special; Ser. No. 9A38905 & After .....	843198M1	9525 GS
<b>GAS ENG.</b>		
Fan & Gen.....	509572M1	9425 GS
<b>MF200 CRAWLER</b>		
Fan.....	508560M1	9370 GS
Fan To Alt.....	508588M2	9319 GS
<b>MF200B</b>		
Fan.....	2740015M1	9295 GS
<b>MF202; MF204</b>		
Fan & Alt. ....	509572M1	9425 GS
<b>MF203</b>		
Fan & Alt. ....	186976M1	9490 GS
<b>MF220 IND. SKIDDER</b>		
Fan & Alt.; Ser. No. 248UA6333 & Before .....	186976M1	9490 GS
Fan & Alt.; Ser. No. 248UA6334 & After .....	1840685M91	②7500
<b>MF300 CRAWLER</b>		
Fan & Alt.; Ser. No. 248UA14402L & Before.....		9470 GS
Fan & Alt.; Ser. No. 248UA17092 Thru 248UA88561 .....	1446046M1	②7470
Fan & Alt.; Ser. No. 248UA88561 & After .....	1446925M1	②7475
<b>MF302; MF304</b>		
<b>CONTINENTAL ENG.</b>		
Fan & Gen.....	509572M1	9425 GS
<b>PERKINS ENG.</b>		
Fan & Alt. ....	512747M1	9530 GS
Fan & Gen.....	186750M1	9476 GS

- |                   |                  |                                      |  |
|-------------------|------------------|--------------------------------------|--|
| ② Two Required.   | ⑤ Five Required. | ▲ Durion® Silicone Hose Recommended. | ✦ Green Stripe® 4-Ply Coolant Hose Recommended.      |
| ③ Three Required. | ⑥ Six Required.  | ✦ Use Notched Belt Only.             | ✦ Use Wire Inserted Green Stripe® Coolant Hose.      |
| ④ Four Required.  | ✦ Cut To Fit.    | GS Green Stripe® Construction.       | ✦ Green Stripe II Straight Coolant Hose Recommended. |

**For a maintenance free coolant connection, see PowerGrip® SB clamp application section.**