

# Belts and Coolant Hose for Farm Tractors and Farm Equipment (1969 And Older)

## OLIVER - Continued

### Coolant Hose - Continued

Application	Molded or Strt.	Vulco-Flex®
<b>40 COMBINE DIESEL ENG.</b>		
Upper.....	>20065	
<b>GAS ENG.</b>		
Upper; Ser. No. 400001 Thru 401001.....		25478
Upper; Ser. No. 401002 Thru 401802.....		25476
Lower; Ser. No. 400001 Thru 401802.....	>20065	
<b>525 COMBINE; 535 COMBINE CHRYSLER IND. ENG.</b>		
Upper.....		26521
Lower.....		25484
<b>545 COMBINE CHRYSLER V-8 GAS ENG.</b>		
Upper.....		25484
Lower.....		25484
By Pass.....	⊕3/4" I.D.	
<b>840 FIELD HARVESTER 6-CYL. DIESEL ENG.</b>		
Upper.....		26511
<b>5542 COMBINE V-8 GAS ENG.</b>		
Upper.....		25487
By Pass.....	>20563	

## OMC

### Farm Equipment Belts

Application	Mfr. Part No.	Belt No.
<b>A12 SHAKER JOHN DEERE 6059D DIESEL ENG.</b>		
W.P. & Alt.....		A76
W.P., Air Cond. & Air Pump.....		A64

### Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
<b>A12 SHAKER JOHN DEERE 6059D DIESEL ENG.</b>		
Upper.....	>21379	
Lower.....	⊕2 1/4" I.D.	

## SATOH

### Tractors Belts

Application	Mfr. Part No.	Belt No.
<b>S550G 4-CYL. GAS ENG.</b>		
Fan & Alt.....		7420
W.P. & Governor.....		7410
<b>650 G 4-CYL. GAS ENG.</b>		
Fan & Alt.; W/41 1/8" Belt O.C....	0180190	7410
Fan & Alt.; W/41 5/8" Belt O.C....		7417
Fan & Alt.; W/43 1/8" Belt O.C....	0180200	7430
Gov.; W/41 1/8" Belt O.C.....	0180190	7410
Gov.; W/43 5/8" Belt O.C.....	0180200	7430
<b>BEAVER 3</b>		
Fan & Alt.....		7375
<b>BISON; BULL S670 ENG.</b>		
Fan & Alt.....	REMF1380	7390
<b>BUCK</b>		
Fan & Alt.....		7320

## SATOH - Continued

### Belts - Continued

Application	Mfr. Part No.	Belt No.
<b>STALLION 108 ENG.</b>		
Fan & Alt.....	4136713030	9412 <sup>GS</sup>

### Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
<b>S550G 4-CYL. GAS ENG.</b>		
Upper.....		25252
Lower.....	>20476	25252
<b>BISON S670 ENG.</b>		
Upper.....		25251
<b>STALLION 108 ENG.</b>		
Upper.....		25252

## SHEPPARD

### Tractors Belts

Application	Mfr. Part No.	Belt No.
<b>SD2; SD3; SDG2; SDG3; SD02; SD03 6B ENG.; 6E ENG.; 13E ENG.</b>		
Fan & Gen.....	0400251	TR22570 <sup>GS</sup>
<b>SD4 16B ENG.</b>		
Fan & Gen.....	0400050	7575

## TERRA-GATOR

### Farm Equipment Belts

Application	Mfr. Part No.	Belt No.
<b>1253 SPRAYER CUMMINS V555 DIESEL ENG.</b>		
Fan.....	204481	⊕9625 <sup>GS</sup>
Alt.....	178398	⊕7340
Hyd. Pump.....		⊕9580 <sup>GS</sup>

### Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
<b>1253 SPRAYER CUMMINS V555 ENG.</b>		
Upper.....		26513
Lower.....		26519

## TERRA POWER TRACTOR

### Tractors Belts

Application	Mfr. Part No.	Belt No.
<b>UNIVERSAL U-640 4-CYL. DIESEL ENG.</b>		
Fan & Alt.....		7450
<b>UNIVERSAL U-1010 6-CYL. DIESEL ENG.</b>		
Fan.....		⊕9420 <sup>GS</sup>
W.P. & Alt.....		7435

⊕ Two Required.  
⊙ Three Required.  
⊙ Four Required.

⊕ Five Required.  
⊙ Six Required.  
⊙ Cut To Fit.

▲ Durion® Silicone Hose Recommended.  
✦ Use Notched Belt Only.  
<sup>GS</sup> Green Stripe® Construction.

⊕ Green Stripe® 4-Ply Coolant Hose Recommended.  
⊙ Use Wire Inserted Green Stripe® Coolant Hose.  
\* Green Stripe II Straight Coolant Hose Recommended.

For a maintenance free coolant connection, see PowerGrip® SB clamp application section.

# Belts and Coolant Hose for Farm Tractors and Farm Equipment (1969 And Older)

## TERRA POWER TRACTOR

- Continued

### Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
<b>UNIVERSAL U-640</b> 4-CYL. DIESEL ENG.		
Lower .....	②1 3/8" I.D.	
<b>UNIVERSAL U-1010</b> 6-CYL. DIESEL ENG.		
Lower - Eng. To Pipe.....	1 1/2" I.D.	
Lower - Pipe To Rad.....		25472

## TOL

### Farm Equipment Belts

Application	Mfr. Part No.	Belt No.
<b>HAS650 TREE TRIMMER; HAS950 TREE TRIMMER</b> LOMBARDINI 3-CYL. DIESEL ENG.		
Fan & Alt. ....		7265
<b>1200 TREE TRIMMER</b> FORD 6-CYL. DIESEL ENG.		
Fan.....		BX48
W.P. ....		9451 <sup>GS</sup>
W.P. To Alt.....	E4NN10C318AA	9313 <sup>GS</sup>
A.C. ....		9476 <sup>GS</sup>

### Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
<b>HAS650 TREE TRIMMER</b> LOMBARDINI 3-CYL. DIESEL ENG.		
Lower - Eng. To Pipe.....	>②0065	
Lower - Pipe To Rad.....	>②0065	

## VALMET

### Tractors Belts

Application	Mfr. Part No.	Belt No.
<b>78 VIKING; 880; 980</b> MWM 4-CYL. DIESEL ENG.		
Fan & Alt. ....		9485 <sup>GS</sup>

## VERSATILE; See Ford Also

### Farm Equipment Belts

Application	Mfr. Part No.	Belt No.
<b>330 WINDROWER</b> FORD 4-CYL. 122 ENG.		
Fan & Alt. ....		②7360
Fan & Gov.....		9500 <sup>GS</sup>
Camshaft Drive.....		T013
<b>400 WINDROWER; 440 WINDROWER</b> FORD 6-CYL. 200 ENG.		
Fan & Alt. ....	C5DE 8620 C	7340
Gov.....	C7ZZ 8620 F	7312

### Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
<b>330 WINDROWER</b> FORD 4-CYL. 122 ENG.		
Upper .....		25476
Lower .....		25487

## VERSATILE; See Ford Also

- Continued

### Coolant Hose - Continued

Application	Molded or Strt.	Vulco-Flex®
<b>400 WINDROWER; 440 WINDROWER</b> FORD 6-CYL. 200 ENG.		
Upper; 1970 & Newer.....		25305
Lower; 1969 & Newer.....		25484

## WHITE; See Minneapolis-Moline And Agco Allis Also Tractors Belts

Application	Mfr. Part No.	Belt No.
<b>FIELD BOSS 31</b> Fan & Alt. ....	5136710400	9400 <sup>GS</sup>
<b>80</b> CUMMINS 6B5.9 ENG.		
Fan & Alt. ....	3911563	K080605 <sup>GS</sup>
A.C. ....	303315134	9400 <sup>GS</sup>
<b>515 (2/44); 588</b> 4-CYL. GAS ENG.		
Fan & Gen.....	102752A	7450
Hyd. Pump.....	101636A	7430
<b>1265</b> 3-CYL. DIESEL ENG.		
Fan & Alt. ....	4818920	7455
<b>1355</b> Fan & Alt. ....		②9580 <sup>GS</sup>
A.C. ....		③9580 <sup>GS</sup>
<b>1365</b> Fan & Alt. ....	676865A	7450
<b>1555</b> DIESEL ENG.		
Fan & Alt.; Ser. No. 160,000 Thru 168,920.....	160610A	9447 <sup>GS</sup>
Fan & Alt.; Ser. No. 168,921 & After.....	158679A	7450
A.C. ....	167897A	7480
<b>GAS ENG.</b>		
Fan & Alt.; Ser. No. 160,000 Thru 169,845.....	160610A	9447 <sup>GS</sup>
Fan & Alt.; Ser. No. 169,846 & After.....	162123A	7445
P.S. ....	157176AA	7290
A.C. ....	167897A	7480
<b>LPG ENG.</b>		
Fan & Alt.; Ser. No. 160,000 Thru 169,386.....	160610A	9447 <sup>GS</sup>
Fan & Alt.; Ser. No. 169,387 & After.....	162123A	7445
P.S. ....	157176AA	7290
A.C. ....	167897A	7480
<b>1655</b> DIESEL ENG.		
Fan & Alt.; W/Single Belt.....	157680A	7460
Fan & Alt.; W/Dual Belts; W/46 1/8" Belt O.C.....	162071A	②7460
Fan & Alt.; W/Dual Belts; W/47 1/4" Belt O.C.....		②9470 <sup>GS</sup>
P.S. ....	157177A	7375
A.C. ....	167897A	7480
<b>GAS ENG.</b>		
Fan & Alt. ....	158679A	7450
P.S. ....	157176AA	7290
A.C. ....	167897A	7480
<b>1755</b> DIESEL ENG.		
Fan & Alt. ....	162071A	②7460
P.S.; W/A.C. ....	103926A	7250
P.S.; W/O A.C. ....	168052A	7417

- ② Two Required.
- ③ Three Required.
- ④ Four Required.

- ⑤ Five Required.
- ⑥ Six Required.
- > Cut To Fit.

- ▲ Durion® Silicone Hose Recommended.
- ✦ Use Notched Belt Only.
- <sup>GS</sup> Green Stripe® Construction.

- ✦ Green Stripe® 4-Ply Coolant Hose Recommended.
- ✦ Use Wire Inserted Green Stripe® Coolant Hose.
- \* Green Stripe II Straight Coolant Hose Recommended.

For a maintenance free coolant connection, see PowerGrip® SB clamp application section.