

# Belts and Coolant Hose for Farm Tractors and Farm Equipment (1969 And Older)

## TERRA POWER TRACTOR

- Continued

### Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
<b>UNIVERSAL U-640</b> 4-CYL. DIESEL ENG.		
Lower .....	②1 3/8" I.D.	
<b>UNIVERSAL U-1010</b> 6-CYL. DIESEL ENG.		
Lower - Eng. To Pipe.....	1 1/2" I.D.	
Lower - Pipe To Rad.....		25472

## TOL

### Farm Equipment Belts

Application	Mfr. Part No.	Belt No.
<b>HAS650 TREE TRIMMER; HAS950 TREE TRIMMER</b> LOMBARDINI 3-CYL. DIESEL ENG.		
Fan & Alt. ....		7265
<b>1200 TREE TRIMMER</b> FORD 6-CYL. DIESEL ENG.		
Fan.....		BX48
W.P. ....		9451 <sup>GS</sup>
W.P. To Alt.....	E4NN10C318AA	9313 <sup>GS</sup>
A.C. ....		9476 <sup>GS</sup>

### Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
<b>HAS650 TREE TRIMMER</b> LOMBARDINI 3-CYL. DIESEL ENG.		
Lower - Eng. To Pipe.....	>②0065	
Lower - Pipe To Rad.....	>②0065	

## VALMET

### Tractors Belts

Application	Mfr. Part No.	Belt No.
<b>78 VIKING; 880; 980</b> MWM 4-CYL. DIESEL ENG.		
Fan & Alt. ....		9485 <sup>GS</sup>

## VERSATILE; See Ford Also

### Farm Equipment Belts

Application	Mfr. Part No.	Belt No.
<b>330 WINDROWER</b> FORD 4-CYL. 122 ENG.		
Fan & Alt. ....		②7360
Fan & Gov.....		9500 <sup>GS</sup>
Camshaft Drive.....		T013
<b>400 WINDROWER; 440 WINDROWER</b> FORD 6-CYL. 200 ENG.		
Fan & Alt. ....	C5DE 8620 C	7340
Gov.....	C7ZZ 8620 F	7312

### Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
<b>330 WINDROWER</b> FORD 4-CYL. 122 ENG.		
Upper .....		25476
Lower .....		25487

## VERSATILE; See Ford Also

- Continued

### Coolant Hose - Continued

Application	Molded or Strt.	Vulco-Flex®
<b>400 WINDROWER; 440 WINDROWER</b> FORD 6-CYL. 200 ENG.		
Upper; 1970 & Newer.....		25305
Lower; 1969 & Newer.....		25484

## WHITE; See Minneapolis-Moline And Agco Allis Also Tractors Belts

Application	Mfr. Part No.	Belt No.
<b>FIELD BOSS 31</b> Fan & Alt. ....	5136710400	9400 <sup>GS</sup>
<b>80</b> CUMMINS 6B5.9 ENG.		
Fan & Alt. ....	3911563	K080605 <sup>GS</sup>
A.C. ....	303315134	9400 <sup>GS</sup>
<b>515 (2/44); 588</b> 4-CYL. GAS ENG.		
Fan & Gen.....	102752A	7450
Hyd. Pump.....	101636A	7430
<b>1265</b> 3-CYL. DIESEL ENG.		
Fan & Alt. ....	4818920	7455
<b>1355</b> Fan & Alt. ....		②9580 <sup>GS</sup>
A.C. ....		③9580 <sup>GS</sup>
<b>1365</b> Fan & Alt. ....	676865A	7450
<b>1555</b> DIESEL ENG.		
Fan & Alt.; Ser. No. 160,000 Thru 168,920.....	160610A	9447 <sup>GS</sup>
Fan & Alt.; Ser. No. 168,921 & After .....	158679A	7450
A.C. ....	167897A	7480
<b>GAS ENG.</b> Fan & Alt.; Ser. No. 160,000 Thru 169,845.....	160610A	9447 <sup>GS</sup>
Fan & Alt.; Ser. No. 169,846 & After .....	162123A	7445
P.S. ....	157176AA	7290
A.C. ....	167897A	7480
<b>LPG ENG.</b> Fan & Alt.; Ser. No. 160,000 Thru 169,386.....	160610A	9447 <sup>GS</sup>
Fan & Alt.; Ser. No. 169,387 & After .....	162123A	7445
P.S. ....	157176AA	7290
A.C. ....	167897A	7480
<b>1655</b> DIESEL ENG.		
Fan & Alt.; W/Single Belt.....	157680A	7460
Fan & Alt.; W/Dual Belts; W/46 1/8" Belt O.C.....	162071A	②7460
Fan & Alt.; W/Dual Belts; W/47 1/4" Belt O.C.....		②9470 <sup>GS</sup>
P.S. ....	157177A	7375
A.C. ....	167897A	7480
<b>GAS ENG.</b> Fan & Alt. ....	158679A	7450
P.S. ....	157176AA	7290
A.C. ....	167897A	7480
<b>1755</b> DIESEL ENG.		
Fan & Alt. ....	162071A	②7460
P.S.; W/A.C. ....	103926A	7250
P.S.; W/O A.C. ....	168052A	7417

- ② Two Required.
- ③ Three Required.
- ④ Four Required.

- ⑤ Five Required.
- ⑥ Six Required.
- > Cut To Fit.

- ▲ Durion® Silicone Hose Recommended.
- ✦ Use Notched Belt Only.
- <sup>GS</sup> Green Stripe® Construction.

- ✦ Green Stripe® 4-Ply Coolant Hose Recommended.
- ✦ Use Wire Inserted Green Stripe® Coolant Hose.
- \* Green Stripe II Straight Coolant Hose Recommended.

For a maintenance free coolant connection, see PowerGrip® SB clamp application section.