



Poly Chain® GT® Idler Sprockets

Bearing and material speed limitations based on rpm are:

| | <u>Bearing Limit</u> | <u>Material Limit</u> |
|---|----------------------|-----------------------|
| 8M-32S-12 8M-32S-21 | 9000 rpm | 9700 rpm |
| 8M-36S-36 8M-36S-62 | 6050 rpm | 8610 rpm |
| 14M-30S-20 14M-30S-37 | 4800 rpm | 5925 rpm |
| 14M-34S-68 14M-34S-90 14M-34S-125 | 3900 rpm | 5215 rpm |