



# RACING PERFORMANCE MUSCLE RPM BELT DIMENSION CHART



## ENGINEERED FOR PERFORMANCE

Gates RPM belts are specifically engineered for forced induction and high-output engines. Featuring a high-modulus, low stretch Aramid or Polyester tensile cord, nylon-fiber reinforced undercord, and dual adhesion gum layers, these belts can handle more power and withstand more punishment than any other belt on the market.

**GOT BELT ISSUES? GET GATES RPM.**

PART NUMBER	PRODUCT DESCRIPTION	NUMBER OF RIBS	EFFECTIVE LENGTH (IN)	EFFECTIVE LENGTH (MM)	OUTSIDE CIRCUMFERENCE (IN)	OUTSIDE CIRCUMFERENCE (MM)
K030250RPM	K03 13/32" x 25 3/4" - Black	3	25.17	639	25.731	654
K030295RPM	K03 13/32" x 30 1/8" - Black	3	29.55	751	30.111	765
K030300RPM	K03 13/32" x 30 3/4" - Black	3	30.19	767	30.755	781
K030334RPM	K03 13/32" x 34" - Black	3	33.46	850	34.024	864
K040220RPM	K04 9/16" x 22 3/4" - Black	4	22.11	562	22.75	578
K040274RPM	K04 9/16" x 28" - Black	4	27.38	695	27.95	710
K040292RPM	K04 9/16" x 29 3/4" - Black	4	29.19	741	29.75	756
K040300RPM	K04 9/16" x 30 3/4" - Black	4	30.17	766	30.74	781
K040305RPM	K04 9/16" x 31 1/4" - Black	4	30.65	779	31.213	792
K040310RPM	K04 9/16" x 31 5/8" - Black	4	31.13	791	31.625	803
K040315RPM	K04 9/16" x 32 1/4" - Black	4	31.65	804	32.25	818
K040322RPM	K04 9/16" x 32 7/8" - Black	4	32.35	822	32.875	835
K040325RPM	K04 9/16" x 33 1/4" - Black	4	32.64	829	33.25	845
K040329RPM	K04 9/16" x 33 3/8" - Black	4	32.87	835	33.375	849
K040330RPM	K04 9/16" x 33 5/8" - Black	4	33.13	842	33.625	854
K040332RPM	K04 9/16" x 33 3/4" - Black	4	33.2	843	33.75	857
K040335RPM	K04 9/16" x 34" - Black	4	33.46	850	34	864
K040338RPM	K04 9/16" x 34 3/8" - Black	4	33.86	860	34.375	874
K040340RPM	K04 9/16" x 34 5/8" - Black	4	34.124	867	34.625	879
K040345RPM	K04 9/16" x 35" - Black	4	34.44	875	35	889
K040347RPM	K04 9/16" x 35 1/4" - Black	4	34.75	883	35.25	895
K040353RPM	K04 9/16" x 35 7/8" - Black	4	35.33	897	35.875	912
K040355RPM	K04 9/16" x 36 1/8" - Black	4	35.56	903	36.125	918
K040360RPM	K04 9/16" x 36 3/4" - Black	4	36.14	918	36.75	933
K040365RPM	K04 9/16" x 37 1/8" - Black	4	36.56	929	37.125	943
K040370RPM	K04 9/16" x 37 1/2" - Black	4	36.994	940	37.5	953
K040372RPM	K04 9/16" x 38" - Black	4	37.38	949	38	964
K040384RPM	K04 9/16" x 39" - Black	4	38.425	976	39	991
K040385RPM	K04 9/16" x 39 1/8" - Black	4	38.52	978	39.09	993
K040390RPM	K04 9/16" x 39 5/8" - Black	4	39.13	994	39.625	1008
K040398RPM	K04 9/16" x 40 3/8" - Black	4	39.87	1013	40.375	1027
K040400RPM	K04 9/16" x 40 5/8" - Black	4	40.133	1019	40.625	1032
K040405RPM	K04 9/16" x 41 1/4" - Black	4	40.649	1032	41.25	1047
K040410RPM	K04 9/16" x 41 5/8" - Black	4	41.126	1045	41.625	1057
K040413RPM	K04 9/16" x 42" - Black	4	41.503	1054	42	1067



PART NUMBER	PRODUCT DESCRIPTION	NUMBER OF RIBS	EFFECTIVE LENGTH (IN)	EFFECTIVE LENGTH (MM)	OUTSIDE CIRCUMFERENCE (IN)	OUTSIDE CIRCUMFERENCE (MM)
K040420RPM	K04 9/16" x 42 5/8" - Black	4	42.13	1070	42.625	1084
K040430RPM	K04 9/16" x 43 3/4" - Black	4	43.15	1096	43.75	1111
K040440RPM	K04 9/16" x 44 5/8" - Black	4	44.125	1121	44.625	1133
K040476RPM	K04 9/16" x 48 1/8" - Black	4	47.61	1209	48.13	1223
K040490RPM	K04 9/16" x 49 1/2" - Black	4	48.97	1244	49.537	1258
K040500RPM	K04 9/16" x 50 5/8" - Black	4	50.07	1272	50.625	1286
K040517RPM	K04 9/16" x 52 1/8" - Black	4	51.6	1311	52.125	1325
K040530RPM	K04 9/16" x 53 1/2" - Black	4	53	1346	53.5	1359
K040551RPM	K04 9/16" x 55 3/4" - Black	4	55.13	1400	55.75	1415
K050321RPM	K05 21/32" x 32 3/4" - Black	5	32.16	817	32.75	831
K050336RPM	K05 21/32" x 34 1/4" - Black	5	33.75	857	34.25	871
K050344RPM	K05 21/32" x 35" - Black	5	34.44	875	35	889
K050345RPM	K05 21/32" x 35 1/4" - Black	5	34.64	880	35.25	895
K050350RPM	K05 21/32" x 35 5/8" - Black	5	35.1	891	35.625	905
K050380RPM	K05 21/32" x 38 5/8" - Black	5	38.14	969	38.625	981
K050390RPM	K05 21/32" x 39 5/8" - Black	5	39.13	994	39.625	1006
K050400RPM	K05 21/32" x 40 5/8" - Black	5	40.01	1016	40.625	1032
K050415RPM	K05 21/32" x 42" - Black	5	41.5	1054	42	1068
K050420RPM	K05 21/32" x 42 5/8" - Black	5	42.12	1070	42.625	1083
K050425RPM	K05 21/32" x 43 1/8" - Black	5	42.54	1081	43.125	1094
K050435RPM	K05 21/32" x 44 1/8" - Black	5	43.62	1108	44.125	1121
K050507RPM	K05 21/32" x 51 1/8" - Black	5	50.61	1285	51.125	1299
K050516RPM	K05 21/32" x 52 1/4" - Black	5	51.66	1312	52.225	1327
K050705RPM	K05 21/32" x 71 1/8" - Black	5	70.57	1792	71.135	1807
K050789RPM	K05 21/32" x 79 1/2" - Black	5	78.9	2004	79.5	2019
K050887RPM	K05 21/32" x 89 1/8" - Black	5	88.61	2251	89.173	2265
K060338RPM	K06 13/16" x 34 3/8" - Black	6	33.8	859	34.375	873
K060355RPM	K06 13/16" x 36 1/8" - Black	6	35.56	903	36.125	918
K060370RPM	K06 13/16" x 37 5/8" - Black	6	37.13	943	37.625	957
K060374RPM	K06 13/16" x 37 7/8" - Black	6	37.38	949	37.875	963
K060388RPM	K06 13/16" x 39 3/8" - Black	6	38.78	985	39.375	999
K060448RPM	K06 13/16" x 45 3/8" - Black	6	44.84	1139	45.375	1153
K060465RPM	K06 13/16" x 47" - Black	6	46.48	1181	47	1195
K060478RPM	K06 13/16" x 48 1/4" - Black	6	47.72	1212	48.25	1227
K060480RPM	K06 13/16" x 48 5/8" - Black	6	48.12	1222	48.63	1235
K060490RPM	K06 13/16" x 49 1/2" - Black	6	48.97	1244	49.537	1258
K060525RPM	K06 13/16" x 53 3/8" - Black	6	52.76	1340	53.375	1356
K060532RPM	K06 13/16" x 53 7/8" - Black	6	53.27	1353	53.835	1367
K060535RPM	K06 13/16" x 54 1/4" - Black	6	53.71	1364	54.272	1379
K060539RPM	K06 13/16" x 54 1/2" - Black	6	53.96	1371	54.521	1385
K060547RPM	K06 13/16" x 55 1/4" - Black	6	54.71	1390	55.276	1404
K060551RPM	K06 13/16" x 55 3/4" - Black	6	55.13	1400	55.7	1415
K060555RPM	K06 13/16" x 56" - Black	6	55.46	1409	56.022	1423
K060605RPM	K06 13/16" x 61 1/8" - Black	6	60.59	1539	61.151	1553
K060642RPM	K06 13/16" x 64 3/4" - Black	6	64.24	1632	64.809	1646
K060667RPM	K06 13/16" x 67 1/4" - Black	6	66.69	1694	67.254	1708
K060680RPM	K06 13/16" x 68 5/8" - Black	6	68	1727	68.567	1742
K060685RPM	K06 13/16" x 69 1/8" - Black	6	68.57	1742	69.133	1756



PART NUMBER	PRODUCT DESCRIPTION	NUMBER OF RIBS	EFFECTIVE LENGTH (IN)	EFFECTIVE LENGTH (MM)	OUTSIDE CIRCUMFERENCE (IN)	OUTSIDE CIRCUMFERENCE (MM)
K060690RPM	K06 13/16" x 69 5/8" - Black	6	69.01	1753	69.57	1767
K060705RPM	K06 13/16" x 71 1/8" - Black	6	70.57	1792	71.135	1807
K060739RPM	K06 13/16" x 74 1/2" - Black	6	73.97	1879	74.531	1893
K060744RPM	K06 13/16" x 75" - Black	6	74.39	1890	74.955	1904
K060763RPM	K06 13/16" x 76 7/8" - Black	6	76.25	1937	76.817	1951
K060775RPM	K06 13/16" x 78" - Black	6	77.48	1968	78.04	1982
K060785RPM	K06 13/16" x 79" - Black	6	78.47	1993	79	2007
K060798RPM	K06 13/16" x 80 3/8" - Black	6	79.76	2026	80.326	2040
K060804RPM	K06 13/16" x 81" - Black	6	80.45	2043	81	2057
K060806RPM	K06 13/16" x 81 1/8" - Black	6	80.58	2047	81.141	2061
K060810RPM	K06 13/16" x 81 5/8" - Black	6	81.04	2058	81.608	2073
K060815RPM	K06 13/16" x 82 1/8" - Black	6	81.54	2071	82.125	2085
K060825RPM	K06 13/16" x 83 1/8" - Black	6	82.59	2098	83.155	2112
K060827RPM	K06 13/16" x 83 1/4" - Black	6	82.72	2101	83.288	2116
K060832RPM	K06 13/16" x 83 3/4" - Black	6	83.19	2113	83.755	2127
K060837RPM	K06 13/16" x 84 1/4" - Black	6	83.68	2125	84.242	2140
K060845RPM	K06 13/16" x 85 1/4" - Black	6	84.66	2150	85.23	2165
K060854RPM	K06 13/16" x 85 7/8" - Black	6	85.33	2167	85.892	2182
K060868RPM	K06 13/16" x 87 3/8" - Black	6	86.78	2204	87.345	2219
K060878RPM	K06 13/16" x 88 3/8" - Black	6	87.82	2231	88.387	2245
K060882RPM	K06 13/16" x 88 7/8" - Black	6	88.3	2243	88.87	2257
K060888RPM	K06 13/16" x 89 1/2" - Black	6	88.9	2258	89.47	2273
K060891RPM	K06 13/16" x 89 3/4" - Black	6	89.13	2264	89.695	2278
K060895RPM	K06 13/16" x 90 1/8" - Black	6	89.56	2275	90.127	2289
K060896RPM	K06 13/16" x 89 21/32" - Black	6	89.562	2294	89.66	2277
K060900RPM	K06 13/16" x 90 5/8" - Black	6	90.03	2287	90.595	2301
K060905RPM	K06 13/16" x 90 7/8" - Black	6	90.31	2294	90.873	2308
K060908RPM	K06 13/16" x 91 1/4" - Black	6	90.71	2304	91.27	2318
K060910RPM	K06 13/16" x 91 5/8" - Black	6	91.11	2314	91.68	2329
K060915RPM	K06 13/16" x 92 1/8" - Black	6	91.56	2326	92.125	2340
K060926RPM	K06 13/16" x 93 1/8" - Black	6	92.5	2350	93.069	2364
K060935RPM	K06 13/16" x 94" - Black	6	93.42	2373	93.985	2387
K060938RPM	K06 13/16" x 94 1/2" - Black	6	93.9	2385	94.47	2400
K060947RPM	K06 13/16" x 95 1/4" - Black	6	94.67	2405	95.236	2419
K060950RPM	K06 13/16" x 95 5/8" - Black	6	95.02	2414	95.585	2428
K060962RPM	K06 13/16" x 96 7/8" - Black	6	96.29	2446	96.855	2460
K060970RPM	K06 13/16" x 97 5/8" - Black	6	97.02	2464	97.582	2479
K060975RPM	K06 13/16" x 98 1/8" - Black	6	97.54	2478	98.11	2492
K060980RPM	K06 13/16" x 98 5/8" - Black	6	98.07	2491	98.64	2505
K060990RPM	K06 13/16" x 99 5/8" - Black	6	99.08	2517	99.65	2531
K060994RPM	K06 13/16" x 99 7/8" - Black	6	99.3	2522	99.865	2537
K061000RPM	K06 13/16" x 100 5/8" - Black	6	100.01	2540	100.58	2555
K061005RPM	K06 13/16" x 101 1/8" - Black	6	100.54	2554	101.11	2568
K061010RPM	K06 13/16" x 101 5/8" - Black	6	101.06	2567	101.63	2581
K061015RPM	K06 13/16" x 102 1/8" - Black	6	101.52	2579	102.09	2593
K061020RPM	K06 13/16" x 102 5/8" - Black	6	102	2591	102.57	2605
K061025RPM	K06 13/16" x 103" - Black	6	102.4	2601	102.97	2615
K061031RPM	K06 13/16" x 103 5/8" - Black	6	103.1	2619	103.67	2633

PART NUMBER	PRODUCT DESCRIPTION	NUMBER OF RIBS	EFFECTIVE LENGTH (IN)	EFFECTIVE LENGTH (MM)	OUTSIDE CIRCUMFERENCE (IN)	OUTSIDE CIRCUMFERENCE (MM)
K061033RPM	K06 13/16" x 103 7/8" - Black	6	103.31	2624	103.88	2639
K061037RPM	K06 13/16" x 104 1/4" - Black	6	103.74	2635	104.31	2649
K061040RPM	K06 13/16" x 104 5/8" - Black	6	104	2642	104.66	2658
K061045RPM	K06 13/16" x 105" - Black	6	104.4	2652	104.97	2666
K061054RPM	K06 13/16" x 106" - Black	6	105.43	2678	106	2692
K061058RPM	K06 13/16" x 106 3/8" - Black	6	105.77	2687	106.34	2701
K061066RPM	K06 13/16" x 107 1/8" - Black	6	106.61	2708	107.175	2722
K061073RPM	K06 13/16" x 107 7/8" - Black	6	107.35	2727	107.92	2741
K061075RPM	K06 13/16" x 108 1/8" - Black	6	107.55	2732	108.115	2746
K061080RPM	K06 13/16" x 108 3/4" - Black	6	108.14	2747	108.71	2761
K061098RPM	K06 13/16" x 109 3/8" - Black	6	108.87	2765	109.44	2780
K061110RPM	K06 13/16" x 111 5/8" - Black	6	111.06	2821	111.63	2835
K061119RPM	K06 13/16" x 112" - Black	6	111.93	2843	111.99	2845
K061120RPM	K06 13/16" x 112 1/2" - Black	6	111.99	2845	112.56	2859
K061123RPM	K06 13/16" x 112 7/8" - Black	6	112.37	2854	112.935	2869
K061130RPM	K06 13/16" x 113 5/8" - Black	6	113.05	2871	113.62	2886
K061140RPM	K06 13/16" x 114 1/2" - Black	6	113.99	2895	114.555	2910
K061145RPM	K06 13/16" x 115 1/4" - Black	6	114.65	2912	115.22	2927
K061187RPM	K06 13/16" x 119 1/4" - Black	6	118.74	3016	119.31	3030
K061247RPM	K06 13/16" x 125 1/4" - Black	6	124.76	3169	125.25	3183
K061251RPM	K06 13/16" x 125 5/8" - Black	6	125.09	3177	125.66	3192
K070500RPM	K07 15/16" x 50 5/8" - Black	7	50.07	1272	50.625	1286
K070653RPM	K07 15/16" x 65 7/8" - Black	7	65.36	1660	65.93	1675
K070680RPM	K07 15/16" x 68 5/8" - Black	7	68.06	1729	68.626	1743
K070730RPM	K07 15/16" x 73 5/8" - Black	7	73.09	1856	73.625	1870
K070745RPM	K07 15/16" x 75 1/4" - Black	7	74.567	1894	75.23	1911
K070763RPM	K07 15/16" x 76 7/8" - Black	7	76.25	1937	76.817	1951
K070795RPM	K07 15/16" x 80" - Black	7	79.5	2019	80	2033
K070810RPM	K07 15/16" x 81 5/8" - Black	7	81.04	2058	81.625	2073
K070825RPM	K07 15/16" x 83 1/8" - Black	7	82.59	2098	83.155	2112
K070852RPM	K07 15/16" x 85 3/4" - Black	7	85.21	2164	85.75	2178
K070896RPM	K07 15/16" x 90 1/8" - Black	7	89.56	2275	90.127	2289
K071065RPM	K07 15/16" x 107 1/8" - Black	7	106.53	2706	107.125	2720
K071141RPM	K07 15/16" x 114 5/8" - Black	7	114.08	2898	114.645	2912
K071150RPM	K07 15/16" x 115 5/8" - Black	7	115.04	2922	115.61	2936
K080220RPM	K08 1 3/32" x 22 3/4" - Black	8	22.107	562	22.77	578
K080408RPM	K08 1 3/32" x 41 3/8" - Black	8	40.79	1036	41.36	1051
K080415RPM	K08 1 3/32" x 42 1/8" - Black	8	41.5	1054	42.068	1069
K080435RPM	K08 1 3/32" x 44 1/8" - Black	8	43.62	1108	44.19	1122
K080450RPM	K08 1 3/32" x 45 5/8" - Black	8	45.12	1146	45.685	1160
K080465RPM	K08 1 3/32" x 47" - Black	8	46.48	1181	47.044	1195
K080468RPM	K08 1 3/32" x 47 3/8" - Black	8	46.82	1189	47.375	1203
K080471RPM	K08 1 3/32" x 47 3/4" - Black	8	47.12	1197	47.69	1211
K080480RPM	K08 1 3/32" x 48 5/8" - Black	8	48.12	1222	48.685	1237
K080485RPM	K08 1 3/32" x 49 1/8" - Black	8	48.59	1234	49.155	1249
K080491RPM	K08 1 3/32" x 49 5/8" - Black	8	49.11	1247	49.625	1260
K080496RPM	K08 1 3/32" x 50 1/8" - Black	8	49.61	1260	50.172	1274



PART NUMBER	PRODUCT DESCRIPTION	NUMBER OF RIBS	EFFECTIVE LENGTH (IN)	EFFECTIVE LENGTH (MM)	OUTSIDE CIRCUMFERENCE (IN)	OUTSIDE CIRCUMFERENCE (MM)
K080507RPM	K08 1 3/32" x 51 1/4" - Black	8	50.748	1289	51.25	1302
K080525RPM	K08 1 3/32" x 53 1/8" - Black	8	52.6	1336	53.169	1351
K080530RPM	K08 1 3/32" x 53 1/2" - Black	8	52.95	1345	53.517	1359
K080537RPM	K08 1 3/32" x 54 1/4" - Black	8	53.71	1364	54.272	1379
K080539RPM	K08 1 3/32" x 54 1/2" - Black	8	53.95	1370	54.5	1384
K080545RPM	K08 1 3/32" x 55 1/8" - Black	8	54.5	1384	55.068	1399
K080550RPM	K08 1 3/32" x 55 3/4" - Black	8	55.13	1400	55.694	1415
K080560RPM	K08 1 3/32" x 56 5/8" - Black	8	56.09	1425	56.658	1439
K080600RPM	K08 1 3/32" x 60 5/8" - Black	8	60	1524	60.565	1538
K080605RPM	K08 1 3/32" x 61 1/8" - Black	8	60.59	1539	61.151	1553
K080610RPM	K08 1 3/32" x 61 3/4" - Black	8	61.22	1555	61.787	1569
K080615RPM	K08 1 3/32" x 62 1/8" - Black	8	61.51	1562	62.076	1577
K080630RPM	K08 1 3/32" x 63 5/8" - Black	8	63.04	1601	63.606	1616
K080640RPM	K08 1 3/32" x 64 1/2" - Black	8	64	1626	64.5	1638
K080645RPM	K08 1 3/32" x 65 1/4" - Black	8	64.67	1643	65.237	1657
K080653RPM	K08 1 3/32" x 65 7/8" - Black	8	65.36	1660	65.922	1674
K080655RPM	K08 1 3/32" x 66 1/4" - Black	8	65.7	1669	66.27	1683
K080660RPM	K08 1 3/32" x 66 1/2" - Black	8	65.99	1676	66.559	1691
K080661RPM	K08 1 3/32" x 66 3/4" - Black	8	66.14	1680	66.75	1695
K080670RPM	K08 1 3/32" x 67 1/2" - Black	8	66.98	1701	67.543	1716
K080675RPM	K08 1 3/32" x 68 1/16" - Black	8	67.49	1714	68.05	1728
K080680RPM	K08 1 3/32" x 68 5/8" - Black	8	68	1727	68.567	1742
K080685RPM	K08 1 3/32" x 69 1/8" - Black	8	68.57	1742	69.133	1756
K080690RPM	K08 1 3/32" x 69 5/8" - Black	8	69.01	1753	69.57	1767
K080700RPM	K08 1 3/32" x 70 1/2" - Black	8	69.88	1775	70.445	1789
K080708RPM	K08 1 3/32" x 71 1/4" - Black	8	70.74	1797	71.3	1811
K080716RPM	K08 1 3/32" x 72 1/8" - Black	8	71.53	1817	72.095	1831
K080751RPM	K08 1 3/32" x 75 5/8" - Black	8	75.08	1907	75.63	1921
K080765RPM	K08 1 3/32" x 77" - Black	8	76.48	1943	77.046	1957
K080780RPM	K08 1 3/32" x 78 5/8" - Black	8	78.02	1982	78.586	1996
K080794RPM	K08 1 3/32" x 80" - Black	8	79.45	2018	80	2032
K080797RPM	K08 1 3/32" x 80 1/8" - Black	8	79.62	2022	80.187	2037
K080810RPM	K08 1 3/32" x 82 5/8" - Black	8	81.04	2058	81.608	2073
K080817RPM	K08 1 3/32" x 82 3/8" - Black	8	81.77	2077	82.34	2091
K080828RPM	K08 1 3/32" x 83 3/8" - Black	8	82.87	2105	83.38	2118
K080842RPM	K08 1 3/32" x 84 3/4" - Black	8	84.23	2139	84.799	2154
K080845RPM	K08 1 3/32" x 85 1/8" - Black	8	84.54	2147	85.13	2162
K080850RPM	K08 1 3/32" x 85 3/8" - Black	8	85.08	2161	85.375	2175
K080852RPM	K08 1 3/32" x 85 3/4" - Black	8	85.24	2165	85.75	2178
K080855RPM	K08 1 3/32" x 86 1/8" - Black	8	85.56	2173	86.121	2187
K080865RPM	K08 1 3/32" x 87 1/8" - Black	8	86.53	2198	87.125	2212
K080885RPM	K08 1 3/32" x 89 1/8" - Black	8	88.54	2249	89.105	2263
K080889RPM	K08 1 3/32" x 89 1/2" - Black	8	88.9	2258	89.5	2272
K080893RPM	K08 1 3/32" x 89 7/8" - Black	8	89.28	2268	89.849	2282
K080903RPM	K08 1 3/32" x 90 7/8" - Black	8	90.31	2294	90.873	2308
K080910RPM	K08 1 3/32" x 91 5/8" - Black	8	91.02	2312	91.59	2326
K080915RPM	K08 1 3/32" x 92 1/8" - Black	8	91.52	2325	92.125	2340
K080922RPM	K08 1 3/32" x 92 3/4" - Black	8	92.16	2341	92.721	2355



PART NUMBER	PRODUCT DESCRIPTION	NUMBER OF RIBS	EFFECTIVE LENGTH (IN)	EFFECTIVE LENGTH (MM)	OUTSIDE CIRCUMFERENCE (IN)	OUTSIDE CIRCUMFERENCE (MM)
K080956RPM	K08 1 3/32" x 96 1/4" - Black	8	95.67	2430	96.25	2444
K081000RPM	K08 1 3/32" x 100 5/8" - Black	8	100.01	2540	100.58	2555
K081088RPM	K08 1 3/32" x 109 3/8" - Black	8	108.8	2764	109.375	2778
K100234RPM	K10 1 3/8" x 24" - Black	10	23.4	594	24	608
K100475RPM	K10 1 3/8" x 48" - Black	10	47.5	1207	48	1219
K100525RPM	K10 1 3/8" x 53" - Black	10	52.5	1334	53	1346
K100529RPM	K10 1 3/8" x 53 3/8" - Black	10	52.95	1345	53.38	1356
K100535RPM	K10 1 3/8" x 54" - Black	10	53.48	1358	54.044	1373
K100540RPM	K10 1 3/8" x 54 1/2" - Black	10	53.96	1371	54.521	1385
K100563RPM	K10 1 3/8" x 56 7/8" - Black	10	56.29	1430	56.857	1444
K100564RPM	K10 1 3/8" x 57" - Black	10	56.45	1434	57	1448
K100570RPM	K10 1 3/8" x 57 1/2" - Black	10	56.99	1448	57.553	1462
K100572RPM	K10 1 3/8" x 57 7/8" - Black	10	57.25	1454	57.88	1469
K100575RPM	K10 1 3/8" x 58 1/8" - Black	10	57.51	1461	58.07	1475
K100576RPM	K10 1 3/8" x 58 1/4" - Black	10	57.68	1465	58.25	1480
K100579RPM	K10 1 3/8" x 58 1/2" - Black	10	57.96	1472	58.527	1487
K100582RPM	K10 1 3/8" x 58 3/4" - Black	10	58.2	1478	58.75	1492
K100594RPM	K10 1 3/8" x 60" - Black	10	59.4	1509	59.97	1523
K100600RPM	K10 1 3/8" x 60 1/2" - Black	10	60	1524	60.5	1538
K100607RPM	K10 1 3/8" x 61 1/4" - Black	10	60.75	1543	61.31	1557
K100618RPM	K10 1 3/8" x 62 3/8" - Black	10	61.83	1570	62.4	1585
K100637RPM	K10 1 3/8" x 64 1/4" - Black	10	63.74	1619	64.302	1633
K100640RPM	K10 1 3/8" x 64 5/8" - Black	10	64.07	1627	64.63	1642
K100655RPM	K10 1 3/8" x 66" - Black	10	65.5	1664	66.062	1678
K100665RPM	K10 1 3/8" x 67 1/8" - Black	10	66.53	1690	67.095	1704
K100670RPM	K10 1 3/8" x 67 1/2" - Black	10	66.98	1701	67.55	1716
K100702RPM	K10 1 3/8" x 70 7/8" - Black	10	70.27	1785	70.875	1800
K100719RPM	K10 1 3/8" x 72 3/8" - Black	10	71.87	1825	72.433	1840
K100731RPM	K10 1 3/8" x 73 5/8" - Black	10	73.09	1856	73.656	1871
K100772RPM	K10 1 3/8" x 77 3/4" - Black	10	77.2	1961	77.75	1975
K100789RPM	K10 1 3/8" x 79 1/2" - Black	10	78.9	2004	79.47	2019
K100816RPM	K10 1 3/8" x 82 1/8" - Black	10	81.57	2072	82.14	2086
K100837RPM	K10 1 3/8" x 84 1/4" - Black	10	83.66	2125	84.25	2140
K100840RPM	K10 1 3/8" x 84 5/8" - Black	10	84.06	2135	84.625	2149
K100878RPM	K10 1 3/8" x 88 3/8" - Black	10	87.82	2231	88.38	2245
K100891RPM	K10 1 3/8" x 89 3/4" - Black	10	89.13	2264	89.69	2278
K101010RPM	K10 1 3/8" x 101 1/2" - Black	10	101	2565	101.5	2579
K101065RPM	K10 1 3/8" x 107 1/8" - Black	10	106.53	2706	107.125	2720
K101078RPM	K10 1 3/8" x 108 3/8" - Black	10	107.87	2740	108.375	2753
K110815RPM	K11 1 1/2" x 82" - Black	11	81.46	2069	82	2083
K110825RPM	K11 1 1/2" x 83 1/8" - Black	11	82.59	2098	83.13	2111
K110841RPM	K11 1 1/2" x 84 3/4" - Black	11	84.16	2138	84.75	2153
K120559RPM	K12 1 21/32" x 56 1/2" - Black	12	55.95	1421	56.519	1436
K120594RPM	K12 1 21/32" x 60" - Black	12	59.4	1509	59.97	1523
K120606RPM	K12 1 21/32" x 61 1/8" - Black	12	60.59	1539	61.16	1553
K120610RPM	K12 1 21/32" x 61 3/4" - Black	12	61.22	1555	61.79	1569
K120620RPM	K12 1 21/32" x 62 3/4" - Black	12	62.08	1577	62.74	1594
K120640RPM	K12 1 21/32" x 64 3/4" - Black	12	64.07	1627	64.73	1644



PART NUMBER	PRODUCT DESCRIPTION	NUMBER OF RIBS	EFFECTIVE LENGTH (IN)	EFFECTIVE LENGTH (MM)	OUTSIDE CIRCUMFERENCE (IN)	OUTSIDE CIRCUMFERENCE (MM)
K120650RPM	K12 1 21/32" x 65 5/8" - Black	12	64.97	1650	65.63	1667
K120655RPM	K12 1 21/32" x 66" - Black	12	65.5	1664	66	1676
K120660RPM	K12 1 21/32" x 66 5/8" - Black	12	65.99	1676	66.65	1693
K120665RPM	K12 1 21/32" x 67" - Black	12	66.5	1689	67	1702
K120670RPM	K12 1 21/32" x 67 5/8" - Black	12	66.98	1701	67.64	1718
K120675RPM	K12 1 21/32" x 68" - Black	12	67.5	1715	68	1727
K120680RPM	K12 1 21/32" x 68 1/2" - Black	12	68	1727	68.5	1740
K120702RPM	K12 1 21/32" x 70 3/4" - Black	12	70.23	1784	70.793	1798
K120815RPM	K12 1 21/32" x 82" - Black	12	81.46	2069	82.026	2083
K120842RPM	K12 1 21/32" x 84 3/4" - Black	12	84.23	2139	84.799	2154
K120864RPM	K12 1 21/32" x 86 7/8" - Black	12	86.36	2194	86.93	2208
K120878RPM	K12 1 21/32" x 88 3/8" - Black	12	87.82	2231	88.387	2245
K120891RPM	K12 1 21/32" x 89 5/8" - Black	12	89.12	2264	89.625	2278
K120903RPM	K12 1 21/32" x 90 7/8" - Black	12	90.31	2294	90.873	2308
K120924RPM	K12 1 21/32" x 93 1/8" - Black	12	92.5	2350	93.07	2364
K120931RPM	K12 1 21/32" x 93 3/4" - Black	12	93.19	2367	93.755	2381
K120964RPM	K12 1 21/32" x 97" - Black	12	96.41	2449	96.98	2463
K120979RPM	K12 1 21/32" x 98 1/8" - Black	12	97.54	2478	98.11	2492
K121039RPM	K12 1 21/32" x 104 1/2" - Black	12	103.94	2640	104.5	2654
K140234RPM	K14 1 15/16" x 24" - Black	14	23.4	594	24	610
K140580RPM	K14 1 15/16" x 58 5/8" - Black	14	58.09	1475	58.655	1490
K140618RPM	K14 1 15/16" x 62 3/8" - Black	14	61.83	1570	62.395	1585
K140627RPM	K14 1 15/16" x 63 3/8" - Black	14	62.76	1594	63.33	1609
K140662RPM	K14 1 15/16" x 66 3/4" - Black	14	66.19	1681	66.755	1696
K140682RPM	K14 1 15/16" x 68 3/4" - Black	14	68.18	1732	68.745	1746

For more information on any of these products, please contact your Gates Sales Representative.

© 2017 Gates Corporation. All rights reserved.  
428-3291 REV 5/17



GATES.COM

Follow GatesRPM

Follow GatesAuto

