

FO20H OIL SUCTION & DELIVERY HOSE 20 BAR



HIGH PRESSURE OILFIELD HOSE

APPLICATION

Delivery of gasoline, diesel and fuel-oil with aromatic content up to 50%, seawater, mud and general applications

TEMPERATURE (-30°C to +100°C) (-22°F to +212°F)

CONSTRUCTION Tube Black NBR Rubber

Reinforcement High Tensile Synthetic Textile with Embedded Steel Helix Wire & Anti-static Copper Wire

Cover Black CR/BR blend rubber
Abrasion, Ozone, Weather, Heat & Oil Resistant

STANDARDS Additional standards/certifications available upon customer request

COUPLINGS Crimped



ID		OD		WORKING PRESSURE		BURST PRESSURE		MBR		WEIGHT		MAX HOSE LENGTH		REFERENCE CODE	REFERENCE NUMBER
inch	mm	inch	mm	bar	psi	bar	psi	inch	mm	kg/m	lb/ft	m	ft		
1 1/2	38	2.05	52	20	300	80	1200	7	0.2	1.7	1.1	60	196	H2F020H24	-
2	51	2.76	70	20	300	80	1200	12	0.3	2.7	1.8	60	196	H2F020H32	-
3	76	3.90	99	20	300	80	1200	15	0.4	4.1	2.8	60	196	H2F020H48	-
3 1/2	89	4.49	114	20	300	80	1200	18	0.5	5.4	3.6	60	196	H2F020H56	-
4	102	4.92	125	20	300	80	1200	20	0.5	6.6	4.4	60	196	H2F020H64	-
5	127	6.06	154	20	300	80	1200	25	0.6	10.0	6.7	60	196	H2F020H80	-
6	152	7.13	181	20	300	80	1200	30	0.8	12.8	8.6	60	196	H2F020H96	-
8	203	9.25	235	20	300	80	1200	40	1.0	18.6	12.5	60	196	H2F020H128	-
10	254	11.30	287	20	300	80	1200	53	1.4	27.0	18.1	60	196	H2F020H160	-

Gates Corporation is a leading manufacturer of application-specific fluid power and power transmission solutions. At Gates, we are driven to push the boundaries of materials science to engineer products that continually exceed expectations.