

WT20H POTABLE WATER SUCTION & DELIVERY HOSE 20 BAR



HIGH PRESSURE OILFIELD HOSE

APPLICATION

Potable Water Transfer

TEMPERATURE (-35°C to +100°C) (-31°F to +212°F)

CONSTRUCTION Tube White Color Non-Toxic, Taste & Odour Free, Natural Rubber

Reinforcement High Tensile Synthetic Textile

Cover Orange NBR/PVC - Abrasion, Ozone & Hydrocarbon Resistant

STANDARDS Additional standards/certifications available upon customer request

COUPLINGS Crimped



ID		OD		WORKING PRESSURE		BURST PRESSURE		MBR		WEIGHT		MAX HOSE LENGTH		REFERENCE CODE	REFERENCE NUMBER
inch	mm	inch	mm	bar	psi	bar	psi	inch	mm	kg/m	lb/ft	m	ft		
1 1/2	38	25.50	51	20	300	80	1200	7	0.2	1.7	1.1	60	196	H2WT20H24	-
2	51	35.00	70	20	300	80	1200	12	0.3	2.7	1.8	60	196	H2WT20H32	-
3	76	49.50	99	20	300	80	1200	15	0.4	4.9	3.3	60	196	H2WT20H48	-
4	102	63.50	127	20	300	80	1200	20	0.5	7.5	5.0	60	196	H2WT20H64	-
5	127	77.50	155	20	300	80	1200	25	0.6	11.0	7.4	60	196	H2WT20H80	-
6	152	91.00	182	20	300	80	1200	30	0.8	15.4	10.3	60	196	H2WT20H96	-

Gates Corporation is a leading manufacturer of application-specific fluid power and power transmission solutions. At Gates, we are driven to push the boundaries of materials science to engineer products that continually exceed expectations.