BP10H BULK PRODUCT SUCTION& DELIVERY HOSE 10 BAR



HIGH PRESSURE OILFIELD HOSE

APPLICATION

Heavy duty barite and cement

TEMPERATURE	(-35°C to +85°C) (-31°F to +185°F)						
CONSTRUCTION	Tube	Black SBR/NR Blend Rubber					
	Reinforcement	High Tensile Synthetic Textile with Embedded Steel Helix Wire					
	Cover	Black IR/BR Blend Rubber Abrasion, Ozone & Weather Resistant					
STANDARDS	Additional standards/certifications available upon customer request						
COUPLINGS	Crimped						













ID		OD		WORKING PRESSURE		BURST PRESSURE		MBR		WEIGHT		MAX HOSE LENGTH		REFERENCE CODE	REFERENCE NUMBER
inch	mm	inch	mm	bar	psi	bar	psi	inch	mm	kg/m	lb/ft	m	ft		
4	102	4.88	124	10	150	40	600	24	0.6	6.5	4.4	60	196	H2BP10H64	-
5	127	5.87	149	10	150	40	600	30	0.8	8.0	5.4	60	196	H2BP10H80	-

Gates Corporation is a leading manufacturer of application-specific fluid power and power transmission solutions. At Gates, we are driven to push the boundaries of materials science to engineer products that continually exceed expectations.