## **CEMENTING 5000**

## HIGH PRESSURE OILFIELD HOSE



## **APPLICATION**

Used as a flexible connection between the cementing pump manifold and cementing head for conveyance of cement slurries at high pressure. The UltraBrasion $^{\text{TM}}$  cover is designed to handle external damage from abrasion, corrosion, gouges, oil and weather.

TEMPERATURE	(-20°C to +82°C) (-4°F to +180°F)					
CONSTRUCTION	Tube	Type C3 (Modified Nitrile)				
	Reinforcement	Multiple layers of textile fabric and steel cable				
	Cover	Type C4 (Modified Nitrile)				
FSL RATING	FSL 0 all sizes					
STANDARDS	API 7K 6th Edition, ISO 47693, ABS Type Approvals					
COUPLINGS	Swaged Couplings					













ID		OD		WORKING PRESSURE		BURST PRESSURE		MBR		WEIGHT		MAX HOSE LENGTH
inch	mm	inch	mm	bar	psi	bar	psi	inch	mm	kg/ft	lb/ft	ft
2 1/2	64	4.14	105	345	5000	860	12500	36	914	4	10	90
3	76	4.61	117	345	5000	860	12500	48	1219	5	11	90
3 1/2	89	5.25	133	345	5000	860	12500	54	1372	6	13	90
4	102	5.61	142	345	5000	860	12500	54	1372	6	13	90

Gates Corporation is a leading manufacturer of application-specific fluid power and power transmission solutions. At Gates, we are driven to push the boundaries of materials science to engineer products that continually exceed expectations.