CHOKE & KILL 10000 MEGASHIELD™

HIGH PRESSURE OILFIELD HOSE



APPLICATION

Flexible Choke and Kill lines used on Blow Out Preventer (BOP) system to control well pressure during the drilling process. MegaShieldTM hoses can be used with or without stainless steel armor. Hoses are manufactured to handle up to 20% hydrogen sulfide H_2S for 1 hour at 200°F (93°C) at rated working pressure.

TEMPERATURE	(-30°C to +93°C)(-20°F to +200°F)					
CONSTRUCTION	Tube	Type V (Flouroelastomer)				
	Reinforcement	Multiple layers of textile fabric and steel cable				
	Cover	Type C4 (Modified Nitrile)				
STANDARDS	Hose survived (Lloyds OD/1000/499) at 704°C for 22 minutes					
COUPLINGS	Swaged Couplings					













ID		OD		WORKING PRESSURE		BURST PRESSURE		MBR		WEIGHT		MAX HOSE LENGTH
inch	mm	inch	mm	bar	psi	bar	psi	inch	mm	kg/ft	lb/ft	ft
2 1/2	64	5.51	140	690	10000	1551	22500	48	1219	10	23	90
3	76	6.06	154	690	10000	1551	22500	48	1219	12	26	90
3 1/2	89	6.78	172	690	10000	1551	22500	54	1371	14	30	90

Gates Corporation is a leading manufacturer of application-specific fluid power and power transmission solutions. At Gates, we are driven to push the boundaries of materials science to engineer products that continually exceed expectations.