ROTARY DRILLING AND VIBRATOR, MUD DELIVERY AND CEMENT HOSES GRADE C



HIGH PRESSURE OILFIELD HOSE

APPLICATION

Flexible connection between standpipe and top drive/swivel or between pump and standpipe for pumping mud at extra high pressure in oil drilling and exploration work.

TEMPERATURE	(-25°C to +100°C) (-13°F to +212°F)					
CONSTRUCTION	Tube	Black Nitrile Rubber				
	Reinforcement	Multiple layers of textile fabric and steel cable				
	Cover	PCR				
FSL RATING	FSL 1 for all sizes					
STANDARDS	API 7K 6th Edition, ISO 47693, ABS Type Approvals					
COUPLINGS	Bonded					













ID		OD		WORKING PRESSURE		BURST PRESSURE		MBR		WEIGHT		MAX HOSE LENGTH		REFERENCE CODE	REFERENCE NUMBER
inch	mm	inch	mm	bar	psi	bar	psi	inch	mm	kg/m	lb/ft	m	ft		
4	102	6.30	160	275	4000	690	10000	55	1.4	28.9	63.7	62	203	APO4C	842

Gates Corporation is a leading manufacturer of application-specific fluid power and power transmission solutions. At Gates, we are driven to push the boundaries of materials science to engineer products that continually exceed expectations.