ROTARY DRILLING AND VIBRATOR, MUD DELIVERY AND CEMENT HOSES 10,000 & 15000 CEMENT



HIGH PRESSURE OILFIELD HOSE

APPLICATION

Used as a flexible connection between the cementing pump manifold and cementing head for conveyance of cement slurries at high pressure.

TEMPERATURE	(-25°C to +100°C) (-13°F to +212°F)					
CONSTRUCTION	Tube	Black Nitrile Rubber				
	Reinforcement	Multiple layers of textile fabric and steel cable				
	Cover	PCR				
STANDARDS	API 7K 6th Edition FSL 0, ISO 47693, ABS Type Approvals					
COUPLINGS	Bonded					













ID		0	OD I		WORKING PRESSURE		BURST PRESSURE		MBR		WEIGHT		HOSE GTH	REFERENCE CODE	REFERENCE NUMBER
inch	mm	inch	mm	bar	psi	bar	psi	inch	mm	kg/m	lb/ft	m	ft		
	10,000 Cement														
3	76	5.59	142	690	10000	1550	22500	47	1.2	34.7	76.5	62	203	AP03F	765
	15,000 Cement														
2	51	4.69	119	1034	15000	2327	33750	55	1.4	41.0	90.4	62	203	AP02G	763
3	76	7.09	180	1034	15000	2327	33750	63	1.6	73.0	160.9	62	203	AP03G	859

Gates Corporation is a leading manufacturer of application-specific fluid power and power transmission solutions. At Gates, we are driven to push the boundaries of materials science to engineer products that continually exceed expectations.