ROTARY VIBRATOR 5000 POWERSPIRAL[™]



O ∕Kg

R

HIGH PRESSURE OILFIELD HOSE

1

5

APPLICATION

 (\rightarrow)

Flexible connection between standpipe and top drive/swivel or between pump and standpipe for pumping mud at extra high pressures in oil drilling and exploration work.

TEMPERATURE	(-20°C to +121°C) (-4°F to +250°F)	
CONSTRUCTION	Tube	Type C2 (Modified Nitrile)
	Reinforcement	High tensile steel wire
	Cover	Type A (Chlorprene)
STANDARDS	NACE MR0175	
COUPLINGS	Crimped GSM	

MAX HOSE WORKING BURST PRESSURE ID 0D MBR WEIGHT PRESSURE LENGTH inch mm inch mm bar psi bar psi inch mm kg/ft lb/ft ft 76 3 3.86 98 345 5000 860 12500 35.0 889 3 7 200

 $\overline{}$

Gates Corporation is a leading manufacturer of application-specific fluid power and power transmission solutions. At Gates, we are driven to push the boundaries of materials science to engineer products that continually exceed expectations.