## WT10S POTABLE WATER DELIVERY HOSE 10 BAR



## HIGH PRESSURE OILFIELD HOSE

## **APPLICATION**

Potable Water Transfer

TEMPERATURE	(-30°C to +100°C) (-22°F to +212°F)						
CONSTRUCTION	Tube	White Color Non-Toxic, Taste & Odour Free, Natural Rubber					
	Reinforcement	High Tensile Synthetic Textile					
	Cover	Orange CR/BR Blend Rubber Abrasion, Ozone & Hydrocarbon Resistant					
STANDARDS	Additional standards/certifications available upon customer request						
COUPLINGS	Crimped						













ID		OD		WORKING PRESSURE		BURST PRESSURE		MBR		WEIGHT		MAX HOSE LENGTH		REFERENCE CODE	REFERENCE NUMBER
inch	mm	inch	mm	bar	psi	bar	psi	inch	mm	kg/m	lb/ft	m	ft		
1 1/2	38	1.97	50	10	150	40	600	8	0.2	1.0	0.7	60	196	H2WT10S24	-
2	51	2.68	68	10	150	40	600	12	0.3	1.9	1.3	60	196	H2WT10S32	-
3	76	3.62	92	10	150	40	600	18	0.5	3.2	2.2	60	196	H2WT10S48	-
4	102	4.69	119	10	150	40	600	24	0.6	4.2	2.8	60	196	H2WT10S64	-
5	127	5.71	145	10	150	40	600	30	0.8	5.4	3.6	60	196	H2WT10S80	-

Gates Corporation is a leading manufacturer of application-specific fluid power and power transmission solutions. At Gates, we are driven to push the boundaries of materials science to engineer products that continually exceed expectations.