

# Belts and Coolant Hose for Farm Tractors and Farm Equipment (1970 And Newer)

## ALLIS-CHALMERS - Continued Farm Equipment, Forage Harvester

### Belts

Application	Mfr. Part No.	Belt No.
<b>880</b>		
Alt.; W/53 1/4" Belt O.C. ....		9530 GS
Alt.; W/54 1/4" Belt O.C. ....		9540 GS
A.C. ....	1148120	9510 GS
Hyd. Pump.....	1173232	9640 GS

## BELARUS

### Tractors Belts

Application	Mfr. Part No.	Belt No.
<b>250</b>		
VLADIMIR 2-CYL. DIESEL ENG. Gen. & Blower.....		7520
<b>250AS</b>		
VLADIMIR 2-CYL. DIESEL ENG. Gen. & Blower.....		7500
<b>310</b>		
BELARUS 4-CYL. DIESEL ENG. Gen. & Blower.....		7500
<b>420A; 420AN</b>		
BELARUS 4-CYL. DIESEL ENG. Alt. & Blower.....	②7525	
<b>500</b>		
BELARUS 4-CYL. DIESEL ENG. Fan & Alt. ....		TR24489 GS
<b>520</b>		
BELARUS 4-CYL. DIESEL ENG. Fan & Alt. ....		TR24489 GS
<b>560</b>		
BELARUS 4-CYL. DIESEL ENG. Fan & Alt. ....		TR24515 GS
Fan & A.C.....		TR22508 GS
Alt.; W/A.C.....		9279 GS
<b>562</b>		
BELARUS 4-CYL. DIESEL ENG. Fan & Alt. ....		TR24515 GS
Fan & A.C.....		TR22508 GS
Alt.; W/A.C.....		9279 GS
<b>611</b>		
BELARUS 4-CYL. DIESEL ENG. Fan & Alt. ....		TR24578 GS
<b>800</b>		
BELARUS 4-CYL. DIESEL ENG. Fan & Alt. ....		7516
Fan & A.C.....		9510 GS
Alt.; W/A.C.....		9270 GS
<b>802</b>		
BELARUS 4-CYL. DIESEL ENG. Fan & Alt. ....		7516
Fan & A.C.....		9510 GS
Alt.; W/A.C.....		9270 GS
<b>822</b>		
BELARUS 4-CYL. DIESEL ENG. Fan & Alt. ....		7516
Fan & A.C.....		9510 GS
Alt.; W/A.C.....		9270 GS
<b>925</b>		
BELARUS 4-CYL. DIESEL ENG. Fan & Alt. ....	17510	9510 GS
A.C., Alt. & Idler.....	17280	9279 GS

## BELARUS - Continued Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
<b>560</b>		
BELARUS 4-CYL. DIESEL ENG.		
Upper.....	>21794	25474
Lower.....	>21145	
By Pass.....	*1" I.D.	
<b>562</b>		
BELARUS 4-CYL. DIESEL ENG.		
Upper.....	>21794	25474
Lower.....	>21145	
By Pass.....	*1" I.D.	
<b>800</b>		
BELARUS 4-CYL. DIESEL ENG.		
Upper.....	>21794	25474
Lower.....	>21145	
By Pass.....	*1" I.D.	
<b>802</b>		
BELARUS 4-CYL. DIESEL ENG.		
Upper.....	>21794	25474
Lower.....	>21145	
By Pass.....	*1" I.D.	
<b>822</b>		
BELARUS 4-CYL. DIESEL ENG.		
Upper.....	>21794	25474
Lower.....	>21145	
By Pass.....	*1" I.D.	
<b>925</b>		
BELARUS 4-CYL. DIESEL ENG.		
Upper.....	20065	25473
<b>M-500; M-520</b>		
BELARUS 4-CYL. DIESEL ENG.		
Upper.....	>20065	
Lower.....	>20945	
By Pass.....	*3/4" I.D.	
<b>XT3</b>		
BELARUS V-6 DIESEL ENG.		
Upper - Eng. To Pipe.....	*1 1/2" I.D.	
Upper - Pipe To Rad.....	*1 1/2" I.D.	
Lower - Eng. To Pipe.....	*2 3/8" I.D.	
Lower - Pipe To Rad.....	*2 3/8" I.D.	
<b>611</b>		
BELARUS V-6 DIESEL ENG.		
Upper.....	*1 3/4" I.D.	
Lower - Eng. To Pipe.....	*1 7/8" I.D.	
Lower - Pipe To Rad.....	*1 1/2" I.D.	
<b>820</b>		
BELARUS 4-CYL. DIESEL ENG.		
Upper.....		25474

### Tractors, Articulated Belts

Application	Mfr. Part No.	Belt No.
<b>1500 (XT3)</b>		
BELARUS V-6 DIESEL ENG.		
Fan.....		②TR24597 GS
Fan To Alt.....		9463 GS
<b>1770</b>		
BELARUS V-6 DIESEL ENG.		
Fan To Alt.....		9451 GS
Fan, Alt. & A.C.....	22490	TR22485 GS
Air Brake Compr.....		TR24449 GS
Fan.....		②TR24597 GS

### Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
<b>1770</b>		
BELARUS V-6 DIESEL ENG.		
Upper.....	*1 5/8" I.D.	
Lower.....	*2 3/8" I.D.	

- ② Two Required.
- ③ Three Required.
- ④ Four Required.
- ⑤ Five Required.
- ⑥ Six Required.
- ✂ Cut To Fit.
- ▲ Durion® Silicone Hose Recommended.
- ✦ Use Notched Belt Only.
- GS Green Stripe® Construction.
- ✦ Green Stripe® 4-Ply Coolant Hose Recommended.
- ✦ Use Wire Inserted Green Stripe® Coolant Hose.
- \* Green Stripe II Straight Coolant Hose Recommended.

For a maintenance free coolant connection, see PowerGrip® SB clamp application section.

# Belts and Coolant Hose for Farm Tractors and Farm Equipment (1970 And Newer)

## BELARUS - Continued Tractors, Compact Utility Belts

Application	Mfr. Part No.	Belt No.
<b>400</b> 4-CYL. DIESEL ENG. Alt. & Blower .....	D37E1308021	②7512
<b>420</b> 4-CYL. DIESEL ENG. Alt. & Blower .....	D37E1308021	②7512

## CASE

### Tractors Belts

Application	Mfr. Part No.	Belt No.
<b>484</b> CASE 179 3-CYL. DIESEL ENG. Fan & Alt.; W/61" Belt O.C..... Fan & Alt.; W/62" Belt O.C.....	3129140R1 3113329R1	9610 GS 9620 GS
<b>730; 740</b> CASE A251G GAS ENG.; CASE A267D DIESEL ENG. Fan & Gen..... P.S.; To Ser. No. 8173400..... P.S.; Ser. No. 8173401 & After...	A21457 A11441 A22765	②9505 GS 7290 7320
<b>770</b> CASE 251B GAS ENG.; CASE 267B DIESEL ENG. Fan & Alt..... A.C.....	A59762	TR22607 GS 9720 GS
<b>830; 840</b> CASE A284G GAS ENG.; CASE A301D DIESEL ENG. Fan & Gen..... P.S.; To Ser. No. 8173400..... P.S.; Ser. No. 8173401 & After...	A21457 A11441 A22765	②9505 GS 7290 7320
<b>870</b> CASE 4-CYL. 336 DIESEL ENG. Fan & Alt..... A.C.....	A59762 A65717	TR22607 GS 9720 GS
<b>930; W-930</b> CASE A377LP L.P.G. ENG.; CASE A401D DIESEL ENG. Fan & Gen..... P.S.....	A21461 A22766	②9490 GS 7300
<b>931CK</b> CASE A377 GAS ENG.; CASE A401 DIESEL ENG. Fan & Gen.; Ser. No. 8253501 & After..... P.S.; Ser. No. 8253501 & After...	A33679 A22766	②9490 GS 7300
<b>940</b> CASE A377LP L.P.G. ENG.; CASE A401D DIESEL ENG. Fan & Gen..... P.S.....	A21461 A22766	②9490 GS 7300
<b>970</b> CASE 401BD DIESEL ENG. Fan & Alt..... A.C.; Ser. No. 8693001 Thru 8705614.....	A65143 A65717	TR22588 GS 9720 GS
<b>990</b> DAVID BROWN DIESEL ENG. Fan & Alt.....	K68073	7465
<b>995</b> DAVID BROWN 4-CYL. DIESEL ENG. Fan & Alt.....	3129139R1	9620 GS
<b>1030; 1030CK</b> CASE A451 6-CYL. DIESEL ENG. Fan & Gen.; Ser. No. 8310335 & Before..... Fan & Gen.; Ser. No. 8310336 & After..... P.S.; Ser. No. 8310335 & Before P.S.; Ser. No. 8310335 & After...	A18426 A57123 A34359 457130	②9530 GS ②TR22534 GS 7550 TR22607 GS

## CASE - Continued Belts - Continued

Application	Mfr. Part No.	Belt No.
<b>1070</b> CASE A451 6-CYL. DIESEL ENG. Fan & Alt.; W/59 1/8" Belt O.C.... Fan & Alt.; W/73 1/4" Belt O.C....	A65143 A62962	TR22588 GS 9730 GS
<b>1090</b> CASE A451 6-CYL. DIESEL ENG. Fan & Alt.; W/59 1/8" Belt O.C.... Fan & Alt.; W/73 1/4" Belt O.C.... A.C.; Ser. No. 8693000 & Before	A65143 A62962 A65717	TR22588 GS 9730 GS 9720 GS
<b>1170</b> CASE A451DT 6-CYL. DIESEL ENG. Fan & Alt.; W/Turbo..... A.C.; W/Turbo.....	A62962	TR22588 GS 9720 GS
<b>1175</b> CASE A451DT 6-CYL. DIESEL ENG. Fan & Alt.....	A65143	TR22588 GS
<b>1190</b> CASE 3-CYL. DIESEL ENG. Fan..... Fan & Hyd. Pump..... Alt..... W.P. & Alt.....	K949311 K949311	7512 ②7425 7320 7512
<b>1194</b> CASE 3-CYL. 164 DIESEL ENG. Fan To Alt..... Fan & P.S.....		7320 ②7430
<b>1200</b> CASE A451 6-CYL. DIESEL ENG. Fan & Gen..... V.P.....	A18426 L10746	②9530 GS 7440
<b>1210</b> DAVID BROWN 4-CYL. DIESEL ENG. Fan & Alt.....	K68073	7465
<b>1270</b> CASE 451BDT 6-CYL. ENG. Fan & Alt..... A.C.....	A65143 A65716	TR22588 GS 9720 GS
<b>1290</b> CASE 4-CYL. DIESEL ENG. Fan & Alt.....	K68073	7465
<b>1294</b> CASE 3.6 L 4-CYL. DIESEL ENG. Fan & Alt.....		7470
<b>1370</b> CASE 504BDT 6-CYL. ENG. Fan & Alt..... A.C.....	A65143 A65716	TR22588 GS 9720 GS
<b>1390</b> CASE 4-CYL. DIESEL ENG. Fan & Alt.....	K68073	7465
<b>1394</b> CASE 3.6 L 4-CYL. DIESEL ENG. Fan & Alt.....		7460
<b>1410; 1412</b> DAVID BROWN 4-CYL. DIESEL ENG. Fan & Alt.....	K68073	7465
<b>1470 TRACTION KING</b> CASE 504 6-CYL. DIESEL ENG. Fan & Alt..... A.C.; Early..... A.C.; W/Idler.....	T38546 T39995 A65716	②TR22657 GS ②9400 GS 9730 GS
<b>1490</b> CASE 4-CYL. DIESEL ENG. Fan & Alt.....	K68073	7465
<b>1494</b> CASE 4-CYL. DIESEL ENG. Fan & Alt.; W/A.C..... Fan & Alt.; W/O A.C..... A.C.....	K308448 K68073 K307429	9490 GS 7465 9400 GS

② Two Required.  
③ Three Required.  
④ Four Required.

⑤ Five Required.  
⑥ Six Required.  
✂ Cut To Fit.

▲ Durion® Silicone Hose Recommended.  
✦ Use Notched Belt Only.  
GS Green Stripe® Construction.

✦ Green Stripe® 4-Ply Coolant Hose Recommended.  
✦ Use Wire Inserted Green Stripe® Coolant Hose.  
\* Green Stripe II Straight Coolant Hose Recommended.

For a maintenance free coolant connection, see PowerGrip® SB clamp application section.