

Thermostats for Trucks, Buses and Off Road Equipment

Application	Conventional/Green Stripe® Thermostats				Green Stripe® Weir Stat® Thermostats			Gasket or Seal
	160°	170°	180°	190°-195°	170°	180°	190°-195°	
CUMMINS - Continued								
MARINE ENGINES								
C SERIES; J SERIES								
C-160-M; C-180-M; JN-130-M	33576 GS	33577 GS	33578 GS		33577 GS	33578 GS	33579 GS	
V-6 SERIES; V-8 SERIES								
V6-215-M; V8-300-M	33576 GS	33577 GS	33578 GS		33577 GS	33578 GS	33579 GS	33601
VT903-M	②33576 GS	②33577 GS	②33578 GS		②33577 GS	②33578 GS	②33579 GS	②33601 & ②>③3635
V504-M; V555-M	33576 GS	33577 GS	33578 GS		33577 GS	33578 GS	33579 GS	33601
V-12 SERIES								
V12-500-M; VT12-635-M; VT12-700-M; VT12-800-M	②33576 GS	②33577 GS	②33578 GS		②33577 GS	②33578 GS	②33579 GS	②33601
DEERE, JOHN; See John Deere								
DETROIT DIESEL								
POWER UNITS								
8.2 L ENG.								
Eng. No. 8G118764; Feb. 1986 Thru 1989			②33728 GS					②>③3635
Before Eng. No. 8G118764; 1980 Thru Feb. 1986			②33498 GS					②>③3635
51 SERIES								
2-51 ENG.; 4-51 ENG.	33176		33178					>③3635
53 SERIES								
2-53 ENG.; 3-53 ENG.; 3-53N ENG.; 4-53 ENG.; 4-53N ENG.; 4-53T ENG.			33208	33209				>③3635
6V-53 ENG.								
Early			②33208	②33209				②>③3635
Late		②33397 GS	②33398 GS					②>③3635
6V-53N ENG.; 8V-53 ENG.; 8V-53N ENG.		②33397 GS	②33398 GS					②>③3635
60 SERIES								
11.1 L ENG.; 12.7 L ENG. 1987 & Newer						②33599 GS		②33635
71 SERIES								
2-71 ENG.	33176		33178					>③3635
3-71 ENG.; 4-71 ENG.; 4-71E ENG.; 4-71N ENG.; 4-71T ENG.; 6-71NE ENG.;								
6-71M ENG.; 6-71T ENG.								
W/Std. Cool.; W/O By Pass Control	33386 GS	33387 GS	33388 GS					>③3635
4-71 TWIN ENG.; 6-71 TWIN ENG.								
W/Std. Cool.; W/O By Pass Control	②33386 GS	②33387 GS	②33388 GS					②>③3635
6-110 ENG.								
Eng. No. 6B17256 & After	②33576 GS	②33577 GS	②33578 GS		②33577 GS	②33578 GS	②33579 GS	②33601 & ②>③3635
Twin Eng. No. 6B17256 & After	④33576 GS	④33577 GS	④33578 GS		④33577 GS	④33578 GS	④33579 GS	④33601 & ④>③3635
6-71 QUAD ENG.								
W/Std. Cool.; W/O By Pass Control	④33386 GS	④33387 GS	④33388 GS					④>③3635
6-71 ENG.								
W/Std. Cool.; W/O By Pass Control; When Used in GMC Coaches Only	33386 GS	33387 GS	33388 GS					>③3635

② Two Required.
③ Three Required.
④ Four Required.

⑤ Five Required.
⑥ Six Required.
⑦ Seven Required.

⑧ Eight Required.
□ As Required.
> Cut To Fit.

GS Green Stripe Thermostat
* OEM Specifies 192° Thermostat.

® Weir Stat is a Registered Trademark of Standard-Thompson.

Thermostats for Trucks, Buses and Off Road Equipment

Application	Conventional/Green Stripe® Thermostats				Green Stripe® Weir Stat® Thermostats			Gasket or Seal
	160°	170°	180°	190°-195°	170°	180°	190°-195°	
DETROIT DIESEL - Continued								
POWER UNITS - Continued								
71 SERIES - Continued								
W/Part No. 5178833		33447 GS						>€33635
W/Part No. 5133358			33448 GS					>€33635
6-71E ENG.; 6-71N ENG.; 6-71SE ENG.; 6-71T ENG.								
W/Std. Cool.; W/O By Pass Control: When Used in GMC Coaches Only	33386 GS	33387 GS	33388 GS					>€33635
6V-71 ENG.; 8V-71 ENG.								
Exc. 7000 Coach, GMC Trucks & Coaches 1964 & Newer	②33576 GS	②33577 GS	②33578 GS		②33577 GS	②33578 GS	②33579 GS	②33601 & ②>€33635
W/Part No. 5178833		②33447 GS						②>€33635
W/Part No. 5133358			②33448 GS					②>€33635
6V-71N ENG.; 6V-71NE ENG.; 8V-71N ENG.; 8V-71NE ENG.								
Exc. 7000 Coach, GMC Trucks & Coaches 1964 & Newer	②33576 GS	②33577 GS	②33578 GS		②33577 GS	②33578 GS	②33579 GS	②33601 & ②>€33635
12V-71 ENG.								
.....	④33576 GS	④33577 GS	④33578 GS		④33577 GS	④33578 GS	④33579 GS	④33601 & ④>€33635
W/Part No. 5178833		②33447 GS						④>€33635
W/Part No. 5133358			④33448 GS					④>€33635
12V-71N ENG.; 16V-71 ENG.; 16V-71T ENG.								
.....	④33576 GS	④33577 GS	④33578 GS		④33577 GS	④33578 GS	④33579 GS	④33601 & ④>€33635
12V-71 TWIN ENG.; 12V-71N TWIN ENG.; 16V-71 TWIN ENG.; 16V-71N TWIN ENG.; 16V-71T TWIN ENG.								
.....	⑥33576 GS	⑥33577 GS	⑥33578 GS		⑥33577 GS	⑥33578 GS	⑥33579 GS	⑥33601 & ⑥>€33635
92 SERIES								
6V-92 ENG.; 6V-92T ENG.; 8V-92 ENG.; 8V-92T ENG.; 16V-92 ENG.; 16V-92T ENG.								
.....	33576 GS	33577 GS	33578 GS		33577 GS	33578 GS	33579 GS	33601 & >€33635
149 SERIES								
16V-149 ENG.								
.....	⑥33576 GS	⑥33577 GS	⑥33578 GS		⑥33577 GS	⑥33578 GS	⑥33579 GS	⑥33601 & ⑥>€33635
DODGE								
MEDIUM AND HEAVY DUTY TRUCKS AND BUSES - GASOLINE UNITS								
1978-1969								
6-CYL. 225 ENG.								
.....	33006		33008	33009				33624
V-8 ENG.								
Exc. 361, 413 Eng.	33036		33038	33039				33625
1968-1963								
6-CYL. 170 ENG.; 6-CYL. 225 ENG.								
.....	33006		33008	33009				33624
V-8 318 ENG.; V-8 361 ENG.; V-8 383 ENG.; V-8 413 ENG.								
.....	33036		33038	33039				33625
1962-1961								
6-CYL. 170 ENG.; 6-CYL. 225 ENG.								
.....	33006		33008	33009				33624
6-CYL. 251 ENG.								
.....	33036		33038	33039				33625

② Two Required. ⑤ Five Required.
 ③ Three Required. ⑥ Six Required.
 ④ Four Required. ⑦ Seven Required.
 ⑧ Weir Stat is a Registered Trademark of Standard-Thompson.

⑧ Eight Required.
 □ As Required.
 >€ Cut To Fit.

GS Green Stripe Thermostat
 * OEM Specifies 192° Thermostat.