

# Belts and Coolant Hose for Farm Tractors and Farm Equipment (1969 And Older)

## FORD - Continued

### Coolant Hose - Continued

Application	Molded or Strt.	Vulco-Flex®
<b>4030</b>		
<b>FORD 3-CYL. DIESEL ENG.</b>		
Lower.....	② 1 1/2" I.D.	
<b>4230; 5530</b>		
<b>FIAT 8045.06 4-CYL. DIESEL ENG.</b>		
Lower - Eng. To Pipe.....	✦ 1 1/2" I.D.	
Lower - Pipe To Rad.....	✦ 1 1/2" I.D.	
<b>5000</b>		
<b>DIESEL ENG.</b>		
Upper.....	✧ 21794	25480(A,B)
<b>GAS ENG.</b>		
Upper.....		25480
<b>5100 SERIES</b>		
<b>256D ENG.; 256DT ENG.; 256G ENG.</b>		
Upper.....	✧ 20065	25526
Lower.....		26502
<b>7100 SERIES</b>		
<b>256D ENG.; 256DT ENG.; 256G ENG.</b>		
Upper.....	✧ 20065	25526
<b>5200 SERIES; 7200 SERIES</b>		
<b>256D ENG.; 256DT ENG.; 256G ENG.</b>		
Upper.....		25480
<b>6000 SERIES</b>		
Upper.....		25480
Lower.....	1 3/4" I.D.	
<b>6500</b>		
<b>DIESEL ENG.</b>		
Upper.....	✧ 21794	25474
Lower.....		26502
<b>7000 SERIES</b>		
<b>256D ENG.; 256DT ENG.; 256G ENG.</b>		
Upper.....	✧ 21794	25480
<b>7500 SERIES</b>		
<b>4-CYL. DIESEL ENG.</b>		
Upper.....	✧ 21794	25477
Lower.....		26611
<b>8000 SERIES</b>		
<b>DIESEL ENG.</b>		
Upper; 2-73 & Older.....		26612
Upper; 3-73 & Newer.....		25482
Lower - Eng. To Cooler.....	20206	26501
Lower - Cooler To Rad.....		26514
<b>8670; 8870; 8970</b>		
<b>FORD 6-CYL. DIESEL ENG.</b>		
By Pass.....	1 1/2" I.D.	
<b>9000 SERIES</b>		
<b>DIESEL ENG.</b>		
Upper; 9-72 & Older.....		26612
Upper; 10-72 & Newer.....		25482
Lower - Eng. To Pipe.....	✧ 20046	26602
Lower - Pipe To Cooler.....	✧ 20357	26601
Lower - Cooler To Rad.....	✧ 20206	26507

### Farm Equipment Belts

Application	Mfr. Part No.	Belt No.
<b>16-1 COMBINE; 16-2 COMBINE</b>		
Fan.....	161132	TR22363 GS
<b>611 COMBINE</b>		
Fan.....	EAG 8577 A	7380
W.P. & Gen.....	EAG 8620 B	7360
<b>622 COMBINE</b>		
Fan.....	721305	7695
W.P. & Gen.....	721211	9540 GS
Gov.....		9430 GS
<b>642 COMBINE</b>		
<b>6-CYL. 380 DIESEL ENG.</b>		
Fan & Alt.....		9470 GS

## FORD - Continued

### Belts - Continued

Application	Mfr. Part No.	Belt No.
<b>642 COMBINE - Continued</b>		
<b>V-8 361 ENG.</b>		
Fan & Alt.....	C4TZ 8620 Z	② 9463 GS
Hyd. Pump.....		9490 GS
<b>1118 WINDROWER</b>		
<b>FORD 4 DIESEL ENG.</b>		
Fan & Alt.....		② 9560 GS
A.C.....	851123	9495 GS
<b>1915 HARVESTER</b>		
<b>CATERPILLAR 3306B ENG.</b>		
Fan & A.C.....		② 9775 GS
Alt.....		9490 GS

### Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
<b>622 COMBINE</b>		
Upper.....	20357	
	&	1 3/4" I.D.
Lower.....	20357	
	&	1 3/4" I.D.
<b>642 COMBINE</b>		
<b>6-CYL. 380 DIESEL ENG.</b>		
Upper.....	✧ 20957	
Lower.....	✧ 20957	
By Pass.....		1 7/8" I.D.
<b>V-8 361 GAS ENG.</b>		
Upper - Pipe To Rad.....	✦ 1 3/4" I.D.	
Lower - Eng. To Pipe.....	✦ 2" I.D.	
Lower - Pipe To Heat Exch.....	✧ 20206	
Lower - Heat Exch. To Pipe.....	✦ 2" I.D.	
Lower - Pipe To Rad.....	✦ 2" I.D.	

## FORDSON

### Tractors Belts

Application	Mfr. Part No.	Belt No.
<b>2N; 9N</b>		
Fan & Gen.; Ser. No. 263842 & Before.....	9N 8620 B	TR20451 GS
Fan & Gen.; Ser. No. 263843 & After.....	8N 8620	TR20412 GS
<b>DEXTA-DX</b>		
<b>DIESEL ENG.</b>		
Fan.....	EIADKN 8620 C	9451 GS
<b>MAJOR; POWER MAJOR; SUPER MAJOR</b>		
<b>DIESEL ENG.</b>		
Fan & Gen.; W/45 1/4" Belt O.C.....	EIADKN 8620 C	9451 GS
Fan & Gen.; W/49 3/4" Belt O.C.....	EIADKN 8620 C	TR28492 GS
P.S.....	EIADKN 8620 C	9451 GS

## FOX

### Farm Equipment Belts

Application	Mfr. Part No.	Belt No.
<b>FA FORAGE HARVESTER</b>		
<b>DETROIT DIESEL 4-53 ENG.</b>		
Fan.....		② TR22443 GS
Gen.....	3224367	TR28390 GS
<b>MAX-I FORAGE HARVESTER</b>		
<b>DETROIT DIESEL 6V-53 ENG.</b>		
Fan.....		③ 9510 GS
Gen.....		9365 GS
Hyd. Pump.....		TR22508 GS
<b>MAX-II FORAGE HARVESTER</b>		
<b>DETROIT DIESEL 6V-71 ENG.</b>		
Fan.....		③ 9520 GS

- ② Two Required.      ⑤ Five Required.      ▲ Durion® Silicone Hose Recommended.      ✦ Green Stripe® 4-Ply Coolant Hose Recommended.  
 ③ Three Required.      ⑥ Six Required.      ✦ Use Notched Belt Only.      ✧ Use Wire Inserted Green Stripe® Coolant Hose.  
 ④ Four Required.      ✧ Cut To Fit.      GS Green Stripe® Construction.      \* Green Stripe II Straight Coolant Hose Recommended.

For a maintenance free coolant connection, see PowerGrip® SB clamp application section.

# Belts and Coolant Hose for Farm Tractors and Farm Equipment (1969 And Older)

## FOX - Continued

### Belts - Continued

Application	Mfr. Part No.	Belt No.
<b>MAX-II FORAGE HARVESTER - Continued</b>		
<b>DETROIT DIESEL 6V-71 ENG. - Continued</b>		
Alt./Gen.....	516 10010	9360 <sup>GS</sup>
Hyd. Pump.....	516 12003	TR22508 <sup>GS</sup>
<b>SUPER D FORAGE HARVESTER</b>		
<b>DETROIT DIESEL 4-CYL. ENG.</b>		
Fan.....		9420 <sup>GS</sup>
Gen.....		9375 <sup>GS</sup>
Hyd. Pump.....		9625 <sup>GS</sup>

### Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
<b>FA FORAGE HARVESTER</b>		
<b>DETROIT DIESEL 4-53 ENG.</b>		
Upper.....	20046	26602
Lower - Eng. To Pipe.....	2" I.D.	
Lower - Pipe To Rad.....	2" I.D.	
<b>MAX-I FORAGE HARVESTER</b>		
Upper; Right Side.....		26517
Lower.....		26536
<b>MAX-II FORAGE HARVESTER</b>		
Upper; Left Side.....		26516
Upper; Right Side.....		26517
Lower.....		26536
<b>SUPER D FORAGE HARVESTER</b>		
<b>DETROIT DIESEL 4-CYL. ENG.</b>		
Upper.....		26502
Lower.....		26504

## FREEMAN

### Farm Equipment Belts

Application	Mfr. Part No.	Belt No.
<b>330T BALER</b>		
<b>3.9 L DIESEL ENG.</b>		
Fan & Alt.....	3911560	K080550 <sup>GS</sup>
<b>370 S.P. BALER</b>		
<b>3.9 L DIESEL ENG.</b>		
Fan & Alt.....	3911560	K080550 <sup>GS</sup>
V.P.....		9463 <sup>GS</sup>
<b>370 PULL TYPE BALER</b>		
<b>DEUTZ F4L912 DIESEL ENG.</b>		
Blower.....		7512
Alt.....		7435
<b>4400 HAYSTACKER; 5000 HAYSTACKER; 6000 HAYSTACKER</b>		
<b>5.9 L DIESEL ENG.</b>		
Fan & Alt.; W/55 5/8" Belt O.C....	3911560	K080550 <sup>GS</sup>
Fan & Alt.; W/56 5/8" Belt O.C....	3911588	K080560 <sup>GS</sup>
V.P.....		9463 <sup>GS</sup>
A.C.....		9600 <sup>GS</sup>

### Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
<b>330T BALER</b>		
<b>3.9 L DIESEL ENG.</b>		
Upper.....	>21379	
Lower - Eng. To Pipe.....	>20847	
Lower - Pipe To Rad.....	>21307	
<b>370 S.P. BALER</b>		
<b>3.9 L DIESEL ENG.</b>		
Upper - Eng. To Pipe.....	>21379	26509
Upper - Pipe To Rad.....	❖2" I.D.	
Lower - Eng. To Pipe.....	>20206	
Lower - Pipe To Rad.....	❖2" I.D.	

## FREEMAN - Continued

### Coolant Hose - Continued

Application	Molded or Strt.	Vulco-Flex®
<b>4400 HAYSTACKER; 5000 HAYSTACKER</b>		
<b>5.9 L DIESEL ENG.</b>		
Upper.....		26505
Lower - Eng. To Pipe.....	21307	
Lower - Pipe To Rad.....	>20206	
<b>6000 HAYSTACKER</b>		
<b>5.9 L DIESEL ENG.</b>		
Upper.....		26505
Lower.....		26515

## GEHL

### Farm Equipment Belts

Application	Mfr. Part No.	Belt No.
<b>CHOP KING FORAGE HARVESTER</b>		
<b>WAUKESHA T35GZ ENG.</b>		
Fan.....		②9480 <sup>GS</sup>
Alt.....		9435 <sup>GS</sup>
<b>2650 WINDROWER</b>		
<b>PERKINS DIESEL ENG.</b>		
Fan & Alt.....	02032158	9520 <sup>GS</sup>
A.C.....	02032194	9465 <sup>GS</sup>

### Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
<b>CHOP KING FORAGE HARVESTER</b>		
<b>WAUKESHA 135GZ ENG.</b>		
Upper.....	>20611	26510
Lower.....	2 1/2" I.D.	
<b>2650 WINDROWER</b>		
<b>PERKINS DIESEL ENG.</b>		
Upper.....		25478

## HAHN

### Farm Equipment Belts

Application	Mfr. Part No.	Belt No.
<b>H670 SPRAYER; H770 SPRAYER</b>		
<b>FORD 4-172 GAS ENG.</b>		
J.S.....		9555 <sup>GS</sup>
Fan; From Jackshaft.....		9380 <sup>GS</sup>
W.P. & Alt.....	C6JZ8620B	9420 <sup>GS</sup>
<b>HI-BOY SPRAYER</b>		
<b>FORD 4-172 DIESEL ENG.</b>		
Fan.....		9360 <sup>GS</sup>
W.P. & Alt.....		9420 <sup>GS</sup>
Hyd. Pump.....		7410
J.S.....		9550 <sup>GS</sup>
<b>FORD 4-172 GAS ENG.</b>		
W.P. & Alt.....	C6JZ8620B	9420 <sup>GS</sup>
Fan; From Jackshaft.....	28278	9360 <sup>GS</sup>
<b>SUPER GO-BOY SPRAYER</b>		
<b>FORD 6-CYL. GAS ENG.</b>		
Fan.....	C7JZ8620A	9395 <sup>GS</sup>
Gov.....	C7JZ8620P	7260
<b>880 SPRAYER</b>		
<b>PERKINS 4-CYL. DIESEL ENG.</b>		
Fan & Alt.....	27923	9510 <sup>GS</sup>
C.S. To Pump.....		A46

- ② Two Required.
- ③ Three Required.
- ④ Four Required.
- ⑤ Five Required.
- ⑥ Six Required.
- ❖ Cut To Fit.
- ▲ Durion® Silicone Hose Recommended.
- ✦ Use Notched Belt Only.
- GS Green Stripe® Construction.
- ❖ Green Stripe® 4-Ply Coolant Hose Recommended.
- ② Use Wire Inserted Green Stripe® Coolant Hose.
- \* Green Stripe II Straight Coolant Hose Recommended.

For a maintenance free coolant connection, see PowerGrip® SB clamp application section.