

# Belts and Coolant Hose for Farm Tractors and Farm Equipment (1969 And Older)

## NEW HOLLAND; See Ford Also Farm Equipment Belts

Application	Mfr. Part No.	Belt No.
<b>TR70 COMBINE</b>		
<b>CATERPILLAR 3208 DIESEL ENG.</b>		
Fan & Alt.....		②9520 GS
A.C.....	255630	9505 GS
<b>FORD 6-CYL. 380 DIESEL ENG.</b>		
Fan & Alt.....	261472	9455 GS
A.C.....	255603	7380
Gov.....	266209	9510 GS
<b>TR75 COMBINE</b>		
<b>FORD 5.95 L DIESEL ENG.</b>		
Fan & Alt.....	626658	9590 GS
A.C.....	576776	9545 GS
<b>TR85 COMBINE; TR95 COMBINE</b>		
<b>CATERPILLAR 3208 DIESEL ENG.</b>		
A.C.....		9480 GS
Hyd. Pump.....		②B65
<b>505 BALER</b>		
<b>DEUTZ F3L912 ENG.</b>		
Alt.....	259347	7417
<b>818 FORAGE HARVESTER</b>		
<b>CHEVROLET V-8 ENG.</b>		
Fan & Gen.....	3767013	7585
Fan & Hyd. Pump.....		7541
Gov.....		9505 GS
<b>885 COMBINE; 975 COMBINE</b>		
<b>FORD 6-CYL. 300 (4.9 L) GAS ENG.</b>		
Fan.....		9412 GS
W.P. & Alt.....		7417
W.P. & Hyd. Pump.....		7450
<b>905 WINDROWER</b>		
<b>CONTINENTAL Y112 ENG.</b>		
Fan.....		TR22358 GS
Hyd. Pump.....		TR22534 GS
<b>FORD 4-CYL. ENG.</b>		
Fan & Gen.....		9415 GS
<b>910 WINDROWER; 912 WINDROWER</b>		
<b>FORD 4-CYL. 256 DIESEL ENG.</b>		
Fan & Alt.....		9540 GS
<b>FORD 6-CYL. 250 ENG.</b>		
Fan.....	259346	9480 GS
W.P. & Alt.....	259347	7417
A.C.....	133929	9430 GS
Gov.....	259348	7470
<b>980 COMBINE</b>		
<b>FORD 6-CYL. 300 (4.9 L) GAS ENG.</b>		
Fan.....		9500 GS
W.P. & Alt.....		7430
Gov.....		7250
<b>995 COMBINE</b>		
<b>FORD 6-CYL. 380 DIESEL ENG.</b>		
Fan & Alt.....		②9470 GS
Hyd. Pump.....	230043	B55
<b>FORD V-8 391 GAS ENG.</b>		
Fan & Alt.....	JC475	9476 GS
Hyd. Pump.....	230043	B55
<b>1047 HAYSTACKER</b>		
<b>FORD 6-CYL. 300 (4.9 L) GAS ENG.</b>		
Fan.....		3VX900
W.P. & Alt.....		9420 GS
Gov.....		9290 GS
<b>1048 HAYSTACKER</b>		
<b>FORD V-8 361 GAS ENG.</b>		
W.P. & Alt.....		9463 GS
J.S.....	519145	7420
<b>1049 HAYSTACKER</b>		
<b>FORD V-8 361 GAS ENG.</b>		
Fan.....		7335
Fan & Alt.....	C5TE 8620 A	②9463 GS
Idler.....		7425

## NEW HOLLAND; See Ford Also - Continued Belts - Continued

Application	Mfr. Part No.	Belt No.
<b>1049 SUPER HAYSTACKER</b>		
<b>FORD V-8 361 GAS ENG.</b>		
Fan.....	525351	7355
W.P. & Alt.....		②7440
J.S.....	519145	7420
<b>1112 WINDROWER</b>		
<b>FORD 6-CYL. 250 GAS ENG.</b>		
Fan.....	259346	9480 GS
W.P. & Alt.....	269347	7420
A.C.....	133929	9430 GS
Gov.....	259348	7470
<b>1283 BALER</b>		
<b>FORD 6-CYL. 240 ENG.; FORD 6-CYL. 300 GAS ENG.</b>		
W.P. & Alt.....	384205	9425 GS
W.P. & Governor.....		9455 GS
Hyd. Pump.....	133929	9430 GS
<b>1283 HAYSTACKER</b>		
<b>FORD 6-CYL. 240 GAS ENG.</b>		
Fan.....	C7JZ 8620 H	9405 GS
W.P. & Alt.....		7417
W.P. & Governor.....		7455
Hyd. Pump.....	133929	9430 GS
<b>1400 COMBINE</b>		
<b>FORD 6-CYL. 300 (4.9 L) GAS ENG.</b>		
Fan.....		9412 GS
W.P. & Alt.....		7420
W.P. & Governor.....		7450

## Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
<b>TR70 COMBINE</b>		
<b>CATERPILLAR 3208 DIESEL ENG.</b>		
Upper.....		26512
<b>TR75 COMBINE</b>		
<b>FORD 5.9 L DIESEL ENG.</b>		
Upper.....		26511
<b>TR85 COMBINE; TR95 COMBINE</b>		
<b>CATERPILLAR 3208 DIESEL ENG.</b>		
Upper.....	×21379	26511
<b>818 FORAGE HARVESTER</b>		
<b>CHEVROLET V-8 GAS ENG.</b>		
Upper.....		25476
Lower.....		26511
<b>885 COMBINE; 975 COMBINE</b>		
<b>FORD 6-CYL. 300 (4.9 L) GAS ENG.</b>		
Upper.....	×20611	26510
Lower - Eng. To Pipe.....	×20957	
Lower - Pipe To Rad.....	1 3/4" I.D.	
<b>905 WINDROWER</b>		
<b>CONTINENTAL Y112 ENG.</b>		
Upper.....	1 3/4" I.D.	
Lower.....	1 3/4" I.D.	
<b>FORD 4-CYL. ENG.</b>		
Upper.....	1 1/4" I.D.	
Lower.....	20065	25473
<b>910 WINDROWER; 912 WINDROWER</b>		
<b>FORD 4-CYL. 256 DIESEL ENG.</b>		
Upper.....		25528
Lower.....		26612
<b>FORD 6-CYL. 250 GAS ENG.</b>		
Upper.....		26611
Lower.....		25528
<b>980 COMBINE</b>		
<b>FORD 6-CYL. ENG.</b>		
Upper.....		26611
Lower.....	1 3/4" I.D.	
<b>992 COMBINE</b>		
Upper.....		26603

② Two Required.  
③ Three Required.  
④ Four Required.

⑤ Five Required.  
⑥ Six Required.  
× Cut To Fit.

▲ Durion® Silicone Hose Recommended.  
✦ Use Notched Belt Only.  
GS Green Stripe® Construction.

✦ Green Stripe® 4-Ply Coolant Hose Recommended.  
✦ Use Wire Inserted Green Stripe® Coolant Hose.  
\* Green Stripe II Straight Coolant Hose Recommended.

**For a maintenance free coolant connection, see PowerGrip® SB clamp application section.**

# Belts and Coolant Hose for Farm Tractors and Farm Equipment (1969 And Older)

## NEW HOLLAND; See Ford Also

- Continued

### Coolant Hose - Continued

Application	Molded or Strt.	Vulco-Flex®
<b>992 COMBINE - Continued</b>		
Lower .....		26502
<b>1047 HAYSTACKER</b>		
<b>FORD 6-CYL. ENG.</b>		
Upper - Eng. To Pipe.....		25476
Upper - Pipe To Rad.....	1 1/2" I.D.	
Lower - Eng. To Pipe.....		26611
Lower - Pipe To Rad.....	1 3/4" I.D.	
<b>1048 HAYSTACKER</b>		
<b>FORD V-8 361 GAS ENG.</b>		
Upper - Eng. To Pipe.....		26504
Upper - Pipe To Rad.....	>20957	
Lower - Eng. To Pipe.....		26504
Lower - Pipe To Rad.....		26501
<b>1049 HAYSTACKER</b>		
<b>FORD V-8 361 GAS ENG.</b>		
Upper - Eng. To Pipe.....		26504
Upper - Pipe To Rad.....	>20957	26603
Lower - Eng. To Pipe.....		26504
Lower - Pipe To Rad.....		26501
By Pass .....	5/8" I.D.	
<b>1112 WINDROWER</b>		
<b>FORD 6-CYL. 250 GAS ENG.</b>		
Upper .....		26611
Lower .....		25530
<b>1283 BALER</b>		
<b>FORD 6-CYL. 300 (4.9 L) GAS ENG.</b>		
Upper .....		26502
Lower .....		26510
<b>1283 HAYSTACKER</b>		
<b>FORD 6-CYL. 240 GAS ENG.</b>		
Upper .....		26502
Lower .....		26504
<b>1400 COMBINE</b>		
<b>FORD 6-CYL. 300 (4.9 L) GAS ENG.</b>		
Upper .....	>20046	26502
Lower - Eng. To Pipe.....		26501
Lower - Pipe To Rad.....	1 3/4" I.D.	
<b>FORD 6-CYL. 380 (5.9 L) DIESEL ENG.</b>		
Upper .....	20046	26501
Lower - Eng. To Cooler.....	20357	
Lower - Pipe To Rad.....		26501

## NEW IDEA; See White Also

### Tractors

#### Belts

Application	Mfr. Part No.	Belt No.
<b>185</b>		
<b>CUMMINS C ENG.</b>		
Fan To A.C.....	30331534	9400 GS

### Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
<b>185</b>		
<b>CUMMINS C ENG.</b>		
Upper .....	>20401	26524
Lower - Eng. To Pipe.....	>21473	
Lower - Pipe To Rad.....		26508

## NEW IDEA; See White Also

- Continued

### Farm Equipment Belts

Application	Mfr. Part No.	Belt No.
<b>702 HARVESTER</b>		
<b>GMC V-6 GAS ENG.</b>		
Fan & Alt. ....	703345	9605 GS
Fan & Hyd. Pump .....	703346	②9690 GS
<b>707 COMBINE</b>		
<b>PERKINS 6.436 DIESEL ENG.</b>		
Fan & Alt. ....		②9525 GS
<b>717 COMBINE; 800 COMBINE</b>		
<b>PERKINS ENG.</b>		
W.P. To Alt.....	706239	②9540 GS
<b>800C HARVESTER</b>		
<b>8.3 L DIESEL ENG.</b>		
Fan.....		②9720 GS
A.C.....		9530 GS
<b>803A COMBINE</b>		
<b>ALLIS-CHALMERS 6-CYL. 426 ENG.</b>		
Fan.....		9430 GS
W.P. & Alt.....		TR22625 GS

### Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
<b>702 HARVESTER</b>		
<b>GMC V-6 GAS ENG.</b>		
Upper .....		26511
Lower .....		26536
<b>707 COMBINE</b>		
<b>PERKINS 6.436 DIESEL ENG.</b>		
Upper .....		26505
<b>803A COMBINE</b>		
<b>ALLIS-CHALMERS 6-CYL. 426 ENG.</b>		
Upper .....	②2 1/4" I.D.	
Lower .....	②2 1/4" I.D.	

## OLIVER

### Tractors Belts

Application	Mfr. Part No.	Belt No.
<b>AG6</b>		
<b>CONTINENTAL F226 ENG.</b>		
Fan.....	141106	TR30428 GS
Fan & Gen.....	141199	TR32491 GS
<b>BD; BG; BG-S</b>		
Fan.....	28056	TR28406 GS
Starter Eng. ....	55476	②TR28545 GS
<b>G; GG; H</b>		
Fan.....	112019	TR26341 GS
<b>HG</b>		
Fan.....	117423	TR26366 GS
Fan & Gen.....	117424	TR28406 GS
<b>OC9 CRAWLER</b>		
<b>HERCULES DD198 ENG.</b>		
Fan & Gen.....	606670F	9530 GS
<b>OC12 CRAWLER</b>		
<b>HERCULES DJXC ENG.</b>		
Fan & Gen.....	24270	TR28557 GS
<b>OC15 CRAWLER</b>		
<b>HERCULES DRXC ENG.</b>		
Fan.....		TR34506 GS
<b>SUPER 55; SUPER 66</b>		
Fan & Gen.....	1M372A	7417
Fan & Gen.; W/W.P.....	1M372B	7435
<b>66; 66D; 66HC</b>		
Fan.....	M372	TR24365 GS

- ② Two Required.
- ③ Three Required.
- ④ Four Required.

- ⑤ Five Required.
- ⑥ Six Required.
- > Cut To Fit.

- ▲ Durion® Silicone Hose Recommended.
- ✦ Use Notched Belt Only.
- GS Green Stripe® Construction.

- ✦ Green Stripe® 4-Ply Coolant Hose Recommended.
- ② Use Wire Inserted Green Stripe® Coolant Hose.
- \* Green Stripe II Straight Coolant Hose Recommended.

For a maintenance free coolant connection, see PowerGrip® SB clamp application section.