

Belts and Coolant Hose for Farm Tractors and Farm Equipment (1969 And Older)

TERRA POWER TRACTOR

- Continued

Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
UNIVERSAL U-640 4-CYL. DIESEL ENG.		
Lower	②1 3/8" I.D.	
UNIVERSAL U-1010 6-CYL. DIESEL ENG.		
Lower - Eng. To Pipe.....	1 1/2" I.D.	
Lower - Pipe To Rad.....		25472

TOL

Farm Equipment Belts

Application	Mfr. Part No.	Belt No.
HAS650 TREE TRIMMER; HAS950 TREE TRIMMER LOMBARDINI 3-CYL. DIESEL ENG.		
Fan & Alt.		7265
1200 TREE TRIMMER FORD 6-CYL. DIESEL ENG.		
Fan.....		BX48
W.P.		9451 ^{GS}
W.P. To Alt.....	E4NN10C318AA	9313 ^{GS}
A.C.		9476 ^{GS}

Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
HAS650 TREE TRIMMER LOMBARDINI 3-CYL. DIESEL ENG.		
Lower - Eng. To Pipe.....	>②0065	
Lower - Pipe To Rad.....	>②0065	

VALMET

Tractors Belts

Application	Mfr. Part No.	Belt No.
78 VIKING; 880; 980 MWM 4-CYL. DIESEL ENG.		
Fan & Alt.		9485 ^{GS}

VERSATILE; See Ford Also

Farm Equipment Belts

Application	Mfr. Part No.	Belt No.
330 WINDROWER FORD 4-CYL. 122 ENG.		
Fan & Alt.		②7360
Fan & Gov.....		9500 ^{GS}
Camshaft Drive.....		T013
400 WINDROWER; 440 WINDROWER FORD 6-CYL. 200 ENG.		
Fan & Alt.	C5DE 8620 C	7340
Gov.....	C7ZZ 8620 F	7312

Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
330 WINDROWER FORD 4-CYL. 122 ENG.		
Upper		25476
Lower		25487

VERSATILE; See Ford Also

- Continued

Coolant Hose - Continued

Application	Molded or Strt.	Vulco-Flex®
400 WINDROWER; 440 WINDROWER FORD 6-CYL. 200 ENG.		
Upper; 1970 & Newer.....		25305
Lower; 1969 & Newer.....		25484

WHITE; See Minneapolis-Moline And Agco Allis Also

Tractors Belts

Application	Mfr. Part No.	Belt No.
FIELD BOSS 31 Fan & Alt.	5136710400	9400 ^{GS}
80 CUMMINS 6B5.9 ENG.		
Fan & Alt.	3911563	K080605 ^{GS}
A.C.	303315134	9400 ^{GS}
515 (2/44); 588 4-CYL. GAS ENG.		
Fan & Gen.....	102752A	7450
Hyd. Pump.....	101636A	7430
1265 3-CYL. DIESEL ENG.		
Fan & Alt.	4818920	7455
1355 Fan & Alt.		②9580 ^{GS}
A.C.		③9580 ^{GS}
1365 Fan & Alt.	676865A	7450
1555 DIESEL ENG.		
Fan & Alt.; Ser. No. 160,000 Thru 168,920.....	160610A	9447 ^{GS}
Fan & Alt.; Ser. No. 168,921 & After.....	158679A	7450
A.C.	167897A	7480
GAS ENG. Fan & Alt.; Ser. No. 160,000 Thru 169,845.....	160610A	9447 ^{GS}
Fan & Alt.; Ser. No. 169,846 & After.....	162123A	7445
P.S.	157176AA	7290
A.C.	167897A	7480
LPG ENG. Fan & Alt.; Ser. No. 160,000 Thru 169,386.....	160610A	9447 ^{GS}
Fan & Alt.; Ser. No. 169,387 & After.....	162123A	7445
P.S.	157176AA	7290
A.C.	167897A	7480
1655 DIESEL ENG.		
Fan & Alt.; W/Single Belt.....	157680A	7460
Fan & Alt.; W/Dual Belts; W/46 1/8" Belt O.C.....	162071A	②7460
Fan & Alt.; W/Dual Belts; W/47 1/4" Belt O.C.....		②9470 ^{GS}
P.S.	157177A	7375
A.C.	167897A	7480
GAS ENG. Fan & Alt.	158679A	7450
P.S.	157176AA	7290
A.C.	167897A	7480
1755 DIESEL ENG.		
Fan & Alt.	162071A	②7460
P.S.; W/A.C.	103926A	7250
P.S.; W/O A.C.	168052A	7417

- ② Two Required.
- ③ Three Required.
- ④ Four Required.

- ⑤ Five Required.
- ⑥ Six Required.
- > Cut To Fit.

- ▲ Durion® Silicone Hose Recommended.
- ✦ Use Notched Belt Only.
- ^{GS} Green Stripe® Construction.

- ✦ Green Stripe® 4-Ply Coolant Hose Recommended.
- ✦ Use Wire Inserted Green Stripe® Coolant Hose.
- * Green Stripe II Straight Coolant Hose Recommended.

For a maintenance free coolant connection, see PowerGrip® SB clamp application section.

Belts and Coolant Hose for Farm Tractors and Farm Equipment (1969 And Older)

WHITE; See Minneapolis-Moline And Agco Allis Also - Continued

Belts - Continued

Application	Mfr. Part No.	Belt No.
1755 - Continued		
DIESEL ENG. - Continued		
A.C.	167897A	7480
GAS ENG.		
Fan & Alt.	162071A	②7460
P.S.	157176A	7290
A.C.	167897A	7480
1855		
Fan & Alt.	162071A	②7460
P.S.		7417
A.C.	167897A	7480
1950		
Fan.	155985A	9400 GS
Alt.	157751A	7417
P.S.; W/Single Belt.	157187AA	7320
P.S.; W/Dual Belts.	167910A	②7340
1950T		
Fan & Alt.	104763A	②7460
A.C.; Ser. No. 204001 & After.	167890A	9530 GS
1955		
Fan & Alt.; W/46 1/8" Belt O.C.	157680A	②7460
Fan & Alt.; W/47 5/8" Belt O.C.		②7470
P.S.; W/A.C.	103926A	7250
P.S.; W/O A.C.	168052A	7417
A.C.	167897A	7480
2255		
CATERPILLAR 3150 ENG.; CATERPILLAR 3208 ENG.		
Fan & Alt.	303075087	②9490 GS
P.S.; W/A.C.		7300
A.C.		9640 GS
2-70 FORKLIFT		
DIESEL ENG.		
Fan & Alt.; W/45 5/8" Belt O.C.		7450
Fan & Alt.	162071A	②7460
GAS ENG.		
Fan & Alt.; W/45 5/8" Belt O.C.		7450
Fan & Alt.	158679A	7450
2-78 FORKLIFT; 4-78 FORKLIFT		
DIESEL ENG.		
Fan & Alt.	162071A	②7460
P.S.	157177AA	7375
A.C.	167897A	7480
GAS ENG.		
Fan & Alt.	158679A	7450
P.S.	157176AA	7290
A.C.	167897A	7480
2-115 IND.; 4-115 IND.		
Fan & Alt.; W/40 1/4" Belt O.C.		9400 GS
Fan & Alt.; W/42 4/8" Belt O.C.		7420
P.S.; W/Single Belt.		7315
P.S.; W/Dual Belts.		②7340
4AT1600		
D585 6-CYL. DIESEL ENG.		
Fan & Alt.		②9580 GS
A.C.		9510 GS
Hyd. Pump.		③7480

Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
FIELD BOSS 31; FIELD BOSS 37		
Upper		25251
515; 515(2/44); 588		
4-CYL. GAS ENG.		
Upper	×20433	25473
1265		
3-CYL. DIESEL ENG.		
Upper		26508
Lower - Eng. To Pipe.	1 1/2" I.D.	
Lower - Pipe To Rad.	1 1/2" I.D.	

WHITE; See Minneapolis-Moline And Agco Allis Also - Continued

Coolant Hose - Continued

Application	Molded or Strt.	Vulco-Flex®
1355		
Upper		26612
Lower	2 3/4" I.D.	
By Pass	2" I.D.	
1365		
Upper		26603
Lower - Eng. To Pipe.	1 1/2" I.D.	
Lower - Pipe To Rad.	1 1/2" I.D.	
1555		
DIESEL ENG.		
Lower	1 3/4" I.D.	
GAS ENG.		
Lower - Eng. To Pipe.	1 3/4" I.D.	
Lower - Pipe To Rad.; Ser. No. 160000 Thru 201509.	1 3/4" I.D.	
Lower - Pipe To Rad.; Ser. No. 201510 & After.	2 1/8" I.D.	
1655		
DIESEL ENG.; GAS ENG.		
Upper	×20611	26508
Lower - Eng. To Pipe.	1 3/4" I.D.	
Lower - Pipe To Rad.; Ser. No. 147569 Thru 178173.	1 3/4" I.D.	
Lower - Pipe To Rad.; Ser. No. 178174 & After.	×20520	
1755		
DIESEL ENG.		
Upper; Wheatland.		26508
Lower - Eng. To Pipe.	2 1/8" I.D.	
Lower - Pipe To Rad.	2 1/8" I.D.	
GAS ENG.		
Upper; Row Crop.		26509
Upper; Wheatland.		26508
Lower - Eng. To Pipe.	2 1/8" I.D.	
Lower - Pipe To Rad.	2 1/8" I.D.	
1855; 1955		
DIESEL ENG.; GAS ENG.		
Upper; Row Crop.		26509
Upper; Wheatland.		26508
Lower - Eng. To Pipe.	2 1/8" I.D.	
Lower - Pipe To Rad.	2 1/8" I.D.	
1950		
Upper; Ser. No. 150421 Thru 163701.	×21794	25476
Upper; Ser. No. 163702 & After.	×20046	25478
Lower		26504
1950T		
Upper; Row Crop.	×20611	26509
Upper; Wheatland.		26508
Lower - Eng. To Pipe.	2 1/8" I.D.	
Lower - Pipe To Rad.	2 1/8" I.D.	
2255		
CATERPILLAR 3150 ENG.		
Upper - Eng. To Pipe.	2" I.D.	
Upper - Pipe To Rad.	2" I.D.	
Lower	×20611	26509
CATERPILLAR 3208 ENG.		
Upper - Eng. To Pipe.	2 1/4" I.D.	
Upper - Pipe To Rad.	2 1/4" I.D.	
Lower	×20611	26509
6105		
SLH S.P.A. 1000.6W DIESEL ENG.		
Upper		26507
Lower - Eng. To Pipe.	♣3" I.D.	
Lower - Pipe To Rad.	♣3 1/2" I.D.	
2-70		
265 GAS ENG.		
Upper	×20611	26510
Lower - Eng. To Pipe.	♣2 1/4" I.D.	
Lower - Pipe To Rad.	♣2 1/4" I.D.	

- | | | | |
|-------------------|------------------|--------------------------------------|--|
| ② Two Required. | ⑤ Five Required. | ▲ Durion® Silicone Hose Recommended. | ♣ Green Stripe® 4-Ply Coolant Hose Recommended. |
| ③ Three Required. | ⑥ Six Required. | ✦ Use Notched Belt Only. | ♣ Use Wire Inserted Green Stripe® Coolant Hose. |
| ④ Four Required. | × Cut To Fit. | GS Green Stripe® Construction. | * Green Stripe II Straight Coolant Hose Recommended. |

For a maintenance free coolant connection, see PowerGrip® SB clamp application section.

Belts and Coolant Hose for Farm Tractors and Farm Equipment (1969 And Older)

WHITE; See Minneapolis-Moline And Agco Allis Also - Continued Farm Equipment Belts

Application	Mfr. Part No.	Belt No.
SP7600 COMBINE CHRYSLER V-8 318 ENG. A.C.....		9630 GS
5542 COMBINE CHRYSLER V-8 318 ENG. Fan & Alt.....	9811670	②9540 GS
7300 COMBINE CHRYSLER V-8 318 ENG. Fan & Alt.....	9811683	②9545 GS
7800 COMBINE CHRYSLER V-8 383 ENG. Fan..... W.P. & Alt.....		②3VX500 7455
8600 COMBINE; 8800 COMBINE PERKINS 6.354 ENG. Fan..... A.C..... Hyd. Pump..... J.S.....	311677150 311679590 311681440 311677220	②7410 9480 GS 9570 GS 9530 GS
8900 COMBINE PERKINS 6.354 ENG. W.P. & Alt..... A.C.....	311774180 311679590	9530 GS 9480 GS
9700 COMBINE PERKINS V-8 640 ENG. Fan, Hyd. Pump & Idler..... W.P..... Alt..... A.C.....		②9455 GS 9490 GS 7425 9463 GS

Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
8900 COMBINE PERKINS V-8 640 ENG. Upper.....		>20206
9700 COMBINE PERKINS V-8 640 ENG. Upper.....		26532

WILMAR MFG. Farm Equipment Belts

Application	Mfr. Part No.	Belt No.
AIR RIDE SPRAYER JOHN DEERE 4-CYL. DIESEL ENG. A.C.; W/Turbo.....		9420 GS

Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
AIR RIDE SPRAYER JOHN DEERE 4-CYL. DIESEL ENG. Upper; W/Turbo..... Lower; W/Turbo.....		26510 26523

WOODS & COPELAND

Tractors

Belts

Application	Mfr. Part No.	Belt No.
320C CUMMINS V903 ENG. Fan & Alt..... Fan & W.P..... Fan To A.C.....	178653 202046 178386	6926 ③9580 GS 9476 GS

Coolant Hose

Application	Molded or Strt.	Vulco-Flex®
320C WHEEL CUMMINS V-903 ENG. Upper..... Lower.....		②26525 2 3/4" I.D.

- ② Two Required.
- ③ Three Required.
- ④ Four Required.
- ⑤ Five Required.
- ⑥ Six Required.
- ∞ Cut To Fit.
- ▲ Durion® Silicone Hose Recommended.
- ✦ Use Notched Belt Only.
- GS Green Stripe® Construction.
- ✦ Green Stripe® 4-Ply Coolant Hose Recommended.
- ✦ Use Wire Inserted Green Stripe® Coolant Hose.
- * Green Stripe II Straight Coolant Hose Recommended.

For a maintenance free coolant connection, see PowerGrip® SB clamp application section.