



**DRIVEN BY POSSIBILITY™**

# DELTA V-BELT

## STANDARD V-BELT WITH TRUSTED GATES QUALITY

Gates, the global engineering leader in Power Transmission and Fluid Power, is not only a dynamic front-runner that continuously develops and delivers forward-thinking premium products, services, systems and solutions for today's challenging applications, but also offers to the market with priced by performance belt range to meet our customers' need.

Customers can rely on the most experienced engineering service and after-sales support in the industry. Our premium belts are synonymous for innovation, superior performance and extreme reliability. Because Gates engineers know that on your critical applications literally every minute of downtime costs you huge amounts in production. Our Delta priced-by performance belts provide the cost-effective solution for all your standard industry drives. They offer a unique combination of advantages only available in Gates quality belts, at a sharp price.

With Gates you are fully equipped to run strong, whatever you need, premium or standard belts.



**DELTA NARROW™**



# GATES DELTA, STANDARD V-BELT WITH TRUSTED QUALITY



## MADE BY GATES

Delta is a 100% Gates brand specifically made belt to run in all standard industry drives with trusted Gates quality. Being our commodity range, it reflects the company's strategy to deliver you these belts fit for purpose at a sharp price. It offers the optimum choice for a cost and quality-conscious production process, guaranteed by Gates.



## MADE IN EUROPE

The Delta belts are made in our Gates European factories. We control the entire production and delivery process completely.



## MADE TO DELIVER

The Delta wrapped V-belts are available in two profile: Delta Classic and Delta Narrow. They come in a complete size range. No need for another brand due to certain sections or belt lengths that are missing.



# PRODUCT FEATURES

## GATES COVERS ALL YOUR NEEDS:

THE DELTA CLASSIC AND DELTA NARROW V-BELTS ARE MADE TO RUN IN ALL YOUR STANDARD INDUSTRY DRIVES.

The Greek letter Delta, is the mathematical symbol for 'difference'. In comparison with other belts developed for standard industry drives, the Gates Delta range stands out in more than one way.

Gates Delta V-belts combine the Gates qualities to perform in a cost-effective way. The range consists of two product lines, Delta Classic and Delta Narrow, to cover all your needs.



## CONSTRUCTION FEATURES




Quality rubber belt body, SBR Material



High-strength polyester tensile cords providing resistance to flexing forces, fatigue and shock loads



Flex-Weave® oil-resistant flip band offering good grip and protecting against abrasion




Specified to operate in a temperature range from -30°C to +70°C



Anti-static (ISO 1813) as well as REACH and RoHS 2 compliant



Good belt flexibility, stability and smooth-running operation guaranteed



All sizes meet Gates UNISSET tolerances and can be installed without matching



## BENEFITS THAT IMPACT YOUR BUSINESS

- Excellent price performance ratio
- Trusted Gates quality that equals peace of mind
- Made to run in all your standard industry drives
- Available in all popular sections and belt lengths

# PRODUCT FEATURES

## DELTA CLASSIC

Wrapped V-belts with a classical V-shaped profile and are built for a reliable and durable performance on all industry standard classical section drives used in compressors, pumps, aggregates, alternators, saw, milling, and processing machines. Just to name a few.

### IDENTIFICATION

Solid white color label and icons with key features and crucial information in a universally understood visual language.



#### SECTIONS AND NOMINAL DIMENSIONS

Section	Width (mm)	Height (mm)	Length range (datum length - mm)	
Z	10	6	400 - 1803	
A	13	8	425 - 5000	
B	17	11	660 - 7110	
C	22	14	1092 - 8532	
D	32	19	2000 - 15240	
E	38	25	3748 - 13918	

## DELTA NARROW

Wrapped V-belts with a narrow section profile, making them the perfect option for all industry standard drives commonly referred to as narrow or deep wedge.

### IDENTIFICATION

Solid white color label and icons with key features and crucial information in a universally understood visual language.



#### SECTIONS AND NOMINAL DIMENSIONS

Section	Width (mm)	Height (mm)	Length range (datum length - mm)	
SPZ	10	8	562 - 3550	
SPA	13	10	732 - 4500	
SPB	16	13	1250 - 8000	
SPC	22	18	2000 - 11200	

**ASK YOUR GATES  
REPRESENTATIVE FOR  
MORE INFORMATION**