



DRIVEN BY POSSIBILITY™

# TT5 REINFORCED BELT 100MM (10x10mm)

Gates polyurethane synchronous timing belts are made out of high quality, abrasion-resistant polyurethane in combination with high strength aramid cords. Nearly every extruded belt type can be customized as per customer requirement.

Gates T pitch belts have the trapezoidal design of imperial belts, with slightly deeper engagement for more reliable tooth meshing, but also with slightly greater backlash.



## FEATURES

Polyurethane for resistance to chemicals, abrasion, and wear

Cords are helically wound for strength and long life

One-piece urethane construction for strength

Temperature range of -22 to + 176 degrees F (-30 to + 80 degrees C)





**DRIVEN BY POSSIBILITY™**

**Tt5 reinforced belts , offer good running characteristics and high traction loads. They are especially suited for power transmission and conveying with high loads and speeds.**

PART NO.	DESCRIPTION
7787-5400	PU TT5-5400-100MM
7787-5600	PU TT5-5600-100MM
7787-5800	PU TT5-5800-100MM
7787-6000	PU TT5-6000-100MM
7787-6200	PU TT5-6200-100MM
7787-6400	PU TT5-6400-100MM
7787-6600	PU TT5-6600-100MM
7787-6800	PU TT5-6800-100MM
7787-7000	PU TT5-7000-100MM
7787-7200	PU TT5-7200-100MM
7787-7400	PU TT5-7400-100MM
7787-7600	PU TT5-7600-100MM
7787-7800	PU TT5-7800-100MM
7787-8000	PU TT5-8000-100MM
7787-8200	PU TT5-8200-100MM
7787-8400	PU TT5-8400-100MM
7787-8600	PU TT5-8600-100MM
7787-8800	PU TT5-8800-100MM
7787-9000	PU TT5-9000-100MM
7787-9200	PU TT5-9200-100MM

PART NO.	DESCRIPTION
7787-9400	PU TT5-9400-100MM
7787-9600	PU TT5-9600-100MM
7787-9800	PU TT5-9800-100MM
7787-10000	PU TT5-10000-100MM
7787-10200	PU TT5-10200-100MM
7787-10400	PU TT5-10400-100MM
7787-10600	PU TT5-10600-100MM
7787-10800	PU TT5-10800-100MM
7787-11000	PU TT5-11000-100MM
7787-11200	PU TT5-11200-100MM
7787-11400	PU TT5-11400-100MM
7787-11600	PU TT5-11600-100MM
7787-11800	PU TT5-11800-100MM
7787-12000	PU TT5-12000-100MM
7787-12200	PU TT5-12200-100MM
7787-12400	PU TT5-12400-100MM
7787-12800	PU TT5-12800-100MM
7787-13000	PU TT5-13000-100MM
7787-13400	TT5-13400-100MM

GATES INDIA CORPORATE OFFICE:  
3rd Floor, Bldg #10, Tower C, Cyber City,  
Phase 2, Gurgaon, Haryana - 122002

GATES UNITTA INDIA CO. PVT. LTD.  
Plot No. F 19, Sipcot Industrial Pondur A,  
Sriperumbudur, Tamil Nadu - 602105

