

# FO20S OIL DELIVERY HOSE 20 BAR

## HIGH PRESSURE OILFIELD HOSE



### APPLICATION

Delivery of gasoline, diesel and fuel-oil with aromatic content up to 50%, seawater, mud and general application

**TEMPERATURE** (-30°C to +100°C) (-22°F to +212°F)

**CONSTRUCTION** Tube Black NBR Rubber

**Reinforcement** High Tensile Synthetic Textile & Anti-static Copper Wire

**Cover** Black CR Rubber  
Abrasion, Ozone, Weather, Heat & Oil Resistant

**STANDARDS** Additional standards/certifications available upon customer request

**COUPLINGS** Crimped



ID		OD		WORKING PRESSURE		BURST PRESSURE		MBR		WEIGHT		MAX HOSE LENGTH		REFERENCE CODE	REFERENCE NUMBER
inch	mm	inch	mm	bar	psi	bar	psi	inch	mm	kg/m	lb/ft	m	ft		
3/8	10	0.75	19	20	300	80	1200	3	0.1	0.4	0.2	60	196	H2F020S06	-
1/2	13	0.91	23	20	300	80	1200	3	0.1	0.4	0.2	60	196	H2F020S08	-
3/4	19	1.18	30	20	300	80	1200	4	0.1	0.6	0.4	60	196	H2F020S12	-
1	25	1.46	37	20	300	80	1200	6	0.2	0.7	0.5	60	196	H2F020S16	-
1 1/4	32	1.77	45	20	300	80	1200	7	0.2	0.9	0.6	60	196	H2F020S20	-
1 1/2	38	2.01	51	20	300	80	1200	9	0.2	1.1	0.7	60	196	H2F020S24	-
2	51	2.52	64	20	300	80	1200	12	0.3	1.4	0.9	60	196	H2F020S32	-
3	76	3.66	93	20	300	80	1200	18	0.5	2.7	1.8	60	196	H2F020S48	-
4	102	4.72	120	20	300	80	1200	24	0.6	3.8	2.6	60	196	H2F020S64	-
5	127	5.83	148	20	300	80	1200	30	0.8	5.5	3.7	60	196	H2F020S80	-
6	152	6.81	173	20	300	80	1200	36	0.9	6.5	4.4	60	196	H2F020S96	-
8	203	9.21	234	20	300	80	1200	40	1.0	18.5	12.4	60	196	H2F020S128	-

Gates Corporation is a leading manufacturer of application-specific fluid power and power transmission solutions. At Gates, we are driven to push the boundaries of materials science to engineer products that continually exceed expectations.