



DRIVEN BY POSSIBILITY™

DATA MASTER™ DATA CENTER COOLING HOSE

COOL DOWN, POWER UP, **BE RELIABLE**

Cooling data center systems is not just about thermal management. It's about guaranteeing performance, preventing slowdowns and crashes, safeguarding valuable infrastructure, and delivering energy efficient solutions.

Studies have shown that data center operations can save up to to 40% of their energy used to cool data centers by switching to liquid or hybrid cooling methods. And with over 18,000 data centers expected to be in operation in just a few years, the demand for quality, reliable data center cooling products is more prevalent than ever.


Gates products power the digital world, from financial transactions to social media interactions. Don't rely on chance; invest in proper cooling solutions to keep your data center operational.

FULL SOLUTION PORTFOLIO

Gates has existing fluid conveyance and power transmission solutions to power your Data Center. From electric water pumps and flexible hoses to premium belts and nylon tubing, Gates is ready to provide you with the reliability and performance you need.



THERMALPRO™ ELECTRIC WATER PUMP




THERMAL FORMED NYLON TUBING




DATA MASTER COOLING HOSE



OIL-BASED & LARGE ID HOSE SOLUTIONS



QUAD-POWER™ 4



POLY CHAIN® CARBON™ VOLT™

HEAVY-DUTY SOLUTIONS FOR HIGH-DENSITY PERFORMANCE

DATA MASTER COOLING HOSE

Engineered to efficiently circulate coolant, the Gates Data Master Cooling Hose keeps your data center operational in the toughest conditions. Its zinc-free peroxide-cured EPDM tube offers the best compatibility with PG25 and other deionized water glycol coolant mixes to avoid fluid contamination and keep your servers running at maximum performance. Our hoses are specially designed to have a narrow profile (diameter) while using Gates special manufacturing techniques to make them flexible for easy connection.


SPECIFICATIONS

- Zinc-Free, Peroxide-Cured EPDM Tube, Synthetic fiber braid reinforcement, and flame-resistant EPDM cover
- Wide temperature range: -40 °C to +100 °C (-40 °F to +212 °F)



CLEANER SYSTEMS

Zinc-free Peroxide Cured EPDM tube to avoid fluid contamination over time



NARROW PROFILE

Smaller diameter for installation when space is constrained



FLAME-RESISTANT

Meets UL224 VW-1 and UL94V-0 standards



SUPERIOR FLEXIBILITY

For easier routing in complex configurations



COOLANT COMPATIBLE

Built for a wide range of coolant mixes, including PG25



OZONE-RESISTANT

Excellent ozone resistance to cover degradation from electronics

GATES DATA MASTER COOLING HOSE											
HOSE I.D.		HOSE O.D.		MAX. WORK PRESSURE		MINIMUM BURST		MINIMUM BEND RADIUS (ISO 10619, METHOD B)		WEIGHT REFERENCE	
mm	in	mm	in	MPa	psi	MPa	psi	mm	in	kg/m	lbs/ft
5	7/32	10.4	0.40	3.4	500	13.8	2,000	15.0	0.59	0.08	0.05
6	1/4	12.4	0.49	2.1	300	8.4	1,200	15.9	0.63	0.10	0.06
10	3/8	15.6	0.61	2.1	300	8.4	1,200	31.6	1.25	0.14	0.09
13	1/2	18.7	0.74	2.1	300	8.4	1,200	50.2	1.98	0.20	0.13
19	3/4	26.1	1.03	2.1	300	8.4	1,200	73.8	2.90	0.35	0.23
25	1	33.9	1.34	1.0	150	4.1	600	89.0	3.50	0.57	0.38

// GATES® // Data Master™


OUR DATA CENTER SOLUTIONS CAN PUT YOUR CRITICAL COOLING SYSTEMS RUNNING AT TOP CAPACITY IN **NUMEROUS APPLICATIONS**



CHILLED
WATER SYSTEMS



CRAC OR CRAH
UNITS



DIRECT TO CHIP
LIQUID COOLING



LIQUID IMMERSION
COOLING SYSTEMS



IN-ROW AND IN-RACK
COOLING SYSTEMS

GATES IS A MEMBER OF THE OPEN COMPUTE PROJECT

As a member of the Open Compute Project, we are ready to work together with this forward-thinking community to create top-notch data center solutions for our customers. We truly believe that together, we can pave the way for a more innovative, sustainable, and efficient future.



OPEN
COMMUNITY®