



DRIVEN BY POSSIBILITY™

# SUPER HC™ MN AND TRI-POWER™ BELTS

## THE PERFECT V-BELTS FOR YOUR IMPERFECT CONDITIONS

The combination of a wide range of jobs, ever-evolving technology, and numerous emerging applications can make choosing the right industrial belt drive seem complicated. Luckily, no matter what is ahead, Gates is there with quality V-belt solutions like Super HC Molded Notch (MN) and Tri-Power.

These two popular families of cost-effective, high-load carrying, and flexible V-belts are made of high-performance Ethylene Elastomer (EE) materials to excel from beverage bottling plants to mixing and grinding facilities.

### SUPER HC MN:

**NARROW  
CROSS-  
SECTION**



### TRI-POWER:

**CLASSICAL  
CROSS-  
SECTION**



## FEATURES AND BENEFITS

- Wider temperature range than previous generation V-belts due to EE materials: -60°F to +250°F (-51°C to +121°C)
- High performance, synthetic rubber compounds resist wear increasing belt life
- Belt edge machined for even sheave groove contact, resulting in smoother running, less slip and wear
- Good resistance to occasional exposure to oil and chemicals
- Meets ARPM IP-3-3 and ISO 1813 static-conductivity standards
- REACH compliant
- Suitable for RoHS required applications

**15%\***

**INCREASED CAPACITY**

**25%\***

**DECREASE IN RECOMMENDED  
MINIMUM PULLEY DIAMETER  
ACROSS PRODUCT FAMILIES**

**EXCELLENT  
PERFORMANCE-TO-COST RATIO**


\*On average vs wrapped/banded belts. Figures vary based on size.

## PRODUCT ATTRIBUTES


<b>SUPER HC MN: MORE POWER IN A SMALLER SPACE</b>	<b>TRI-POWER: TRIED AND TRUE REPLACEMENT OPTION</b>
Raw edge, molded notch	Raw edge, molded notch
<b>NARROW</b> cross-section	<b>CLASSICAL</b> cross-section
Reduces space by allowing for more compact drive designs	The go-to belt for classical section sheaves
<b>RECOMMENDED FOR:</b> Industrial heavy-duty, narrow section V-belt drives where space, weight, and horsepower capacity are critical. Ideal when designing new drives or replacing sheaves on existing drives.	<b>RECOMMENDED FOR:</b> Industrial applications where small sheave diameters are required. Ideal for applications where sheave replacement is not a possibility or like-for like replacement is preferred.

## AVAILABLE CROSS SECTIONS

SECTION	WIDTH (W) in (mm)	HEIGHT (H) in (mm)
3VX/XPZ	.375 (10)	.328 (8)
XPA	.512 (13)	.394 (10)
5VX/XPB	.625 (16)	.563 (13)
8VX	1 (25)	.828 (21)



SECTION	WIDTH (W) in (mm)	HEIGHT (H) in (mm)
AX	.5 (13)	.313 (8)
BX	.656 (17)	.406 (10)
CX	.875 (22)	.531 (13)




## GATES BANDLESS ADVANTAGE


### BENDING STRESS COMPARISON

When space is at a premium, drives are often designed with small pulleys. Notched belts excel by reducing the bending stress and heat generation while extending belt life.

Not all notches are created equal, it requires a balance between flexibility and stress distribution. Meeting one of these is easy, meeting both presents quite a challenge.



Using Finite Element Analysis (FEA), the increased bending stresses are clearly visible on a belt without notches.



Molding notches into the belt helps reduce and spread out these stresses.

CONCENTRATED BENDING STRESS

OPTIMALLY DISTRIBUTED BENDING STRESS

## SUPER HC MN AND TRI-POWER CAN ENHANCE THE PERFORMANCE OF YOUR OPERATION IN **NUMEROUS MARKETS:**



**AGRICULTURE**



**DIVERSIFIED INDUSTRIAL**



**FOOD AND BEVERAGE**



**MATERIAL HANDLING**



**PULP AND PAPER**



**WATER TREATMENT**



**NEED HELP DECIDING WHICH BELT IS BEST FOR YOUR APPLICATION? USE **DESIGN POWER****