

CEMENTING 5000 POWERSPIRAL™

HIGH PRESSURE OILFIELD HOSE



APPLICATION

Used as a flexible connection between the cementing pump manifold and cementing head for conveyance of cement slurries at high pressure. The tube is designed to handle abrasive and corrosive cements. The cover is designed to handle external damage from abrasion, corrosion, gouges, oil and weather.

TEMPERATURE (-20°C to +121°C) (-4°F to +250°F)

CONSTRUCTION Tube Type C (Nitrile)

Reinforcement Multiple layers of spiraled high tensile steel wire

Cover Type A (Chloroprene)

FSL RATING FSL 0 all sizes

STANDARDS API 7K 6th Edition, ISO 47693, ABS Type Approvals

COUPLINGS Swaged Couplings



ID		OD		WORKING PRESSURE		BURST PRESSURE		MBR		WEIGHT		MAX HOSE LENGTH
inch	mm	inch	mm	bar	psi	bar	psi	inch	mm	kg/ft	lb/ft	ft
2	51	2.80	71	345	5000	860	12500	36	914	2	5	200

Gates Corporation is a leading manufacturer of application-specific fluid power and power transmission solutions. At Gates, we are driven to push the boundaries of materials science to engineer products that continually exceed expectations.