

DRIVEN BY POSSIBILITY

MEGASYS[™] M TM HYDRAULIC HOS WITH STANDARD AND XTRATUFFTM PLUS COVERS

OPTIMIZED PERFORMANCE, **EXTRAORDINARY** DURABILITY

MXT was designed to address our customers' evolving application challenges. Using materials science and process innovation, combined with a patent-pending construction, Gates offers a hydraulic solution that is lighter, stronger, and more flexible. Made with strong, high-performance reinforcement and high quality, abrasion-resistant rubber, MXT is a universally applicable premium product offering performance above industry standards. Its diversified application allows you to consolidate inventory while giving you exactly the hose you need, when you need it.

GATES XTRATUFF PLUS COVER AVAILABLE ON MXT. PROVIDING INCREASED ABRASION AND OZONE RESISTANCE

FEATURES + BENEFITS

GATES MEAN

GATES" // MEGASys" (?) // 8 MXT' XTP Xtratuff Plus (?)

- Lighter weight for easier handling
- More flexible with lower force-to-bend for faster and more ergonomic installation
- Tested to 3 times the industry standard impulse criteria (600,000 cycles)
- Compatible with MegaCrimp[™] Couplings and Gates Crimpers
- Cross-functional, multi-spec hydraulic solution covering 90% of the wire braid market
- Up to 45% of EN 857 2SC bend radius at rated working pressure



DRIVEN BY POSSIBILITY[™]

| MXT PRODUCT SPECIFICATIONS | | | | | | | | |
|----------------------------|---|--|--|--|--|--|--|--|
| STANDARD | Meets EN 853 2SN and EN 857 2SC performance. Meets ISO 11237 R16 and ISO 11237 R17* dimension and performance. Meets ISO 1436 R2 and ISO 11237 R19* performance. | | | | | | | |
| CONSTRUCTION | Black, oil resistant, synthetic rubber tube. Braided high-tensile steel wire reinforcement. | | | | | | | |
| COVER | Black, smooth, synthetic rubber cover. Meets MSHA flame resistance. XtraTuff [™] Plus cover (optional). | | | | | | | |
| TEMPERATURE RANGE | -40 °C to +100 °C. | | | | | | | |



WE'VE GOT YOU COVERED.

Gates XtraTuff Plus is also available on MXT. Our latest material breakthrough is engineered for exceptional durability to cover your assets in the most demanding fluid power applications.

- 25X more abrasion resistant
- Enhanced ozone resistance
- No impact to flexibility
- Exceptional durability
- MSHA certified

| SECTIONS + DIMENSIONS | | | | | | | | | | | |
|-----------------------|----|------|------|------|------|------|-------|-------|---------|---------|--|
| Θ | | ĨO | | Ô | | | | | o kg | | |
| -size | DN | " | " | mm | PSI | MPa | PSI | MPa | mm | kg/100m | |
| -4 | 6 | 1/4 | 0.56 | 14.0 | 6000 | 42.0 | 24000 | 168.0 | 40 | 30 | |
| -5 | 8 | 5/16 | 0.61 | 15.2 | 5500 | 38.0 | 22000 | 152.0 | 45 | 33 | |
| -6 | 10 | 3/8 | 0.68 | 17.1 | 4800 | 33.0 | 19200 | 132.0 | 65 | 39 | |
| -8 | 12 | 1/2 | 0.80 | 20.2 | 4000 | 27.5 | 16000 | 110.0 | 70 | 46 | |
| -10 | 16 | 5/8 | 0.95 | 24.0 | 3625 | 25.0 | 14500 | 100.0 | 100* | 57 | |
| -12 | 19 | 3/4 | 1.08 | 27.4 | 3100 | 21.5 | 12400 | 86.0 | 120 | 70 | |
| -16 | 25 | 1 | 1.38 | 35.1 | 2400 | 16.5 | 9600 | 66.0 | 150 | 100 | |

* Note: 10MXT is able to meet minimum bend radius (MBR) of 75mm; 10MXT-XTP is able to meet MBR of 100mm.