

CHOKE & KILL HOSE

HIGH PRESSURE OILFIELD HOSE



APPLICATION

Flexible hose between the riser and manifold or around the ball joint of offshore drilling rigs. Specially designed to withstand flexing and high pressures encountered in offshore applications. Hoses are manufactured to handle up to 20% hydrogen sulfide H₂S for 1 hour at 200 °F (93 °C) at rated working pressure.

TEMPERATURE (-25°C to +100°C) (-13°F to +212°F)

CONSTRUCTION Tube Stripwound and HNBR

Reinforcement Multiple layers of textile fabric and steel cable

Cover PCR

STANDARDS API 16C 2nd Edition FSL3, ISO 47693, ABS Type Approvals

COUPLINGS Bonded



| ID | | OD | | WORKING PRESSURE | | BURST PRESSURE | | MBR | | WEIGHT | | MAX HOSE LENGTH | | REFERENCE CODE | REFERENCE NUMBER |
|------|----|------|-------|------------------|-------|----------------|-------|------|------|--------|-------|-----------------|-------|----------------|------------------|
| inch | mm | inch | mm | bar | psi | bar | psi | inch | mm | kg/m | lb/ft | m | ft | | |
| 2 | 51 | 4.70 | 118.2 | 345 | 5175 | 863 | 12945 | 43.3 | 1100 | 17.9 | 12.03 | 62 | 203.4 | CK02D | 603 |
| 3 | 76 | 7.10 | 181.1 | 690 | 10000 | 1553 | 22500 | 59.1 | 1500 | 63.0 | 42.33 | 62 | 203.4 | CK03F | 884 |

Gates Corporation is a leading manufacturer of application-specific fluid power and power transmission solutions. At Gates, we are driven to push the boundaries of materials science to engineer products that continually exceed expectations.