

# FO10H OIL SUCTION & DELIVERY HOSE 10 BAR



## HIGH PRESSURE OILFIELD HOSE

### APPLICATION

Delivery of gasoline, diesel and fuel-oil with aromatic content up to 50%, seawater, mud and general applications

**TEMPERATURE** (-35°C to +100°C) (-31°F to +212°F)

**CONSTRUCTION** Tube Black NBR Rubber

**Reinforcement** High Tensile Synthetic Textile with Embedded Steel Helix Wire & Anti-static Copper Wire

**Cover** Black CR/BR blend rubber  
Abrasion, Ozone, Weather, Heat & Oil Resistant

**STANDARDS** Additional standards/certifications available upon customer request

**COUPLINGS** Crimped



ID		OD		WORKING PRESSURE		BURST PRESSURE		MBR		WEIGHT		MAX HOSE LENGTH		REFERENCE CODE	REFERENCE NUMBER
inch	mm	inch	mm	bar	psi	bar	psi	inch	mm	kg/m	lb/ft	m	ft		
1	25	1.46	37	10	150	40	600	5	0.1	1.1	0.7	60	196	H2F010H16	-
1 1/2	38	2.01	51	10	150	40	600	7	0.2	1.6	1.1	60	196	H2F010H24	-
2	51	2.60	66	10	150	40	600	10	0.3	2.2	1.5	60	196	H2F010H32	-
2 1/2	63	3.03	77	10	150	40	600	13	0.3	2.8	1.9	60	196	H2F010H40	-
3	76	3.62	92	10	150	40	600	15	0.4	3.2	2.2	60	196	H2F010H48	-
4	102	4.72	120	10	150	40	600	20	0.5	5.4	3.6	60	196	H2F010H64	-
5	127	5.91	150	10	150	40	600	25	0.6	7.8	5.2	60	196	H2F010H80	-
6	152	6.89	175	10	150	40	600	30	0.8	10.4	7.0	60	196	H2F010H96	-
8	203	9.21	234	10	150	40	600	40	1.0	17.2	11.6	60	196	H2F010H128	-
10	254	11.34	288	10	150	40	600	50	1.3	26.5	17.8	60	196	H2F010H160	-
12	305	13.50	343	10	150	40	600	60	1.5	36.5	24.5	60	196	H2F010H192	-

Gates Corporation is a leading manufacturer of application-specific fluid power and power transmission solutions. At Gates, we are driven to push the boundaries of materials science to engineer products that continually exceed expectations.