



TPU BELTS

THERMOPLASTIC POLYURETHANE

GATES TPU FOOD BELT QUOTE CHECKLIST STRAIGHT CONVEYOR

*Name: _____ *Phone: _____ *Email: _____


*Company Name: _____ *Site Location: _____

APPLICATION

*Briefly describe what is being conveyed, what type of belt is being replaced.
 *Max. Load lbs.
 *Load Rate lbs/hr and Conveyor Speed ft/min
 *Lb per Cubic Ft. and Depth of Product in

or
or


BELT	INPUT
*Belt Pitch/Type	
*Belt Width (in/mm)	
*Belt Length (in/mm)	
*Splice Type	
Mechanical	
Weld	
*Straight Cleats (5mm thick)	
Overall Height	
Spacing	
Offset From Edge (in/mm) / Centered	
*Scoop Cleats (7 mm thick)	
Overall Height	
Spacing	
Offset From Edge (in/mm) / Centered	
*Sidewalls	
Overall Height	
Offset From Edge (in/mm)	
V-Guide	
Type	
Offset From Edge (in/mm) / Centered	




Comments (environment, cleaning protocol, etc.)

SPROCKETS
of Sprockets
Number of Teeth or Diameter
Bore Type
Dimension (in/mm)
Keyway Dimension (in/mm)
Any Back Idlers
Diameter of Back Bend (in/mm)
Smallest In Conveyor (in/mm)
Drum Motor / Motorized Pulley


Common Pitch Types




PC10



PC20



CC40



FC12

CONVEYOR
Bed Type
Wear Strips
Number Across Conveyor Width
Spacing
Pattern
*Material
or Slider Bed
Dimensions (in/mm)
*Material
Roller
Number of Rollers
Spacing of Rollers
Returnway
Conveyor Sidewalls/Fenders - Height
Material
Troughing
Transition Length (in/mm)
Angle
Side Wear Strips
Drive Type
Incline Angle
Angle of Belt Wrap On Drive Pulley
Tensioning Device (Take Up) Avail
Type
Total Travel
Extended Distance When Center Distance Is Measured

ADDITIONAL INFORMATION

*Dry/Wet Application

Outside Sales Contact Info

GATES TPU
 9 Northwestern Drive Salem, NH 03079, U.S.A.
 Tel. +1 (603) 890-1515. / +1 (800) 394-4844.
 contact@gates.com
 www.gates.com/TPU

Application Engineering
 email: slo.apps@gates.com
 Tel. +1 (800) 505-8494