






TPU BELTS

INDUSTRIAL PITCH GUIDE



V-GUIDES



All dimensions shown in inches (mm)

INPUT BELT REQUIREMENTS

Belt Basics (Required)

SPLICE TYPE:	Open Ended	Welded	Truly Endless
	Mech. Splice	Prepared Ends	

PITCH:	(use front page)
---------------	------------------

LENGTH:	in	mm
----------------	----	----

WIDTH:	in	mm
---------------	----	----

V-GUIDE:	K6	K10	K13	A	O	Other	(use front page)
-----------------	----	-----	-----	---	---	-------	------------------

CORD TYPE:	Steel	Aramid	Other
-------------------	-------	--------	-------

COLOR:	Natural	White	Other
---------------	---------	-------	-------

NYLON:	None	Tooth	Back	Tooth & Back
---------------	------	-------	------	--------------

Machining: holes, grooves, etc. (Optional)

Yes None

If yes, please sketch pattern and dimensions below

ADDITIONAL COMMENTS:

Backing (Optional)

Yes None

MATERIAL:

DUROMETER:	Shore A
-------------------	---------

COLOR:

THICKNESS:	in	mm
-------------------	----	----

Profiles/Cleats (Optional)

Yes None

PROFILE NUMBER:	Custom
------------------------	--------

CENTERING:	Belt center	Other
-------------------	-------------	-------


NUMBER OF PROFILES:

SPACING:	in	mm
-----------------	----	----



SCAN TO USE PROFILE SELECTOR TOOL

If custom, please sketch and list dimensions below
Use sketch area to define profile dimensions, machined geometries, etc.



SEND TO SASALES@GATES.COM

GATES.COM/TPU
05/2024

