

FO40H OIL DELIVERY HOSE 40 BAR

HIGH PRESSURE OILFIELD HOSE



APPLICATION

Delivery of gasoline, diesel and fuel-oil with aromatic content up to 50%, liquid mud contain crude oil and grit

TEMPERATURE	(-30°C to +100°C) (-22°F to +212°F)	
CONSTRUCTION	Tube	Black NBR Rubber
	Reinforcement	High Tensile Synthetic Textile with Embedded Steel Helix & Anti-Static Copper Wire
	Cover	Black CR/BR Blend Rubber Abrasion, Ozone, Weather, Heat & Oil Resistant
STANDARDS	Additional standards/certifications available upon customer request	
COUPLINGS	Crimped	



ID		OD		WORKING PRESSURE		BURST PRESSURE		MBR		WEIGHT		MAX HOSE LENGTH		REFERENCE CODE	REFERENCE NUMBER
inch	mm	inch	mm	bar	psi	bar	psi	inch	mm	kg/m	lb/ft	m	ft		
3	76	4.72	120	40	600	160	2400	18	0.5	5.5	3.7	60	196	H2FO40H48	-
4	102	5.08	129	40	600	160	2400	24	0.6	7.5	5.0	60	196	H2FO40H64	-
5	127	6.65	169	40	600	160	2400	30	0.8	13.8	9.3	60	196	H2FO40H80	-

Gates Corporation is a leading manufacturer of application-specific fluid power and power transmission solutions. At Gates, we are driven to push the boundaries of materials science to engineer products that continually exceed expectations.