



DRIVEN BY POSSIBILITY™

# CLEAN MASTER™ PRESSURE WASH



-SIZE	DN	"	"	MM	PSI	MPA	PSI	MPA	MM	PACKAGING	KG/100M	REF.
-4	6	1/4	0.52	13.2	4000	28.0	12000	84.0	50	91	24	CLEAN MAS PW4000 1/4"
-5	8	5/16	0.59	14.9	4000	28.0	12000	84.0	55	91	27	CLEAN MAS PW4000 5/16"
-6	10	3/8	0.66	16.8	4000	28.0	12000	84.0	65	91	34	CLEAN MAS PW4000 3/8"
-5	8	5/16	0.59	14.9	4000	28.0	12000	84.0	55	91	27	CLEAN MAS PW4000B 5/16"
-6	10	3/8	0.66	16.8	4000	28.0	12000	84.0	65	91	34	CLEAN MAS PW4000B 3/8"
-8	12	1/2	0.78	19.8	3000	21.0	9000	62.0	90	91	43	CLEAN MAS PW3000B 1/2"
-6	10	3/8	0.66	16.8	4000	28.0	12000	84.0	65	91	34	CLEAN MAS PW4000G 3/8"
-8	12	1/2	0.78	19.8	3000	21.0	9000	62.0	90	91	43	CLEAN MAS PW3000G 1/2"

#### RECOMMENDED FOR

Use on pressure cleaning equipment for commercial and industrial purposes, in food processing, sanitation and car wash applications.  
All hot and cold water high-pressure cleaning services.

#### TUBE

NBR (Nitrile) based. Black.

#### REINFORCEMENT

One braid of high tensile steel wire.

#### COVER

Modified Nitrile. MSHA approved. Available in black, blue (B) and grey (G).  
Blue and grey covers are non-marking.

#### TEMPERATURE RANGE

-40°C to +121°C. For water emulsions, etc. see Temperature Limits Table.

#### STANDARDS

Exceeds EN 1829-2.

#### COUPLINGS

MegaCrimp®.

#### CHARACTERISTICS / BENEFITS

Abrasion and ozone resistant cover.

#### IMPORTANT



**Not for steam service.**