## **AF20S AIR HOSE 20 BAR**

## **HIGH PRESSURE OILFIELD HOSE**



## APPLICATION

Compressed Air - heavy duty applications

| TEMPERATURE  | (-35°C to +85 °C) (-31°F to +185 °F)                                |  |  |  |  |  |  |
|--------------|---|--|--|--|--|--|--|
| CONSTRUCTION | Tube  | Black NBR Rubber   |  |  |  |  |  |
|              | Reinforcement   | High Tensile Synthetic Textile                           |  |  |  |  |  |
|              | Cover   | Yellow NBR Rubber<br>Abrasion, Ozone & Weather Resistant |  |  |  |  |  |
| STANDARDS    | Additional standards/certifications available upon customer request |  |  |  |  |  |  |
| COUPLINGS    | Crimped   |  |  |  |  |  |  |

## $\bigoplus \qquad \fbox{} \qquad \textcircled{} \qquad \end{array}{} \qquad \textcircled{} \qquad \textcircled{} \qquad \end{array}{} \qquad \textcircled{} \qquad \end{array}{} \qquad \textcircled{} \qquad \textcircled{} \qquad \textcircled{} \qquad \textcircled{} \qquad \textcircled{} \qquad \\ \end{array}{} \qquad \qquad \textcircled{} \qquad \\} \qquad \qquad \qquad \qquad \qquad$

| ID    |    | OD   |    | WORKING<br>PRESSURE |     | BURST<br>PRESSURE |     | MBR  |     | WEIGHT |       | MAX HOSE<br>LENGTH |     | REFERENCE<br>CODE | REFERENCE<br>NUMBER |
|-------|----|------|----|---------------------|-----|-------------------|-----|------|-----|--------|-------|--------------------|-----|-------------------|---------------------|
| inch  | mm | inch | mm | bar                 | psi | bar               | psi | inch | mm  | kg/m   | lb/ft | m                  | ft  |                   |                     |
| 1/2   | 13 | 0.91 | 23 | 20                  | 300 | 60                | 900 | 3    | 0.1 | 0.4    | 0.3   | 60                 | 196 | H2AF20S08         | -                   |
| 3/4   | 19 | 1.18 | 30 | 20                  | 300 | 60                | 900 | 4    | 0.1 | 0.6    | 0.4   | 60                 | 196 | H2AF20S12         | -                   |
| 1     | 25 | 1.46 | 37 | 20                  | 300 | 60                | 900 | 6    | 0.2 | 0.8    | 0.5   | 60                 | 196 | H2AF20S16         | -                   |
| 1 1/4 | 32 | 1.77 | 45 | 20                  | 300 | 60                | 900 | 7    | 0.2 | 1.1    | 0.7   | 60                 | 196 | H2AF20S20         | -                   |
| 1 1/2 | 38 | 2.05 | 52 | 20                  | 300 | 60                | 900 | 9    | 0.2 | 1.4    | 0.9   | 60                 | 196 | H2AF20S24         | -                   |
| 2     | 51 | 2.64 | 67 | 20                  | 300 | 60                | 900 | 12   | 0.3 | 2.1    | 1.4   | 60                 | 196 | H2AF20S32         | -                   |

Gates Corporation is a leading manufacturer of application-specific fluid power and power transmission solutions. At Gates, we are driven to push the boundaries of materials science to engineer products that continually exceed expectations.