

# CEMENTING 10000 POWERSPIRAL™

## HIGH PRESSURE OILFIELD HOSE



### APPLICATION

Used as a flexible connection between the cementing pump manifold and cementing head for conveyance of cement slurries at high pressure. The tube is designed to handle abrasive and corrosive cements. The MegaTuff® cover is designed to handle severe external damage from abrasion, corrosion, gouges, oil and weather.

<b>TEMPERATURE</b>	(-20°C to +121°C) (-4°F to +250°F)	
<b>CONSTRUCTION</b>	<b>Tube</b>	Type C3 (Nitrile)
	<b>Reinforcement</b>	Multiple layers of spiraled high tensile steel wire
	<b>Cover</b>	Type L (MegaTuff)
<b>FSL RATING</b>	FSL 0 all sizes	
<b>STANDARDS</b>	API 7K 6th Edition, ISO 47693, ABS Type Approvals	
<b>COUPLINGS</b>	Crimped Couplings	



ID		OD		WORKING PRESSURE		BURST PRESSURE		MBR		WEIGHT		MAX HOSE LENGTH
inch	mm	inch	mm	bar	psi	bar	psi	inch	mm	kg/ft	lb/ft	ft
1 1/2	38	2.26	57	689	10000	1550	22500	20	508	1	3	200
2	51	2.8	71	689	10000	1550	22500	36	635	2	5	200

Gates Corporation is a leading manufacturer of application-specific fluid power and power transmission solutions. At Gates, we are driven to push the boundaries of materials science to engineer products that continually exceed expectations.