CEMENTING 15000

HIGH PRESSURE OILFIELD HOSE



APPLICATION

Used as a flexible connection between the cementing pump manifold and cementing head for conveyance of cement slurries at high pressure. The tube is designed to handle abrasive and corrosive cements. The UltraBrasion™ cover is designed to handle external damage from abrasion, corrosion, gouges, oil and weather.

TEMPERATURE	(-20°C to +100°C)(-4°F to +212°F)						
CONSTRUCTION	Tube	pe V (Fluoroelastomer)					
	Reinforcement	Multiple layers of textile fabric and steel cable					
	Cover	Type C4 (Modified Nitrile)					
COUPLINGS	Built-in Couplings						













ID		OD		WORKING PRESSURE		BURST PRESSURE		MBR		WEIGHT		MAX HOSE LENGTH
inch	mm	inch	mm	bar	psi	bar	psi	inch	mm	kg/ft	lb/ft	ft
2 1/2	64	5.66	144	1034	15000	2068	30000	60	1524	13	29	90
3	76	6.16	156	1034	15000	2068	30000	48	1524	15	33	90

Gates Corporation is a leading manufacturer of application-specific fluid power and power transmission solutions. At Gates, we are driven to push the boundaries of materials science to engineer products that continually exceed expectations.