## **CHOKE & KILL 15000**

## HIGH PRESSURE OILFIELD HOSE



## **APPLICATION**

Flexible hose between the riser and manifold or around the ball joint of offshore drilling rigs. Specially designed to withstand flexing and high pressures encountered in offshore applications. Hoses are manufactured to handle up to 20% hydrogen sulfide  $H_2S$  for 1 hour at 200°F (93°C) at rated working pressure.

TEMPERATURE	(-20°C to +93°C)(-4°F to +200°F)						
CONSTRUCTION	Tube	Type V (Fluoroelastomer)					
	Reinforcement	Multiple layers of textile fabric and steel cable					
	Cover	Type C4 (Modified Nitrile)					
FSL RATING	FSL 0 all sizes						
STANDARDS	NACE MR0175						
COUPLINGS	Built-in Couplings						













ID		OD		WORKING PRESSURE		BURST PRESSURE		MBR		WEIGHT		MAX HOSE LENGTH
inch	mm	inch	mm	bar	psi	bar	psi	inch	mm	kg/ft	lb/ft	ft
2 1/2	64	5.66	144	1034	15000	2327	33750	60	1524	13	29	90
3	76	6.16	156	1034	15000	2327	33750	60	1524	15	33	90

Gates Corporation is a leading manufacturer of application-specific fluid power and power transmission solutions. At Gates, we are driven to push the boundaries of materials science to engineer products that continually exceed expectations.