

# FO40S OIL DELIVERY HOSE 40 BAR

## HIGH PRESSURE OILFIELD HOSE



### APPLICATION

Delivery of gasoline, diesel and fuel-oil with aromatic content up to 50%, liquid mud contain crude oil and grit

**TEMPERATURE** (-30°C to +100°C) (-22°F to +212°F)

**CONSTRUCTION** **Tube** Black Synthetic Nitrile Rubber

**Reinforcement** High Tensile Synthetic Textile & Anti-Static Copper Wire

**Cover** Black CR/BR Blend Synthetic Rubber  
Abrasion, Ozone, Weather, Heat & Oil Resistant

**STANDARDS** Additional standards/certifications available upon customer request

**COUPLINGS** Crimped



ID		OD		WORKING PRESSURE		BURST PRESSURE		MBR		WEIGHT		MAX HOSE LENGTH		REFERENCE CODE	REFERENCE NUMBER
inch	mm	inch	mm	bar	psi	bar	psi	inch	mm	kg/m	lb/ft	m	ft		
3	76	4.06	103	40	600	160	2400	18	0.5	4.3	2.9	60	196	H2F040S48	-
4	102	5.04	128	40	600	160	2400	24	0.6	5.6	3.8	60	196	H2F040S64	-
5	127	6.61	168	40	600	160	2400	30	0.8	12.4	8.3	60	196	H2F040S80	-
6	152	7.76	197	40	600	160	2400	36	0.9	14.0	9.4	60	196	H2F040S96	-

Gates Corporation is a leading manufacturer of application-specific fluid power and power transmission solutions. At Gates, we are driven to push the boundaries of materials science to engineer products that continually exceed expectations.