



DRIVEN BY POSSIBILITY™

CLEAN MASTER™ PLUS PRESSURE WASH 6000



↔		○			⊙		⚖		📏
-SIZE	DN	"	"	MM	PSI	MPA	MM	KG/100M	REF.
-4	6	1/4	0.52	13.1	6000	42.0	50	25	4PWPLUS6000
-5	8	5/16	0.58	14.7	6000	42.0	85	30	5PWPLUS6000
-6	10	3/8	0.68	17.3	6000	42.0	110	39	6PWPLUS6000
-8	12	1/2	0.81	20.6	6000	42.0	125	46	8PWPLUS6000
-4	6	1/4	0.52	13.1	6000	42.0	50	25	4PWPLUS6000B
-5	8	5/16	0.58	14.7	6000	42.0	85	30	5PWPLUS6000B
-6	10	3/8	0.68	17.3	6000	42.0	110	39	6PWPLUS6000B
-8	12	1/2	0.81	20.6	6000	42.0	125	46	8PWPLUS6000B
-4	6	1/4	0.52	13.1	6000	42.0	50	25	4PWPLUS6000G
-5	8	5/16	0.58	14.7	6000	42.0	85	30	5PWPLUS6000G
-6	10	3/8	0.68	17.3	6000	42.0	110	39	6PWPLUS6000G
-8	12	1/2	0.81	20.6	6000	42.0	125	46	8PWPLUS6000G

RECOMMENDED FOR

Use on pressure cleaning equipment for commercial and industrial purposes, in food processing, sanitation and car wash applications. All hot and cold water high-pressure cleaning services.

TUBE

NBR (Nitrile) based. Black.

REINFORCEMENT

Braided high-tensile steel wire.

COVER

NBR/PVC based. MSHA approved. Available in black, blue (B) and grey (G).

TEMPERATURE RANGE

-40 °C to +150 °C intermittent (to EN 1829-2)
For water emulsions, etc. see Temperature Limits Table in catalogue E/50080

STANDARDS

Exceeds EN 1829-2.

COUPLINGS

MegaCrimp®.

CHARACTERISTICS / BENEFITS

Abrasion and ozone resistant cover.
Light weight.

IMPORTANT



Not for steam service.