## **OILFIELD SERVICE 1000**

## **HIGH PRESSURE OILFIELD HOSE**



## 

## APPLICATION

Used to transfer chemicals and fill tanks on blender trucks, such as "Chem Add" applications. Special chemical resistant tube. The Hypalon<sup>®</sup> cover provides additional resistance to oil and environmental conditions.

TEMPERATURE	( -40°C to +150°C) ( -40°F to +300°F)					
CONSTRUCTION	Tube	Туре Ј (СРЕ)				
	Reinforcement	Braided, High tensile steel wire				
	Cover	Type M (Hypalon®)				
STANDARDS	ARPM (Class A) High Oil Resistant Tube and MSHA 2G-IC-11C Flame resistant Cover					
COUPLINGS	MegaCrimp <sup>®</sup> , GlobalSpiral <sup>™</sup> and Stainless Steel Couplings					
CAUTION	1000 psi maximum working pressure for liquids, 300 psi maximum working pressure for gases					

$\ominus$	ţ	$\bigcirc$	$\bigcirc$	R	С Кg

ID		OD		WORKING PRESSURE		BURST PRESSURE		MBR		WEIGHT		MAX HOSE LENGTH	
inch	mm	inch	mm	bar	psi	bar	psi	inch	mm	kg/ft	lb/ft	ft	Pack
3/8	10	0.74	19	69	1000	276	4000	5.0	127	0.2	0.3	400	Reel - BB
1/2	13	0.86	22	69	1000	276	4000	7.0	178	0.2	0.4	400	Reel - GG
3/4	19	1.145	29	69	1000	276	4000	9.5	241	0.3	0.6	400	Reel - GG
1	25	1.48	38	69	1000	276	4000	12.0	305	0.4	1.0	400	Reel - GG

Gates Corporation is a leading manufacturer of application-specific fluid power and power transmission solutions. At Gates, we are driven to push the boundaries of materials science to engineer products that continually exceed expectations.