

## **PREMIUM**<sup>™</sup> WASHDOWN MASTER

$\bigcirc$	10	→Đ	$\odot$		R		i <del>∢ →</del> i	0	
мм	ММ	ММ	MPA	MPA	мм	KG/100M	м	REF.	
10	18	4.0	0.6	6.0	70	20	40	WASHDOWN MASTER 10mm x CL40	
13	23	5.0	0.6	6.0	91	40	40	WASHDOWN MASTER 13mm x CL40	
16	26	5.0	0.6	6.0	112	40	40	WASHDOWN MASTER 16mm x CL40	
19	31	6.0	0.6	6.0	133	60	40	WASHDOWN MASTER 19mm x CL40	
25	37	6.0	0.6	6.0	175	70	40	WASHDOWN MASTER 25mm x CL40	
32	45	6.5	0.6	6.0	224	90	40	WASHDOWN MASTER 32mm x CL40	
38	52	7.0	0.6	6.0	266	120	40	WASHDOWN MASTER 38mm x CL40	
51	65	7.0	0.6	6.0	357	150	40	WASHDOWN MASTER 51mm x CL40	
ECOMMEND	ED FOR			Premium hot water and open steam system washdown hose for the food and dairy industry. Used for paper mill, food handling or processing plant washdown service requiring a hose with a non-marking cover.					
JBE			EPDM ba	EPDM based rubber, white, smooth.					
				,	r				
EINFORCEM	ENT		High tens	High tensile textile cords.					

TEMPERATURE RANGE	-30°C to +164°C.
BURST PRESSURE	> 60 bar.
STANDARDS	FDA, animal derived ingredient free.
BRANDING TRANSFER LABEL	PREMIUM <sup>™</sup> WASHDOWN MASTER - FDA 6 BAR - STEAM OPEN SYSTEM