AS30S AIR HOSE 30 BAR & AS40S AIR HOSE 40 BAR



HIGH PRESSURE OILFIELD HOSE

APPLICATION

Compressed Air, Water - heavy duty applications

| TEMPERATURE | (-35°C to +100°C) (-31°F to +212°F) | | | | | | | |
|--------------|---|--|--|--|--|--|--|--|
| CONSTRUCTION | Tube | Black NBR Rubber | | | | | | |
| | Reinforcement | Wire Braid | | | | | | |
| | Cover | Yellow SBR Rubber Abrasion, Ozone & Weather Resistant | | | | | | |
| STANDARDS | Additional standards/certifications available upon customer request | | | | | | | |
| COUPLINGS | Crimped | | | | | | | |

$\bigoplus \qquad \fbox{} \qquad \textcircled{} \qquad \end{array}{} \qquad \textcircled{} \qquad \textcircled{} \qquad \textcircled{} \qquad \end{array}{} \qquad \textcircled{} \qquad \textcircled{} \qquad \end{array}{} \qquad \textcircled{} \qquad \textcircled{} \qquad \textcircled{} \qquad \end{array}{} \qquad \textcircled{} \qquad \textcircled{} \qquad \end{array}{} \qquad \textcircled{} \qquad \textcircled{} \qquad \textcircled{} \qquad \end{array}{} \qquad \textcircled{} \qquad \textcircled{} \qquad \textcircled{} \qquad \textcircled{} \qquad \textcircled{} \qquad \end{array}{} \qquad \textcircled{} \qquad \textcircled{} \qquad \textcircled{} \qquad \textcircled{} \qquad \textcircled{} \qquad \\ \end{array}{} \qquad \qquad \textcircled{} \qquad \\} \qquad \qquad \qquad \qquad \qquad$

| ID | | OD | | WORKING PRESSURE | | BURST PRESSURE | | MBR | | WEIGHT | | MAX HOSE LENGTH | | REFERENCE CODE | REFERENCE NUMBER |
|-------|-----|------|-----|---------------------|-----|-------------------|------|------|-----|--------|-------|--------------------|-----|-------------------|---------------------|
| inch | mm | inch | mm | bar | psi | bar | psi | inch | mm | kg/m | lb/ft | m | ft | | |
| 1 1/2 | 38 | 2.05 | 52 | 40 | 600 | 160 | 2400 | 7 | 0.2 | 1.6 | 1.1 | 60 | 196 | H2AS40S24 | - |
| 2 | 51 | 2.56 | 65 | 40 | 600 | 160 | 2400 | 10 | 0.3 | 2.2 | 1.5 | 60 | 196 | H2AS40S32 | _ |
| 3 | 76 | 3.74 | 95 | 30 | 450 | 120 | 1800 | 15 | 0.4 | 4.1 | 2.8 | 60 | 196 | H2AS30S48 | - |
| 4 | 102 | 4.76 | 121 | 30 | 450 | 120 | 1800 | 20 | 0.5 | 5.6 | 3.8 | 60 | 196 | H2AS30S64 | - |

Gates Corporation is a leading manufacturer of application-specific fluid power and power transmission solutions. At Gates, we are driven to push the boundaries of materials science to engineer products that continually exceed expectations.