BLACK GOLD[™] BLENDER TRANSFER 150D



HIGH PRESSURE OILFIELD HOSE

APPLICATION

Transfer of water, petroleum based fluids, dilute acids, chemicals and abrasive slurries used in oil and gas well stimulation and fracking.

TEMPERATURE	(-40°C to +82°C) (-40°F to +180°F)					
CONSTRUCTION	Tube	Type C (Nitrile)				
	Reinforcement	Synthetic, high tensile textile				
	Cover	Type A (Chloroprene)				
STANDARDS	Tube: ARPM (Class A) Nitrile for high oil resistance.					

E	\ominus \Box		\bigcirc (Ð	R			С Кg					
ID		OD		WORKING PRESSURE		BURST PRESSURE		VAC	MBR		WEIGHT		MAX HOSE LENGTH	
inch	mm	inch	mm	bar	psi	bar	psi	(in Hg)	inch	mm	kg/ft	lb/ft	ft	Pack
4	102	4.73	120	10.3	150	41.4	600	-	-	-	1.4	3.1	100	PLT - T
5	127	5.73	146	10.3	150	41.4	600	-	-	-	1.7	3.8	100	PLT - T

Gates Corporation is a leading manufacturer of application-specific fluid power and power transmission solutions. At Gates, we are driven to push the boundaries of materials science to engineer products that continually exceed expectations.