BLACK GOLD™ POTABLE WATER 150-300D

HIGH PRESSURE OILFIELD HOSE



APPLICATION

Transfer of potable water, non-potable water or liquids not containing oils or chemicals and applications which require a lightweight, flexible hose with a tight bend radius and a high rated working pressure in long continuous lengths.

TEMPERATURE	(-40°C to +66°C) (-40°F to +150°F)						
CONSTRUCTION	Tube	Type D2 (Natural Rubber - food grade)					
	Reinforcement	Multiple plies of synthetic cord					
	Cover	Type P (EPDM)					
STANDARDS	Tube meets FDA requirements.						
COUPLINGS	Interlocking ground or washer Joint, permanent swaged or crimped coupling, or Tri-Lokt						













				_	_		_							
ID		OD		WORKING PRESSURE		BURST PRESSURE		VAC	MBR		WEIGHT		MAX HOSE LENGTH	
inch	mm	inch	mm	bar	psi	bar	psi	(in Hg)	inch	mm	kg/ft	lb/ft	ft	Pack
1	25	1.53	39	20.7	300	82.7	1200	15	10	254	0.3	0.6	200	PLT - MTO
2	51	2.63	67	20.7	300	82.7	1200	10	14	356	0.5	1.2	200	PLT - MTO
3	76	3.61	92	13.8	200	55.2	800	10	21	533	0.8	1.7	200	PLT - MTO
4	102	4.70	119	10.3	150	41.4	600	10	28	711	1.0	2.2	200	PLT - MTO

Gates Corporation is a leading manufacturer of application-specific fluid power and power transmission solutions. At Gates, we are driven to push the boundaries of materials science to engineer products that continually exceed expectations.