

BP20H BULK PRODUCT SUCTION & DELIVERY HOSE 20 BAR



HIGH PRESSURE OILFIELD HOSE

APPLICATION

Heavy duty barite and cement

TEMPERATURE (-35°C to +85°C) (-31°F to +185°F)

CONSTRUCTION Tube Black SBR/NR Blend Rubber

Reinforcement High Tensile Synthetic Textile with Embedded Steel Helix Wire

Cover Black IR/BR Blend Rubber
Abrasion, Ozone & Weather Resistant

STANDARDS Additional standards/certifications available upon customer request

COUPLINGS Crimped



ID		OD		WORKING PRESSURE		BURST PRESSURE		MBR		WEIGHT		MAX HOSE LENGTH		REFERENCE CODE	REFERENCE NUMBER
inch	mm	inch	mm	bar	psi	bar	psi	inch	mm	kg/m	lb/ft	m	ft		
3	51	2.83	72	20	300	80	1200	15	0.4	4.2	2.8	60	196	H2BP20H48	-
4	102	5.00	127	20	300	80	1200	20	0.5	6.7	4.5	60	196	H2BP20H64	-
5	127	6.14	156	20	300	80	1200	25	0.6	10.1	6.8	60	196	H2BP20H80	-
6	152	7.24	184	20	300	80	1200	30	0.8	12.9	8.7	60	196	H2BP20H96	-

Gates Corporation is a leading manufacturer of application-specific fluid power and power transmission solutions. At Gates, we are driven to push the boundaries of materials science to engineer products that continually exceed expectations.