CE16H CHEMICAL SUCTION & DELIVERY HOSE 16 BAR



HIGH PRESSURE OILFIELD HOSE

APPLICATION

Acid and chemical suction & delivery suitable for 98% of existing chemicals

TEMPERATURE	(-30°C to +100°C) (-22°F to +212°F)						
CONSTRUCTION	Tube	Black Conductive EPDM Blend Rubber					
	Reinforcement	High Tensile Synthetic Textile with Embedded Zinc Plated Steel Helix Wire, Copper Static Wire					
	Cover	Black CR Rubber Abrasion, Ozone, Oil & Weather Resistant					
STANDARDS	Additional standards/certifications available upon customer request						
COUPLINGS	Crimped						













ID		OD		WORKING PRESSURE		BURST PRESSURE		MBR		WEIGHT		MAX HOSE LENGTH		REFERENCE CODE	REFERENCE NUMBER
inch	mm	inch	mm	bar	psi	bar	psi	inch	mm	kg/m	lb/ft	m	ft		
1	25	1.46	37	16	232	64	928	10	0.3	1.0	0.7	60	196	H2CE16H16	-
1 1/2	38	2.01	51	16	232	64	928	16	0.4	1.6	1.1	60	196	H2CE16H24	-
2	51	2.64	67	16	232	64	928	22	0.6	2.4	1.6	60	196	H2CE16H32	-
3	76	3.58	91	16	232	64	928	31	0.8	3.1	2.1	60	196	H2CE16H48	-

Gates Corporation is a leading manufacturer of application-specific fluid power and power transmission solutions. At Gates, we are driven to push the boundaries of materials science to engineer products that continually exceed expectations.