

CEMENTING 10000

HIGH PRESSURE OILFIELD HOSE



APPLICATION

Used as a flexible connection between the cementing pump manifold and cementing head for conveyance of cement slurries at high pressure. The UltraBration™ cover is designed to handle external damage from abrasion, corrosion, gouges, oil and weather.

TEMPERATURE (-20°C to +82°C) (-4°F to +180°F)

CONSTRUCTION **Tube** Type C3 (Modified Nitrile)

Reinforcement Multiple layers of textile fabric and steel cable

Cover Type C4 (Modified Nitrile)

FSL RATING FSL 0 all sizes

STANDARDS API 7K 6th Edition, ISO 47693, ABS Type Approvals

COUPLINGS Swaged Couplings



ID		OD		WORKING PRESSURE		BURST PRESSURE		MBR		WEIGHT		MAX HOSE LENGTH
inch	mm	inch	mm	bar	psi	bar	psi	inch	mm	kg/ft	lb/ft	ft
2 1/2	64	5.16	131	689	10000	1550	22500	48	1219	9	20	90
3	76	5.66	144	689	10000	1550	22500	48	1219	10	23	90
3 1/2	89	6.04	153	689	10000	1550	22500	54	1372	11	24	90

Gates Corporation is a leading manufacturer of application-specific fluid power and power transmission solutions. At Gates, we are driven to push the boundaries of materials science to engineer products that continually exceed expectations.